

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562861

Luminaire Tested: **SQ4-PC3-0U-100D-940-1D-UNV-STD-W-12**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P562861  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-289-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PC3-0U-100D-940-1D-UNV-STD-W-12  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.  
DOWNLIGHT 1000 LUMENS PER FOOT  
DIRECT ONLY  
Light Source: 4000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 9995.1 lumens  
Efficiency: N/A  
Efficacy: 92.4 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37  
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')  
CIE Type: Direct

Input Watts (W): 108.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P562861  
CATALOG NUMBER: SQ4-PC3-0U-100D-940-1D-UNV-STD-W-12

### Luminous Intensity Polar Plot





TEST NUMBER: P562861

CATALOG NUMBER: SQ4-PC3-0U-100D-940-1D-UNV-STD-W-12

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	105	100	97	106	102	98	95	98	95	92	94	92	89	91	88	87	85
2	99	91	85	79	97	90	83	78	86	81	76	83	78	75	80	76	73	71
3	91	80	72	66	88	79	71	65	76	70	64	73	68	63	71	66	62	60
4	83	71	63	56	81	70	62	56	68	61	55	65	59	54	63	58	53	51
5	77	64	55	48	74	63	54	48	61	53	48	59	52	47	57	51	47	44
6	71	58	49	42	69	57	48	42	55	47	42	53	46	41	52	46	41	39
7	66	52	43	37	64	51	43	37	50	42	37	48	42	37	47	41	36	34
8	61	48	39	33	60	47	39	33	46	38	33	44	38	33	43	37	33	31
9	57	44	36	30	56	43	35	30	42	35	30	41	34	30	40	34	29	28
10	54	40	32	27	52	40	32	27	39	32	27	38	31	27	37	31	27	25

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	11263	11263	11263
5°	11348	11275	11233
10°	11320	11267	11235
15°	11261	11261	11250
20°	11187	11220	11220
25°	11081	11162	11127
30°	10946	11079	11030
35°	10783	10949	10872
40°	10605	10755	10646
45°	10412	10486	10324
50°	10140	10140	9978
55°	9818	9691	9546
60°	9344	9156	9010
65°	8636	8464	8390
70°	7562	7622	7593
75°	6084	6729	6769
80°	4325	5705	5765
85°	2632	4785	4785



TEST NUMBER: P562861

CATALOG NUMBER: SQ4-PC3-0U-100D-940-1D-UNV-STD-W-12

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	346.6	3.5
10°-20°	994.6	10.0
20°-30°	1506.2	15.1
30°-40°	1805.8	18.1
40°-50°	1841.3	18.4
50°-60°	1607.3	16.1
60°-70°	1150.7	11.5
70°-80°	592.7	5.9
80°-90°	149.9	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2847.5	28.5
0°-40°	4653.2	46.6
0°-60°	8101.8	81.1
0°-90°	9995.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9995.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	3662	3662	3662	3662	3662	
5°	3676	3639	3652	3642	3638	349
15°	3537	3507	3537	3537	3533	997
25°	3266	3242	3289	3279	3279	1503
35°	2872	2866	2916	2896	2896	1796
45°	2394	2387	2411	2380	2374	1843
55°	1831	1808	1807	1780	1780	1632
65°	1187	1160	1163	1153	1153	1174
75°	512	535	566	570	570	553
85°	75	114	136	139	136	104
90°	0	0	0	0	0	



TEST NUMBER: P562861

CATALOG NUMBER: SQ4-PC3-0U-100D-940-1D-UNV-STD-W-12

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	3662.3	3662.3	3662.3	3662.3	3662.3
2.5°	3684.0	3652.1	3662.3	3653.8	3640.6
5°	3675.8	3639.4	3652.1	3641.9	3638.5
7.5°	3649.4	3612.9	3629.7	3622.9	3619.5
10°	3625.0	3588.5	3608.0	3601.2	3597.8
12.5°	3592.4	3558.6	3580.9	3574.1	3573.4
15°	3536.8	3507.0	3536.8	3536.7	3533.4
17.5°	3467.0	3439.8	3471.7	3473.7	3471.7
20°	3418.1	3388.3	3428.3	3425.0	3428.3
22.5°	3358.4	3333.9	3376.8	3368.0	3371.3
25°	3265.5	3242.3	3289.3	3279.1	3279.1
27.5°	3155.7	3139.1	3190.2	3179.4	3179.4
30°	3082.4	3065.8	3119.7	3106.1	3106.1
32.5°	3001.0	2989.8	3041.0	3024.8	3024.8
35°	2872.2	2865.5	2916.3	2895.9	2895.9
37.5°	2739.2	2733.3	2779.3	2754.7	2746.7
40°	2641.6	2638.3	2678.9	2651.8	2651.8
42.5°	2543.9	2540.6	2575.8	2543.2	2543.2
45°	2394.0	2387.4	2411.0	2380.3	2373.7
47.5°	2230.6	2224.0	2238.7	2205.4	2202.1
50°	2119.4	2112.7	2119.4	2088.8	2085.5
52.5°	2005.4	1993.5	1994.6	1964.0	1963.4
55°	1831.1	1807.9	1807.4	1780.3	1780.3
57.5°	1646.7	1616.2	1618.9	1595.7	1592.4
60°	1519.2	1486.0	1488.6	1468.2	1464.9
62.5°	1394.4	1355.9	1363.9	1340.8	1340.1
65°	1186.8	1160.3	1163.1	1152.9	1152.9
67.5°	987.5	962.9	980.7	972.5	971.9
70°	841.0	824.4	847.7	847.7	844.4
72.5°	705.3	704.7	733.8	733.9	735.8
75°	512.0	535.2	566.3	569.7	569.7
77.5°	341.8	382.9	417.1	418.4	417.8
80°	244.2	290.6	322.1	328.9	325.5
82.5°	165.5	214.6	240.8	247.5	244.2
85°	74.6	114.4	135.6	139.0	135.6
87.5°	21.7	45.6	54.3	54.1	48.8
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)