

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562909

Luminaire Tested: **SQ4-PC3-100U-050D-940-1D-UNV-STD-W-12**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562909
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-23, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-100U-050D-940-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 15523.2 lumens
Efficiency: N/A
Efficacy: 121.8 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 127.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562909
CATALOG NUMBER: SQ4-PC3-100U-050D-940-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P562909

CATALOG NUMBER: SQ4-PC3-100U-050D-940-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40	33
1	94	90	86	83	85	81	78	75	65	63	61	50	48	47	36	35	34	28
2	86	78	72	67	77	71	66	62	57	53	50	44	41	39	31	30	29	23
3	78	69	62	56	70	62	56	51	50	46	42	38	36	33	28	26	24	20
4	71	61	53	47	64	55	48	43	44	39	36	34	31	28	25	23	21	17
5	65	54	46	40	59	49	42	37	39	34	31	31	27	24	22	20	18	15
6	60	48	40	35	54	44	37	32	35	30	27	28	24	21	20	18	16	13
7	55	43	36	30	50	40	33	28	32	27	23	25	21	19	18	16	14	11
8	51	39	32	27	46	36	29	25	29	24	21	23	19	17	17	14	13	10
9	48	36	29	24	43	33	26	22	27	22	18	21	17	15	16	13	11	9
10	44	33	26	21	40	30	24	19	24	20	16	19	16	13	14	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5751	5751	5751
5°	5795	5757	5736
10°	5780	5754	5737
15°	5750	5750	5745
20°	5712	5729	5729
25°	5658	5699	5682
30°	5590	5657	5633
35°	5506	5591	5552
40°	5415	5492	5436
45°	5317	5354	5272
50°	5178	5178	5095
55°	5013	4948	4874
60°	4771	4676	4601
65°	4410	4322	4284
70°	3861	3893	3877
75°	3107	3436	3457
80°	2209	2913	2943
85°	1344	2445	2445



TEST NUMBER: P562909

CATALOG NUMBER: SQ4-PC3-100U-050D-940-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	177.0	1.1
10°-20°	507.9	3.3
20°-30°	769.1	5.0
30°-40°	922.1	5.9
40°-50°	940.2	6.1
50°-60°	820.7	5.3
60°-70°	587.6	3.8
70°-80°	302.6	1.9
80°-90°	79.9	0.5
90°-100°	750.7	4.8
100°-110°	2072.5	13.4
110°-120°	2137.5	13.8
120°-130°	1717.6	11.1
130°-140°	1349.9	8.7
140°-150°	1035.3	6.7
150°-160°	744.1	4.8
160°-170°	455.0	2.9
170°-180°	153.4	1.0
0°-30°	1454.0	9.4
0°-40°	2376.1	15.3
0°-60°	4137.0	26.7
0°-90°	5107.1	32.9
90°-120°	4960.7	32.0
90°-150°	9063.6	58.4
90°-180°	10416.0	67.1
0°-180°	15523.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1870	1870	1870	1870	1870	
5°	1877	1858	1865	1860	1858	178
15°	1806	1791	1806	1806	1804	509
25°	1668	1656	1680	1674	1674	767
35°	1467	1463	1489	1479	1479	917
45°	1222	1219	1231	1216	1212	941
55°	935	923	923	909	909	833
65°	606	592	594	589	589	599
75°	262	273	289	291	291	283
85°	38	58	69	71	69	52
90°	5	10	20	23	26	9
95°	110	406	1362	560	364	118
105°	369	570	2280	3481	3278	393
115°	662	800	1836	3636	4135	650
125°	908	1033	1665	2817	3306	808
135°	1093	1210	1618	2282	2573	845
145°	1267	1355	1598	1942	2090	793
155°	1429	1476	1585	1743	1798	658
165°	1547	1567	1593	1655	1667	436
175°	1603	1606	1595	1618	1613	152
180°	1603	1603	1603	1603	1603	



TEST NUMBER: P562909

CATALOG NUMBER: SQ4-PC3-100U-050D-940-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1870.1	1870.1	1870.1	1870.1	1870.1
2.5°	1881.2	1864.9	1870.1	1865.8	1859.0
5°	1877.0	1858.4	1864.9	1859.6	1858.0
7.5°	1863.5	1844.9	1853.5	1850.0	1848.3
10°	1851.0	1832.4	1842.4	1838.9	1837.2
12.5°	1834.4	1817.1	1828.5	1825.0	1824.7
15°	1806.0	1790.8	1806.0	1806.0	1804.3
17.5°	1770.3	1756.5	1772.8	1773.8	1772.8
20°	1745.4	1730.2	1750.6	1748.9	1750.6
22.5°	1714.9	1702.4	1724.3	1719.8	1721.5
25°	1667.5	1655.6	1679.6	1674.4	1674.4
27.5°	1611.4	1602.9	1629.0	1623.5	1623.5
30°	1574.0	1565.5	1593.0	1586.1	1586.1
32.5°	1532.4	1526.7	1552.9	1544.5	1544.5
35°	1466.6	1463.2	1489.1	1478.7	1478.7
37.5°	1398.7	1395.7	1419.2	1406.6	1402.6
40°	1348.9	1347.2	1367.9	1354.1	1354.1
42.5°	1299.0	1297.3	1315.3	1298.7	1298.7
45°	1222.5	1219.1	1231.1	1215.5	1212.1
47.5°	1139.0	1135.6	1143.2	1126.2	1124.5
50°	1082.2	1078.8	1082.2	1066.6	1064.9
52.5°	1024.0	1017.9	1018.5	1002.9	1002.6
55°	935.0	923.2	922.9	909.1	909.1
57.5°	840.8	825.3	826.6	814.8	813.1
60°	775.7	758.8	760.2	749.7	748.0
62.5°	712.0	692.4	696.4	684.6	684.3
65°	606.0	592.5	593.9	588.7	588.7
67.5°	504.2	491.7	500.8	496.6	496.3
70°	429.4	421.0	432.9	432.8	431.2
72.5°	360.2	359.8	374.7	374.7	375.7
75°	261.5	273.3	289.2	290.9	290.9
77.5°	174.5	195.5	213.0	213.7	213.3
80°	124.7	148.4	164.5	167.9	166.2
82.5°	84.5	109.6	122.9	126.4	124.7
85°	38.1	58.4	69.3	71.0	69.3
87.5°	12.1	25.3	31.8	32.3	30.1
90°	5.1	10.1	20.5	23.1	25.6
92.5°	46.2	191.6	342.7	125.1	97.5
95°	110.3	406.2	1362.0	559.8	364.2
97.5°	182.6	455.0	2017.6	1553.3	1125.0
100°	236.0	484.3	2259.7	2275.7	1849.3
102.5°	287.3	517.5	2306.9	2811.8	2407.5
105°	369.4	570.0	2280.2	3481.2	3278.0
107.5°	456.6	635.1	2153.0	3804.0	3878.2
110°	518.1	678.6	2054.5	3873.4	4114.2

TEST NUMBER: P562909

CATALOG NUMBER: SQ4-PC3-100U-050D-940-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	573.5	728.0	1962.2	3818.6	4173.7
115°	661.8	799.7	1836.5	3635.6	4134.7
117.5°	738.7	876.1	1753.9	3378.1	3945.9
120°	790.0	925.4	1721.1	3203.8	3775.6
122.5°	839.3	968.7	1694.4	3041.0	3582.7
125°	908.0	1033.4	1664.7	2817.2	3306.2
127.5°	966.5	1091.9	1647.2	2627.9	3049.7
130°	1005.5	1130.9	1639.0	2512.1	2895.8
132.5°	1042.4	1161.8	1630.8	2414.9	2762.5
135°	1092.7	1210.5	1618.5	2281.7	2572.7
137.5°	1149.1	1256.4	1612.3	2170.0	2418.2
140°	1179.9	1285.2	1608.2	2095.4	2313.6
142.5°	1214.8	1312.1	1604.1	2029.1	2221.3
145°	1267.1	1354.9	1598.0	1942.5	2090.4
147.5°	1317.4	1394.1	1592.3	1869.4	1984.2
150°	1354.3	1417.0	1590.3	1825.8	1918.6
152.5°	1383.0	1441.7	1588.2	1788.5	1865.2
155°	1428.7	1476.3	1585.1	1742.9	1798.0
157.5°	1470.7	1507.4	1585.7	1709.6	1747.2
160°	1495.4	1528.0	1587.7	1690.9	1718.5
162.5°	1515.9	1544.5	1589.8	1674.4	1695.9
165°	1546.7	1566.7	1592.8	1654.7	1667.2
167.5°	1570.3	1582.3	1595.4	1642.7	1646.7
170°	1582.6	1592.6	1595.4	1636.4	1636.4
172.5°	1592.8	1598.9	1595.4	1628.2	1626.2
175°	1603.1	1605.6	1595.4	1618.4	1613.4
177.5°	1607.2	1605.2	1594.9	1609.2	1605.1
180°	1603.1	1603.1	1603.1	1603.1	1603.1

(END OF REPORT)