

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563149

Luminaire Tested: **SQ4-PC3-150U-100D-940-1D-UNV-STD-W-12**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563149
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-25, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-150U-100D-940-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 25622.9 lumens
Efficiency: N/A
Efficacy: 114.5 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 223.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563149
CATALOG NUMBER: SQ4-PC3-150U-100D-940-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P563149

CATALOG NUMBER: SQ4-PC3-150U-100D-940-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46	39
1	95	91	87	84	87	83	80	77	68	65	63	54	52	51	41	40	39	33
2	87	80	74	69	79	73	67	63	59	56	52	47	45	42	36	34	33	28
3	79	70	63	57	72	64	58	53	52	48	44	42	38	36	32	30	28	23
4	72	62	54	48	65	56	50	44	46	41	37	37	33	31	28	26	24	20
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	23	21	17
6	61	49	41	35	55	45	38	33	37	32	28	30	26	23	23	20	18	15
7	56	44	36	31	51	41	34	29	34	28	25	27	23	20	21	18	16	13
8	52	40	32	27	47	37	30	25	31	25	22	25	21	18	19	17	14	12
9	49	37	29	24	44	34	27	23	28	23	19	23	19	16	18	15	13	11
10	45	33	26	22	41	31	24	20	26	21	17	21	17	15	16	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11263	11263	11263
5°	11348	11275	11233
10°	11320	11267	11235
15°	11261	11261	11250
20°	11187	11220	11220
25°	11081	11162	11127
30°	10946	11079	11030
35°	10783	10949	10872
40°	10605	10755	10646
45°	10412	10486	10324
50°	10140	10140	9978
55°	9818	9691	9546
60°	9344	9156	9010
65°	8636	8464	8390
70°	7562	7622	7593
75°	6084	6729	6769
80°	4325	5705	5765
85°	2632	4785	4785



TEST NUMBER: P563149

CATALOG NUMBER: SQ4-PC3-150U-100D-940-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	346.6	1.4
10°-20°	994.6	3.9
20°-30°	1506.2	5.9
30°-40°	1805.8	7.0
40°-50°	1841.3	7.2
50°-60°	1607.3	6.3
60°-70°	1150.7	4.5
70°-80°	592.7	2.3
80°-90°	154.9	0.6
90°-100°	1126.1	4.4
100°-110°	3044.8	11.9
110°-120°	3201.2	12.5
120°-130°	2600.2	10.1
130°-140°	2039.6	8.0
140°-150°	1565.4	6.1
150°-160°	1125.8	4.4
160°-170°	687.8	2.7
170°-180°	231.9	0.9
0°-30°	2847.5	11.1
0°-40°	4653.2	18.2
0°-60°	8101.8	31.6
0°-90°	10000.1	39.0
90°-120°	7372.0	28.8
90°-150°	13577.3	53.0
90°-180°	15623.0	61.0
0°-180°	25622.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3662	3662	3662	3662	3662	
5°	3676	3639	3652	3642	3638	349
15°	3537	3507	3537	3537	3533	997
25°	3266	3242	3289	3279	3279	1503
35°	2872	2866	2916	2896	2896	1796
45°	2394	2387	2411	2380	2374	1843
55°	1831	1808	1807	1780	1780	1632
65°	1187	1160	1163	1153	1153	1174
75°	512	535	566	570	570	553
85°	75	114	136	139	136	102
90°	5	15	34	36	34	15
95°	175	613	1873	969	576	183
105°	566	875	3378	4982	4778	596
115°	996	1218	2801	5423	6122	984
125°	1364	1563	2525	4261	5005	1216
135°	1635	1829	2457	3440	3894	1264
145°	1902	2044	2423	2945	3169	1190
155°	2147	2231	2402	2642	2728	990
165°	2337	2360	2413	2507	2520	658
175°	2426	2423	2415	2446	2441	230
180°	2423	2423	2423	2423	2423	

TEST NUMBER: P563149

CATALOG NUMBER: SQ4-PC3-150U-100D-940-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3662.3	3662.3	3662.3	3662.3	3662.3
2.5°	3684.0	3652.1	3662.3	3653.8	3640.6
5°	3675.8	3639.4	3652.1	3641.9	3638.5
7.5°	3649.4	3612.9	3629.7	3622.9	3619.5
10°	3625.0	3588.5	3608.0	3601.2	3597.8
12.5°	3592.4	3558.6	3580.9	3574.1	3573.4
15°	3536.8	3507.0	3536.8	3536.7	3533.4
17.5°	3467.0	3439.8	3471.7	3473.7	3471.7
20°	3418.1	3388.3	3428.3	3425.0	3428.3
22.5°	3358.4	3333.9	3376.8	3368.0	3371.3
25°	3265.5	3242.3	3289.3	3279.1	3279.1
27.5°	3155.7	3139.1	3190.2	3179.4	3179.4
30°	3082.4	3065.8	3119.7	3106.1	3106.1
32.5°	3001.0	2989.8	3041.0	3024.8	3024.8
35°	2872.2	2865.5	2916.3	2895.9	2895.9
37.5°	2739.2	2733.3	2779.3	2754.7	2746.7
40°	2641.6	2638.3	2678.9	2651.8	2651.8
42.5°	2543.9	2540.6	2575.8	2543.2	2543.2
45°	2394.0	2387.4	2411.0	2380.3	2373.7
47.5°	2230.6	2224.0	2238.7	2205.4	2202.1
50°	2119.4	2112.7	2119.4	2088.8	2085.5
52.5°	2005.4	1993.5	1994.6	1964.0	1963.4
55°	1831.1	1807.9	1807.4	1780.3	1780.3
57.5°	1646.7	1616.2	1618.9	1595.7	1592.4
60°	1519.2	1486.0	1488.6	1468.2	1464.9
62.5°	1394.4	1355.9	1363.9	1340.8	1340.1
65°	1186.8	1160.3	1163.1	1152.9	1152.9
67.5°	987.5	962.9	980.7	972.5	971.9
70°	841.0	824.4	847.7	847.7	844.4
72.5°	705.3	704.7	733.8	733.9	735.8
75°	512.0	535.2	566.3	569.7	569.7
77.5°	341.8	382.9	417.1	418.4	417.8
80°	244.2	290.6	322.1	328.9	325.5
82.5°	165.5	214.6	240.8	247.5	244.2
85°	74.6	114.4	135.6	139.0	135.6
87.5°	22.7	48.7	61.0	61.4	55.6
90°	5.2	15.4	33.9	36.5	33.9
92.5°	74.1	269.9	532.6	231.2	167.5
95°	174.8	613.4	1872.8	969.2	576.4
97.5°	280.7	703.5	2919.2	2415.8	1774.2
100°	359.9	739.9	3244.7	3383.9	2736.1
102.5°	433.0	790.5	3359.5	4117.9	3633.4
105°	566.0	874.6	3377.8	4982.5	4778.4
107.5°	689.1	970.7	3230.1	5521.8	5589.6
110°	785.1	1040.1	3098.7	5666.6	5954.8



TEST NUMBER: P563149

CATALOG NUMBER: SQ4-PC3-150U-100D-940-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	870.7	1109.4	2977.7	5637.7	6121.7
115°	996.4	1218.3	2801.3	5422.9	6121.7
117.5°	1119.5	1327.6	2685.0	5094.8	5887.0
120°	1194.6	1398.6	2616.1	4859.4	5667.9
122.5°	1265.6	1465.5	2574.4	4607.1	5421.6
125°	1364.1	1563.1	2524.8	4260.7	5005.4
127.5°	1454.9	1650.3	2495.6	3978.0	4632.9
130°	1505.0	1706.5	2483.1	3803.3	4395.0
132.5°	1557.2	1756.6	2470.6	3645.8	4190.5
135°	1635.4	1829.2	2457.0	3440.2	3894.2
137.5°	1714.2	1897.3	2445.6	3273.5	3643.3
140°	1768.4	1939.3	2441.4	3166.1	3495.1
142.5°	1820.6	1981.3	2433.0	3069.2	3357.4
145°	1901.5	2044.3	2423.1	2944.7	3169.1
147.5°	1975.0	2101.5	2411.6	2831.9	3004.3
150°	2029.3	2141.5	2407.5	2770.6	2908.3
152.5°	2079.3	2177.3	2405.4	2713.7	2826.9
155°	2146.6	2230.8	2402.3	2641.6	2728.3
157.5°	2216.5	2275.2	2402.8	2591.4	2648.5
160°	2256.2	2304.6	2404.9	2559.7	2600.5
162.5°	2287.5	2327.8	2407.0	2534.4	2565.0
165°	2337.0	2360.0	2412.7	2506.9	2519.6
167.5°	2371.0	2386.8	2413.2	2483.3	2489.4
170°	2391.8	2399.5	2415.3	2472.7	2472.7
172.5°	2408.5	2410.0	2415.3	2460.1	2458.1
175°	2425.7	2423.2	2415.3	2446.5	2441.4
177.5°	2431.5	2425.3	2414.8	2435.5	2429.4
180°	2423.1	2423.1	2423.1	2423.1	2423.1

(END OF REPORT)