

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563197

Luminaire Tested: **SQ4-PP3-025U-050D-940-1D-UNV-STD-W-12**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563197
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-32, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-025U-050D-940-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7587.8 lumens
Efficiency: N/A
Efficacy: 110.3 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 68.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563197

CATALOG NUMBER: SQ4-PP3-025U-050D-940-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P563197

CATALOG NUMBER: SQ4-PP3-025U-050D-940-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	71	71	71	67
1	102	97	94	90	96	92	89	86	82	79	77	72	70	69	64	62	61	57
2	93	85	79	74	87	81	75	71	72	68	64	64	61	58	56	54	52	48
3	85	75	68	62	80	71	65	59	64	58	54	57	52	49	50	47	44	41
4	78	67	59	53	73	63	56	50	57	51	46	51	46	42	45	41	38	35
5	72	60	51	45	67	57	49	44	51	45	40	45	41	37	40	37	33	31
6	66	54	45	39	62	51	43	38	46	40	35	41	36	32	37	33	29	27
7	61	49	40	35	57	46	39	33	42	36	31	37	32	29	34	29	26	24
8	57	44	36	31	53	42	35	30	38	32	28	34	29	26	31	27	24	21
9	53	40	33	28	50	39	31	27	35	29	25	32	27	23	28	24	21	19
10	50	37	30	25	47	35	29	24	32	26	22	29	24	21	26	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6075	6075	6075
5°	6119	6082	6060
10°	6109	6065	6039
15°	6068	6035	6002
20°	6028	5994	5949
25°	5957	5916	5857
30°	5846	5816	5742
35°	5694	5654	5583
40°	5511	5476	5414
45°	5361	5323	5270
50°	5168	5135	5085
55°	4901	4836	4799
60°	4461	4334	4312
65°	3930	3767	3754
70°	3394	3253	3253
75°	2921	2880	2839
80°	2575	2605	2545
85°	2015	2198	2198



TEST NUMBER: P563197

CATALOG NUMBER: SQ4-PP3-025U-050D-940-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	186.8	2.5
10°-20°	533.3	7.0
20°-30°	798.8	10.5
30°-40°	937.0	12.3
40°-50°	939.9	12.4
50°-60°	801.8	10.6
60°-70°	522.9	6.9
70°-80°	262.4	3.5
80°-90°	74.7	1.0
90°-100°	190.3	2.5
100°-110°	500.2	6.6
110°-120°	518.7	6.8
120°-130°	416.0	5.5
130°-140°	326.4	4.3
140°-150°	250.5	3.3
150°-160°	180.4	2.4
160°-170°	110.4	1.5
170°-180°	37.3	0.5
0°-30°	1518.9	20.0
0°-40°	2455.9	32.4
0°-60°	4197.6	55.3
0°-90°	5057.6	66.7
90°-120°	1209.1	15.9
90°-150°	2202.1	29.0
90°-180°	2530.0	33.3
0°-180°	7587.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1975	1975	1975	1975	1975	
5°	1982	1964	1970	1963	1963	188
15°	1906	1887	1896	1889	1885	538
25°	1755	1735	1743	1728	1726	807
35°	1516	1501	1506	1489	1487	947
45°	1233	1224	1224	1212	1212	949
55°	914	911	902	897	895	812
65°	540	530	518	514	516	539
75°	246	246	242	241	239	267
85°	57	62	62	62	62	67
90°	2	7	20	10	10	4
95°	25	98	328	169	115	28
105°	90	137	553	840	783	95
115°	160	194	443	884	1008	158
125°	223	250	403	681	803	198
135°	265	292	390	550	623	205
145°	308	327	385	469	506	193
155°	348	358	385	423	435	160
165°	375	380	385	400	405	106
175°	390	390	388	393	393	37
180°	390	390	390	390	390	

TEST NUMBER: P563197

CATALOG NUMBER: SQ4-PP3-025U-050D-940-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1975.2	1975.2	1975.2	1975.2	1975.2
2.5°	1987.7	1971.4	1975.2	1972.3	1964.2
5°	1982.2	1963.5	1970.0	1963.1	1963.1
7.5°	1968.7	1948.3	1954.8	1947.9	1947.5
10°	1956.2	1935.9	1942.3	1935.4	1933.7
12.5°	1938.2	1917.9	1925.7	1917.4	1917.1
15°	1906.0	1887.4	1895.6	1888.6	1885.2
17.5°	1869.6	1849.3	1859.2	1849.5	1848.2
20°	1841.9	1821.6	1831.5	1817.7	1817.7
22.5°	1808.7	1788.4	1799.7	1781.7	1781.7
25°	1755.4	1735.1	1743.3	1727.6	1725.9
27.5°	1692.0	1672.0	1680.6	1662.9	1662.6
30°	1646.3	1627.7	1637.7	1618.6	1616.9
32.5°	1596.5	1579.2	1586.4	1567.3	1565.6
35°	1516.5	1501.2	1506.1	1488.7	1487.1
37.5°	1432.3	1416.8	1422.3	1407.4	1406.7
40°	1372.8	1362.6	1364.1	1351.9	1348.6
42.5°	1317.4	1305.9	1307.4	1295.2	1294.5
45°	1232.6	1224.1	1223.9	1211.8	1211.8
47.5°	1142.6	1136.1	1134.2	1124.2	1123.9
50°	1080.2	1075.2	1073.3	1064.6	1062.9
52.5°	1015.1	1012.8	1006.8	999.6	999.2
55°	914.0	910.7	901.9	896.7	895.0
57.5°	804.3	797.5	787.7	780.1	781.4
60°	725.3	718.6	704.6	701.1	701.1
62.5°	649.2	641.1	627.0	622.2	624.9
65°	540.1	530.0	517.6	514.2	515.9
67.5°	441.1	432.0	418.6	418.6	417.2
70°	377.4	372.3	361.8	361.8	361.8
72.5°	320.6	318.2	310.6	310.5	309.2
75°	245.8	245.8	242.4	240.6	238.9
77.5°	184.2	184.9	183.2	181.4	178.3
80°	145.4	148.8	147.1	145.4	143.7
82.5°	109.4	112.8	112.5	109.4	109.1
85°	57.1	62.2	62.3	62.3	62.3
87.5°	15.7	22.1	26.2	24.2	25.5
90°	2.5	7.4	20.0	10.0	10.0
92.5°	10.5	50.6	112.1	49.6	32.0
95°	25.0	98.4	327.8	168.9	115.1
97.5°	43.5	108.1	490.5	390.0	287.3
100°	57.6	116.3	540.5	547.8	425.4
102.5°	69.6	124.4	554.5	682.3	577.6
105°	90.1	136.6	553.0	839.5	783.3
107.5°	111.1	154.2	521.5	921.2	934.9
110°	125.1	164.3	495.5	942.2	1001.0

TEST NUMBER: P563197

CATALOG NUMBER: SQ4-PP3-025U-050D-940-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	139.1	176.3	471.5	928.9	1019.0
115°	160.2	194.4	442.9	883.7	1008.5
117.5°	180.7	212.0	423.4	820.9	959.4
120°	192.7	222.0	415.4	778.8	913.4
122.5°	204.7	234.1	409.4	736.7	869.3
125°	222.7	249.6	402.9	680.9	803.3
127.5°	237.2	264.6	397.4	636.0	739.2
130°	245.2	274.6	395.4	607.8	703.2
132.5°	253.2	282.6	393.4	583.5	669.1
135°	265.3	292.2	390.4	549.7	623.1
137.5°	277.8	304.2	389.9	524.4	584.6
140°	287.8	312.2	387.9	504.3	560.5
142.5°	295.8	318.3	387.9	490.1	538.5
145°	307.8	327.4	385.4	468.8	505.5
147.5°	319.8	338.9	385.4	451.1	481.5
150°	327.8	344.9	385.4	441.0	465.4
152.5°	335.8	349.0	385.4	432.8	451.4
155°	347.8	357.6	385.4	423.2	435.4
157.5°	356.8	366.1	385.4	414.6	423.4
160°	362.8	370.2	385.4	410.5	415.4
162.5°	368.9	374.2	385.4	406.5	411.4
165°	375.4	380.3	385.4	400.5	405.4
167.5°	381.4	383.8	387.9	397.9	399.9
170°	385.4	387.8	387.9	397.9	397.9
172.5°	387.4	387.9	387.9	395.8	393.9
175°	390.4	390.4	387.9	392.9	392.9
177.5°	390.4	390.4	388.4	392.3	390.4
180°	390.4	390.4	390.4	390.4	390.4

(END OF REPORT)