

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P936476

Luminaire Tested: SQ4-FB-025U-100D-940-1D-UNV-STD-W-8

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P936476
REPORT IS A COMBINATION OF REPORTS P933455 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-025U-100D-940-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7365.1 lumens
Efficiency: N/A
Efficacy: 94.9 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 8' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 77.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P936476
CATALOG NUMBER: SQ4-FB-025U-100D-940-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P936476

CATALOG NUMBER: SQ4-FB-025U-100D-940-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									20
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	113	113	113	113	108	108	108	108	98	98	98	89	89	89	81	81	81	77																			77									
1	103	98	94	90	98	94	90	86	85	82	79	77	75	73	70	68	66	63																			63									
2	93	85	78	72	88	81	75	69	73	68	64	67	63	59	61	57	55	51																			51									
3	84	74	65	59	80	70	63	57	64	58	53	58	53	49	53	49	45	42																			42									
4	77	65	56	49	73	62	54	47	56	50	44	51	46	41	47	42	38	35																			35									
5	70	57	48	42	66	55	46	40	50	43	38	46	40	35	41	37	33	30																			30									
6	64	51	42	36	61	49	41	35	45	38	32	41	35	30	37	32	28	26																			26									
7	59	46	37	31	56	44	36	30	40	33	28	37	31	27	34	29	25	22																			22									
8	55	42	33	27	52	40	32	26	37	30	25	34	28	23	31	26	22	20																			20									
9	51	38	30	24	49	36	29	23	33	27	22	31	25	21	28	23	20	17																			17									
10	48	35	27	21	45	33	26	21	31	24	20	28	23	19	26	21	17	16																			16									

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3386	3386	3386
5°	3308	3914	4551
10°	3001	5705	7546
15°	2550	7453	9111
20°	2076	8637	9286
25°	1732	9038	9097
30°	1461	9095	9080
35°	1291	8945	9314
40°	1125	8748	9557
45°	1019	8604	9595
50°	935	8475	9436
55°	895	8285	9018
60°	916	7922	8358
65°	954	7369	7450
70°	1015	6426	6294
75°	1125	5240	4912
80°	1230	3634	3310
85°	1090	1928	1695

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 9595 cd/sqm



TEST NUMBER: P936476

CATALOG NUMBER: SQ4-FB-025U-100D-940-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.4	1.3
10°-20°	418.4	5.7
20°-30°	731.9	9.9
30°-40°	942.1	12.8
40°-50°	1052.3	14.3
50°-60°	1007.9	13.7
60°-70°	798.7	10.8
70°-80°	469.7	6.4
80°-90°	131.5	1.8
90°-100°	129.2	1.8
100°-110°	339.7	4.6
110°-120°	352.2	4.8
120°-130°	282.5	3.8
130°-140°	221.7	3.0
140°-150°	170.1	2.3
150°-160°	122.5	1.7
160°-170°	75.0	1.0
170°-180°	25.3	0.3
0°-30°	1244.7	16.9
0°-40°	2186.8	29.7
0°-60°	4247.0	57.7
0°-90°	5646.9	76.7
90°-120°	821.0	11.1
90°-150°	1495.3	20.3
90°-180°	1718.0	23.3
0°-180°	7365.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	730	730	730	730	730	
5°	711	763	859	972	1007	66
15°	533	983	1657	2009	2072	148
25°	340	1115	1974	2060	2063	157
35°	230	1065	1859	1964	2042	144
45°	157	850	1643	1882	1967	122
55°	113	540	1394	1619	1664	103
65°	89	286	1035	1164	1180	88
75°	66	176	568	624	627	69
85°	23	54	141	155	157	25
90°	2	5	14	7	7	3
95°	17	67	222	115	78	19
105°	61	93	376	570	532	65
115°	109	132	301	600	685	107
125°	151	170	274	462	545	134
135°	180	198	265	373	423	139
145°	209	222	262	318	343	131
155°	236	243	262	287	296	109
165°	255	258	262	272	275	72
175°	265	265	264	267	267	25
180°	265	265	265	265	265	



TEST NUMBER: P936476

CATALOG NUMBER: SQ4-FB-025U-100D-940-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	729.8	729.8	729.8	729.8	729.8	729.8	729.8	729.8	729.8	729.8	729.8
2.5°	729.8	729.8	734.6	736.9	741.6	743.9	748.6	753.3	767.4	769.7	774.4
5°	711.0	720.4	751.0	762.7	795.6	840.1	858.9	889.4	952.7	971.6	983.3
7.5°	682.9	704.0	779.1	797.9	880.0	997.3	1046.6	1112.3	1213.3	1262.6	1302.4
10°	638.3	682.9	816.7	861.3	995.0	1173.3	1264.9	1356.4	1508.9	1577.0	1602.8
12.5°	589.0	661.7	856.6	917.6	1110.0	1370.5	1480.7	1581.7	1755.3	1846.9	1860.9
15°	532.7	631.3	894.1	983.3	1232.0	1534.7	1656.7	1781.2	1943.0	2008.7	2025.2
17.5°	483.4	607.8	929.3	1023.2	1325.9	1682.6	1807.0	1910.2	2041.6	2086.2	2098.0
20°	422.4	570.3	952.7	1074.7	1424.4	1790.6	1910.2	1990.0	2079.2	2107.3	2112.0
22.5°	377.8	530.3	966.9	1093.6	1490.2	1856.3	1957.2	2020.5	2081.6	2090.9	2093.3
25°	340.3	485.7	964.5	1114.7	1546.5	1896.1	1973.6	2020.5	2055.7	2060.4	2060.4
27.5°	305.0	436.5	955.1	1119.4	1588.7	1905.6	1966.6	1999.4	2015.8	2025.2	2025.2
30°	274.6	389.6	931.6	1110.0	1607.5	1896.1	1945.4	1961.9	1978.3	1992.3	1999.4
32.5°	251.1	345.0	896.4	1091.2	1609.9	1872.7	1907.9	1917.3	1940.7	1973.6	1985.3
35°	230.0	300.4	856.6	1065.4	1595.7	1835.1	1858.6	1868.0	1914.9	1964.2	1980.6
37.5°	208.9	267.6	804.9	1020.8	1574.6	1790.6	1807.0	1823.4	1896.1	1954.8	1973.6
40°	187.7	239.4	743.9	971.6	1541.7	1736.6	1750.6	1776.4	1872.7	1940.7	1959.5
42.5°	171.3	215.9	678.2	919.9	1499.6	1675.6	1696.7	1734.2	1844.5	1917.3	1938.4
45°	157.3	192.4	607.8	849.5	1445.6	1612.2	1642.7	1694.3	1811.6	1882.0	1900.9
47.5°	143.1	176.0	535.0	776.7	1386.9	1548.8	1588.7	1647.4	1767.0	1835.1	1851.6
50°	131.4	159.6	462.3	699.3	1323.6	1480.7	1527.7	1588.7	1710.7	1774.1	1795.2
52.5°	122.0	145.5	394.3	621.9	1250.7	1410.3	1464.3	1527.7	1642.7	1703.7	1717.7
55°	112.6	133.7	335.6	539.7	1175.7	1335.3	1393.9	1455.0	1567.6	1619.2	1628.6
57.5°	108.0	124.4	286.3	462.3	1095.9	1250.7	1316.5	1372.8	1478.4	1518.3	1527.7
60°	100.9	117.3	248.7	396.6	1009.1	1171.0	1227.3	1283.6	1372.8	1405.7	1412.7
62.5°	93.9	112.6	220.6	333.3	919.9	1077.1	1133.4	1185.1	1260.2	1283.6	1293.0
65°	89.2	108.0	199.4	286.3	828.4	978.6	1034.9	1079.5	1140.5	1164.0	1168.7
67.5°	84.4	103.3	183.0	246.4	736.9	880.0	922.3	964.5	1011.4	1034.9	1037.3
70°	77.4	98.6	169.0	218.3	643.0	767.4	802.6	847.2	884.7	896.4	903.5
72.5°	72.7	91.6	159.6	197.1	546.7	659.4	692.3	718.1	751.0	762.7	762.7
75°	65.7	82.1	150.2	176.0	448.3	539.7	567.9	593.7	619.6	624.3	617.2
77.5°	58.7	72.7	129.0	147.9	349.7	427.1	450.6	464.6	485.7	490.4	492.8
80°	49.3	63.4	100.9	115.0	253.4	314.4	330.9	342.6	361.4	361.4	366.1
82.5°	37.6	49.3	72.7	82.1	171.3	215.9	230.0	237.0	248.7	248.7	248.7
85°	23.4	30.5	47.0	54.0	103.3	131.4	140.8	143.1	152.6	154.9	154.9
87.5°	11.7	16.4	30.5	32.9	54.0	68.0	68.0	72.7	72.7	70.4	68.0
90°	1.8	3.2	4.6	5.0	7.8	11.6	13.5	12.0	9.0	6.7	6.7
92.5°	7.1	19.2	31.3	34.4	48.3	66.9	76.1	66.7	48.0	33.8	32.5
95°	17.0	39.2	61.4	66.9	118.7	187.9	222.5	198.6	150.7	114.7	110.6
97.5°	29.6	49.1	68.6	73.4	159.9	275.3	333.0	317.9	287.6	264.9	257.2
100°	39.2	56.8	74.5	78.9	174.9	302.9	366.9	368.1	370.3	372.0	362.7
102.5°	47.3	63.8	80.4	84.4	181.9	311.7	376.6	395.9	434.4	463.4	455.5
105°	61.2	75.2	89.2	92.7	187.0	312.7	375.5	418.8	505.3	570.1	565.8
107.5°	75.4	88.4	101.5	104.8	187.9	298.7	354.1	414.4	535.1	625.6	626.7
110°	85.1	96.8	108.6	111.5	186.5	286.4	336.4	403.8	538.7	639.8	644.2



TEST NUMBER: P936476

CATALOG NUMBER: SQ4-FB-025U-100D-940-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	94.5	105.7	116.9	119.7	186.6	275.6	320.2	389.2	527.2	630.7	637.6
115°	108.7	119.0	129.4	132.0	188.3	263.3	300.8	367.3	500.3	600.0	609.4
117.5°	122.7	132.1	141.5	143.9	191.8	255.6	287.4	347.5	467.4	557.5	568.0
120°	130.9	139.8	148.7	150.9	194.6	253.0	282.1	336.9	446.6	528.8	538.9
122.5°	138.9	147.9	156.8	159.0	198.7	251.6	278.0	327.4	426.2	500.2	510.2
125°	151.2	159.4	167.5	169.5	204.2	250.5	273.6	315.5	399.4	462.3	471.5
127.5°	161.2	169.3	177.6	179.6	209.7	249.8	269.9	305.9	377.9	431.9	439.7
130°	166.5	175.4	184.2	186.4	213.7	250.2	268.4	300.5	364.6	412.7	419.8
132.5°	172.0	180.9	189.7	191.9	217.0	250.5	267.2	295.9	353.2	396.3	402.8
135°	180.2	188.3	196.3	198.4	220.6	250.2	265.1	289.1	337.2	373.2	378.7
137.5°	188.5	196.5	204.5	206.5	225.9	251.7	264.7	285.0	325.6	356.1	360.6
140°	195.4	202.8	210.2	212.1	229.2	252.0	263.5	281.1	316.1	342.4	346.7
142.5°	200.9	207.6	214.5	216.1	231.9	253.0	263.5	278.9	309.7	332.8	336.5
145°	209.0	215.0	220.8	222.4	235.5	253.0	261.7	274.3	299.5	318.4	321.2
147.5°	217.2	223.0	228.7	230.2	240.6	254.7	261.7	271.6	291.4	306.3	308.6
150°	222.5	227.8	232.9	234.3	243.4	255.6	261.7	270.0	286.8	299.3	301.2
152.5°	228.0	231.9	235.9	236.9	245.2	256.2	261.7	268.8	283.1	293.8	295.3
155°	236.2	239.1	242.1	242.8	249.1	257.5	261.7	267.4	278.7	287.3	288.2
157.5°	242.2	245.1	247.9	248.6	253.0	258.8	261.7	266.1	274.9	281.6	282.2
160°	246.3	248.6	250.8	251.3	254.8	259.4	261.7	265.5	273.1	278.7	279.1
162.5°	250.4	252.1	253.7	254.1	256.6	260.0	261.7	264.9	271.3	276.1	276.4
165°	254.9	256.5	258.0	258.3	259.5	261.0	261.7	264.0	268.5	272.0	272.3
167.5°	259.0	259.7	260.5	260.6	261.6	262.8	263.5	265.0	268.0	270.2	270.4
170°	261.7	262.4	263.1	263.3	263.4	263.5	263.5	265.0	268.0	270.2	270.2
172.5°	263.1	263.3	263.5	263.5	263.5	263.5	263.5	264.6	267.0	268.8	268.6
175°	265.1	265.1	265.1	265.1	264.5	263.8	263.5	264.2	265.7	266.8	266.8
177.5°	265.1	265.1	265.1	265.1	264.6	264.1	263.8	264.4	265.6	266.5	266.3
180°	265.1	265.1	265.1	265.1	265.1	265.1	265.1	265.1	265.1	265.1	265.1



TEST NUMBER: P936476

CATALOG NUMBER: SQ4-FB-025U-100D-940-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	729.8	729.8
2.5°	779.1	774.4
5°	1002.0	1006.7
7.5°	1349.3	1347.0
10°	1677.9	1699.0
12.5°	1917.3	1922.0
15°	2062.7	2072.1
17.5°	2119.0	2121.4
20°	2121.4	2116.7
22.5°	2095.6	2090.9
25°	2065.1	2062.7
27.5°	2036.9	2039.3
30°	2025.2	2032.3
32.5°	2025.2	2036.9
35°	2029.9	2041.6
37.5°	2027.6	2041.6
40°	2018.2	2034.6
42.5°	1992.3	2004.0
45°	1952.4	1966.6
47.5°	1900.9	1910.2
50°	1835.1	1844.5
52.5°	1753.0	1755.3
55°	1654.4	1663.8
57.5°	1548.8	1551.2
60°	1431.5	1438.6
62.5°	1307.1	1307.1
65°	1175.7	1180.4
67.5°	1039.6	1051.3
70°	901.1	903.5
72.5°	765.0	765.0
75°	624.3	626.6
77.5°	490.4	490.4
80°	363.7	366.1
82.5°	251.1	255.8
85°	157.3	157.3
87.5°	72.7	65.7
90°	6.7	6.7
92.5°	27.1	21.7
95°	94.4	78.1
97.5°	226.1	195.1
100°	325.8	288.9
102.5°	423.8	392.2
105°	548.9	531.8
107.5°	630.7	634.8
110°	661.9	679.7



TEST NUMBER: P936476

CATALOG NUMBER: SQ4-FB-025U-100D-940-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	664.8	691.9
115°	647.2	684.8
117.5°	609.8	651.6
120°	579.6	620.3
122.5°	550.3	590.3
125°	508.5	545.4
127.5°	470.8	502.0
130°	448.6	477.4
132.5°	428.5	454.3
135°	400.9	423.1
137.5°	378.8	397.0
140°	363.6	380.7
142.5°	351.1	365.7
145°	332.3	343.3
147.5°	317.7	327.0
150°	308.7	316.1
152.5°	300.9	306.4
155°	291.9	295.6
157.5°	284.9	287.4
160°	280.6	282.1
162.5°	277.9	279.3
165°	273.9	275.4
167.5°	271.0	271.6
170°	270.2	270.2
172.5°	268.1	267.6
175°	266.8	266.8
177.5°	265.7	265.1
180°	265.1	265.1



TEST NUMBER: P936476
 CATALOG NUMBER: SQ4-FB-025U-100D-940-1D-UNV-STD-W-8

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.37	8.61	8.05	9.31	10.14	20.55	21.79	21.23	22.49	23.32
	3H	8.11	9.22	8.80	9.94	10.80	22.42	23.53	23.11	24.25	25.11
	4H	8.42	9.47	9.13	10.20	11.07	23.08	24.13	23.79	24.86	25.73
	6H	8.69	9.67	9.42	10.40	11.29	23.53	24.51	24.26	25.24	26.13
	8H	8.77	9.70	9.51	10.46	11.35	23.66	24.59	24.40	25.35	26.24
	12H	8.80	9.69	9.54	10.44	11.36	23.74	24.63	24.49	25.38	26.30
4H	2H	14.63	15.69	15.35	16.41	17.28	20.87	21.92	21.59	22.65	23.52
	3H	16.23	17.12	16.96	17.88	18.77	22.95	23.83	23.68	24.60	25.49
	4H	16.34	17.15	17.09	17.91	18.83	23.73	24.54	24.48	25.30	26.22
	6H	16.38	17.08	17.14	17.87	18.79	24.29	25.00	25.06	25.78	26.71
	8H	16.36	17.02	17.13	17.80	18.75	24.47	25.12	25.23	25.91	26.85
	12H	16.34	16.93	17.13	17.74	18.69	24.58	25.17	25.37	25.98	26.92
8H	4H	17.82	18.48	18.59	19.26	20.20	23.82	24.48	24.59	25.27	26.21
	6H	18.08	18.63	18.88	19.45	20.40	24.47	25.02	25.27	25.84	26.79
	8H	18.10	18.59	18.91	19.42	20.37	24.70	25.18	25.51	26.01	26.97
	12H	18.09	18.52	18.90	19.34	20.35	24.86	25.29	25.67	26.10	27.12
12H	4H	17.98	18.58	18.77	19.38	20.33	23.80	24.39	24.59	25.20	26.14
	6H	18.34	18.83	19.15	19.66	20.61	24.46	24.95	25.27	25.77	26.73
	8H	18.43	18.86	19.25	19.68	20.69	24.71	25.14	25.52	25.95	26.97