

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563581

Luminaire Tested: **SQ4-PP3-100U-050D-940-1D-UNV-STD-W-12**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563581
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-23, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-100U-050D-940-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 15474.9 lumens
Efficiency: N/A
Efficacy: 121.5 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 127.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563581
CATALOG NUMBER: SQ4-PP3-100U-050D-940-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P563581

CATALOG NUMBER: SQ4-PP3-100U-050D-940-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40	33				
1	94	90	86	83	85	81	78	75	65	63	61	50	48	47	36	35	34	28				
2	86	79	73	68	77	71	66	62	57	53	50	44	41	39	32	30	29	23				
3	78	69	62	56	70	63	57	52	50	46	42	39	36	33	28	26	25	20				
4	71	61	53	48	64	55	49	44	45	40	36	34	31	29	25	23	21	17				
5	66	54	47	41	59	49	43	37	40	35	31	31	27	25	23	20	19	15				
6	60	49	41	35	54	44	37	32	36	31	27	28	24	22	20	18	16	13				
7	56	44	36	31	50	40	33	28	32	27	24	25	22	19	19	16	15	12				
8	52	40	32	27	46	36	30	25	29	24	21	23	20	17	17	15	13	10				
9	48	36	29	24	43	33	27	22	27	22	19	21	18	15	16	13	12	9				
10	45	33	26	21	40	30	24	20	25	20	17	19	16	14	15	12	11	9				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6075	6075	6075
5°	6119	6082	6060
10°	6109	6065	6039
15°	6068	6035	6002
20°	6028	5994	5949
25°	5957	5916	5857
30°	5846	5816	5742
35°	5694	5654	5583
40°	5511	5476	5414
45°	5361	5323	5270
50°	5168	5135	5085
55°	4901	4836	4799
60°	4461	4334	4312
65°	3930	3767	3754
70°	3394	3253	3253
75°	2921	2880	2839
80°	2575	2605	2545
85°	2015	2198	2198



TEST NUMBER: P563581

CATALOG NUMBER: SQ4-PP3-100U-050D-940-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	186.8	1.2
10°-20°	533.3	3.4
20°-30°	798.8	5.2
30°-40°	937.0	6.1
40°-50°	939.9	6.1
50°-60°	801.8	5.2
60°-70°	522.9	3.4
70°-80°	262.4	1.7
80°-90°	75.9	0.5
90°-100°	750.7	4.9
100°-110°	2072.5	13.4
110°-120°	2137.5	13.8
120°-130°	1717.6	11.1
130°-140°	1349.9	8.7
140°-150°	1035.3	6.7
150°-160°	744.1	4.8
160°-170°	455.0	2.9
170°-180°	153.4	1.0
0°-30°	1518.9	9.8
0°-40°	2455.9	15.9
0°-60°	4197.6	27.1
0°-90°	5058.8	32.7
90°-120°	4960.7	32.1
90°-150°	9063.6	58.6
90°-180°	10416.0	67.3
0°-180°	15474.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1975	1975	1975	1975	1975	
5°	1982	1964	1970	1963	1963	188
15°	1906	1887	1896	1889	1885	538
25°	1755	1735	1743	1728	1726	807
35°	1516	1501	1506	1489	1487	947
45°	1233	1224	1224	1212	1212	949
55°	914	911	902	897	895	812
65°	540	530	518	514	516	539
75°	246	246	242	241	239	267
85°	57	62	62	62	62	67
90°	5	10	20	23	26	10
95°	110	406	1362	560	364	118
105°	369	570	2280	3481	3278	393
115°	662	800	1836	3636	4135	650
125°	908	1033	1665	2817	3306	808
135°	1093	1210	1618	2282	2573	845
145°	1267	1355	1598	1942	2090	793
155°	1429	1476	1585	1743	1798	658
165°	1547	1567	1593	1655	1667	436
175°	1603	1606	1595	1618	1613	152
180°	1603	1603	1603	1603	1603	

TEST NUMBER: P563581

CATALOG NUMBER: SQ4-PP3-100U-050D-940-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1975.2	1975.2	1975.2	1975.2	1975.2
2.5°	1987.7	1971.4	1975.2	1972.3	1964.2
5°	1982.2	1963.5	1970.0	1963.1	1963.1
7.5°	1968.7	1948.3	1954.8	1947.9	1947.5
10°	1956.2	1935.9	1942.3	1935.4	1933.7
12.5°	1938.2	1917.9	1925.7	1917.4	1917.1
15°	1906.0	1887.4	1895.6	1888.6	1885.2
17.5°	1869.6	1849.3	1859.2	1849.5	1848.2
20°	1841.9	1821.6	1831.5	1817.7	1817.7
22.5°	1808.7	1788.4	1799.7	1781.7	1781.7
25°	1755.4	1735.1	1743.3	1727.6	1725.9
27.5°	1692.0	1672.0	1680.6	1662.9	1662.6
30°	1646.3	1627.7	1637.7	1618.6	1616.9
32.5°	1596.5	1579.2	1586.4	1567.3	1565.6
35°	1516.5	1501.2	1506.1	1488.7	1487.1
37.5°	1432.3	1416.8	1422.3	1407.4	1406.7
40°	1372.8	1362.6	1364.1	1351.9	1348.6
42.5°	1317.4	1305.9	1307.4	1295.2	1294.5
45°	1232.6	1224.1	1223.9	1211.8	1211.8
47.5°	1142.6	1136.1	1134.2	1124.2	1123.9
50°	1080.2	1075.2	1073.3	1064.6	1062.9
52.5°	1015.1	1012.8	1006.8	999.6	999.2
55°	914.0	910.7	901.9	896.7	895.0
57.5°	804.3	797.5	787.7	780.1	781.4
60°	725.3	718.6	704.6	701.1	701.1
62.5°	649.2	641.1	627.0	622.2	624.9
65°	540.1	530.0	517.6	514.2	515.9
67.5°	441.1	432.0	418.6	418.6	417.2
70°	377.4	372.3	361.8	361.8	361.8
72.5°	320.6	318.2	310.6	310.5	309.2
75°	245.8	245.8	242.4	240.6	238.9
77.5°	184.2	184.9	183.2	181.4	178.3
80°	145.4	148.8	147.1	145.4	143.7
82.5°	109.4	112.8	112.5	109.4	109.1
85°	57.1	62.2	62.3	62.3	62.3
87.5°	16.3	22.7	26.3	26.8	28.7
90°	5.1	10.1	20.5	23.1	25.6
92.5°	46.2	191.6	342.7	125.1	97.5
95°	110.3	406.2	1362.0	559.8	364.2
97.5°	182.6	455.0	2017.6	1553.3	1125.0
100°	236.0	484.3	2259.7	2275.7	1849.3
102.5°	287.3	517.5	2306.9	2811.8	2407.5
105°	369.4	570.0	2280.2	3481.2	3278.0
107.5°	456.6	635.1	2153.0	3804.0	3878.2
110°	518.1	678.6	2054.5	3873.4	4114.2



TEST NUMBER: P563581

CATALOG NUMBER: SQ4-PP3-100U-050D-940-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	573.5	728.0	1962.2	3818.6	4173.7
115°	661.8	799.7	1836.5	3635.6	4134.7
117.5°	738.7	876.1	1753.9	3378.1	3945.9
120°	790.0	925.4	1721.1	3203.8	3775.6
122.5°	839.3	968.7	1694.4	3041.0	3582.7
125°	908.0	1033.4	1664.7	2817.2	3306.2
127.5°	966.5	1091.9	1647.2	2627.9	3049.7
130°	1005.5	1130.9	1639.0	2512.1	2895.8
132.5°	1042.4	1161.8	1630.8	2414.9	2762.5
135°	1092.7	1210.5	1618.5	2281.7	2572.7
137.5°	1149.1	1256.4	1612.3	2170.0	2418.2
140°	1179.9	1285.2	1608.2	2095.4	2313.6
142.5°	1214.8	1312.1	1604.1	2029.1	2221.3
145°	1267.1	1354.9	1598.0	1942.5	2090.4
147.5°	1317.4	1394.1	1592.3	1869.4	1984.2
150°	1354.3	1417.0	1590.3	1825.8	1918.6
152.5°	1383.0	1441.7	1588.2	1788.5	1865.2
155°	1428.7	1476.3	1585.1	1742.9	1798.0
157.5°	1470.7	1507.4	1585.7	1709.6	1747.2
160°	1495.4	1528.0	1587.7	1690.9	1718.5
162.5°	1515.9	1544.5	1589.8	1674.4	1695.9
165°	1546.7	1566.7	1592.8	1654.7	1667.2
167.5°	1570.3	1582.3	1595.4	1642.7	1646.7
170°	1582.6	1592.6	1595.4	1636.4	1636.4
172.5°	1592.8	1598.9	1595.4	1628.2	1626.2
175°	1603.1	1605.6	1595.4	1618.4	1613.4
177.5°	1607.2	1605.2	1594.9	1609.2	1605.1
180°	1603.1	1603.1	1603.1	1603.1	1603.1

(END OF REPORT)