

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563725

Luminaire Tested: **SQ4-PP3-125U-100D-940-1D-UNV-STD-W-12**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563725
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-125U-100D-940-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 22870.6 lumens
Efficiency: N/A
Efficacy: 113.7 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 201.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563725
CATALOG NUMBER: SQ4-PP3-125U-100D-940-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P563725

CATALOG NUMBER: SQ4-PP3-125U-100D-940-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	43
1	96	92	88	85	88	85	81	78	70	68	66	57	55	54	44	43	43	37
2	88	81	75	70	80	74	69	65	62	58	55	50	47	45	39	38	36	31
3	80	71	64	58	73	65	59	54	54	50	46	44	41	38	35	33	31	26
4	73	63	55	49	67	58	51	46	48	43	39	39	36	33	31	29	27	23
5	67	56	48	42	61	52	45	39	43	38	34	35	32	28	28	25	23	20
6	62	50	42	37	57	46	39	34	39	34	30	32	28	25	26	23	20	17
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	23	20	18	15
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	21	18	16	14
9	49	37	30	25	45	35	28	24	29	24	21	24	20	18	20	17	15	12
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11896	11896	11896
5°	11984	11910	11869
10°	11963	11879	11826
15°	11884	11820	11755
20°	11806	11739	11650
25°	11665	11584	11469
30°	11449	11389	11244
35°	11150	11074	10933
40°	10793	10725	10603
45°	10498	10425	10321
50°	10122	10056	9959
55°	9598	9471	9398
60°	8737	8487	8445
65°	7697	7377	7352
70°	6646	6371	6371
75°	5720	5639	5559
80°	5044	5104	4984
85°	3949	4305	4305



TEST NUMBER: P563725

CATALOG NUMBER: SQ4-PP3-125U-100D-940-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	365.8	1.6
10°-20°	1044.4	4.6
20°-30°	1564.4	6.8
30°-40°	1834.9	8.0
40°-50°	1840.7	8.0
50°-60°	1570.2	6.9
60°-70°	1024.1	4.5
70°-80°	513.8	2.2
80°-90°	146.9	0.6
90°-100°	939.5	4.1
100°-110°	2530.9	11.1
110°-120°	2656.1	11.6
120°-130°	2155.4	9.4
130°-140°	1690.4	7.4
140°-150°	1297.8	5.7
150°-160°	933.1	4.1
160°-170°	570.1	2.5
170°-180°	192.2	0.8
0°-30°	2974.6	13.0
0°-40°	4809.5	21.0
0°-60°	8220.4	35.9
0°-90°	9905.2	43.3
90°-120°	6126.5	26.8
90°-150°	11270.0	49.3
90°-180°	12965.0	56.7
0°-180°	22870.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3868	3868	3868	3868	3868	
5°	3882	3845	3858	3844	3844	369
15°	3733	3696	3712	3698	3692	1053
25°	3438	3398	3414	3383	3380	1581
35°	2970	2940	2950	2916	2912	1855
45°	2414	2397	2397	2373	2373	1859
55°	1790	1783	1766	1756	1753	1591
65°	1058	1038	1014	1007	1010	1056
75°	481	481	475	471	468	522
85°	112	122	122	122	122	132
90°	5	15	31	33	33	14
95°	143	511	1540	788	545	150
105°	468	728	2799	4188	3930	492
115°	826	1012	2331	4504	5094	813
125°	1128	1296	2093	3537	4163	1007
135°	1359	1516	2034	2854	3231	1049
145°	1571	1694	2008	2440	2620	985
155°	1783	1848	1990	2189	2259	821
165°	1934	1957	1998	2078	2088	545
175°	2011	2008	2001	2029	2024	191
180°	2008	2008	2008	2008	2008	

TEST NUMBER: P563725

CATALOG NUMBER: SQ4-PP3-125U-100D-940-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3868.2	3868.2	3868.2	3868.2	3868.2
2.5°	3892.6	3860.8	3868.2	3862.4	3846.5
5°	3881.8	3845.3	3858.0	3844.5	3844.5
7.5°	3855.3	3815.5	3828.2	3814.6	3814.0
10°	3830.9	3791.1	3803.8	3790.2	3786.8
12.5°	3795.7	3755.9	3771.2	3755.0	3754.3
15°	3732.6	3696.1	3712.3	3698.5	3691.9
17.5°	3661.4	3621.6	3641.1	3622.0	3619.4
20°	3607.2	3567.4	3586.8	3559.7	3559.7
22.5°	3542.1	3502.3	3524.4	3489.2	3489.2
25°	3437.7	3397.9	3413.9	3383.3	3380.0
27.5°	3313.6	3274.5	3291.2	3256.6	3255.9
30°	3224.1	3187.6	3207.1	3169.8	3166.4
32.5°	3126.4	3092.6	3106.8	3069.4	3066.1
35°	2969.8	2940.0	2949.5	2915.5	2912.2
37.5°	2805.0	2774.5	2785.4	2756.2	2754.9
40°	2688.4	2668.5	2671.5	2647.6	2641.0
42.5°	2579.9	2557.4	2560.3	2536.5	2535.2
45°	2413.8	2397.2	2396.9	2373.1	2373.1
47.5°	2237.5	2224.9	2221.3	2201.6	2200.9
50°	2115.5	2105.5	2101.9	2084.9	2081.6
52.5°	1988.0	1983.4	1971.7	1957.5	1956.8
55°	1790.0	1783.4	1766.3	1756.0	1752.7
57.5°	1575.1	1561.8	1542.5	1527.7	1530.3
60°	1420.5	1407.2	1379.8	1373.0	1373.0
62.5°	1271.3	1255.4	1227.9	1218.6	1223.9
65°	1057.7	1037.9	1013.7	1007.0	1010.3
67.5°	863.8	845.9	819.7	819.7	817.0
70°	739.1	729.1	708.5	708.5	708.5
72.5°	627.9	623.2	608.2	608.1	605.5
75°	481.4	481.4	474.6	471.2	467.8
77.5°	360.7	362.0	358.7	355.2	349.2
80°	284.8	291.4	288.2	284.7	281.4
82.5°	214.3	220.9	220.4	214.2	213.6
85°	111.9	121.8	122.0	122.0	122.0
87.5°	30.9	43.5	49.5	50.1	52.8
90°	5.1	15.1	30.7	33.3	33.3
92.5°	62.4	220.5	436.0	209.9	145.8
95°	143.3	511.0	1540.2	787.6	545.0
97.5°	228.7	585.0	2415.7	2018.1	1521.8
100°	294.2	614.4	2694.1	2818.8	2338.5
102.5°	357.7	655.9	2786.2	3418.4	3024.1
105°	468.2	728.4	2799.0	4187.5	3929.8
107.5°	572.6	804.7	2679.8	4582.7	4649.3
110°	642.2	862.3	2571.3	4705.4	4948.1

TEST NUMBER: P563725

CATALOG NUMBER: SQ4-PP3-125U-100D-940-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	715.9	920.0	2466.9	4678.3	5077.1
115°	826.4	1011.5	2330.8	4503.6	5093.9
117.5°	927.2	1100.8	2225.4	4224.7	4882.1
120°	992.7	1160.3	2172.2	4024.5	4699.9
122.5°	1050.0	1215.6	2133.3	3819.8	4493.2
125°	1128.3	1295.9	2092.8	3537.2	4162.7
127.5°	1203.5	1368.6	2067.3	3288.1	3846.4
130°	1248.5	1413.6	2057.0	3145.3	3635.6
132.5°	1293.6	1456.7	2046.8	3019.5	3469.8
135°	1358.6	1516.2	2034.0	2853.6	3231.4
137.5°	1420.5	1571.6	2027.3	2712.9	3023.1
140°	1463.5	1608.5	2021.2	2626.3	2906.4
142.5°	1508.5	1643.6	2017.1	2545.4	2781.6
145°	1570.9	1693.5	2008.4	2439.8	2619.9
147.5°	1638.5	1745.0	1999.7	2350.9	2492.5
150°	1683.5	1776.0	1995.6	2295.1	2412.6
152.5°	1724.4	1805.0	1993.6	2249.5	2345.1
155°	1783.3	1848.3	1990.5	2189.1	2259.1
157.5°	1834.9	1885.5	1991.0	2146.6	2193.6
160°	1867.7	1910.2	1993.1	2121.8	2156.8
162.5°	1896.3	1930.9	1995.1	2101.1	2126.1
165°	1934.2	1956.7	1998.2	2077.7	2087.7
167.5°	1964.9	1977.9	2000.7	2059.7	2063.7
170°	1985.4	1990.4	2000.7	2049.3	2049.3
172.5°	1997.7	1998.7	2002.8	2039.1	2039.1
175°	2011.0	2008.5	2000.7	2028.8	2023.8
177.5°	2016.6	2012.6	2002.3	2018.6	2014.5
180°	2008.4	2008.4	2008.4	2008.4	2008.4

(END OF REPORT)