

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563845

Luminaire Tested: **SQ4-PP3-150U-125D-940-1D-UNV-STD-W-12**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563845
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-25, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-150U-125D-940-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 28262.1 lumens
Efficiency: N/A
Efficacy: 110.3 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 256.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563845
CATALOG NUMBER: SQ4-PP3-150U-125D-940-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P563845

CATALOG NUMBER: SQ4-PP3-150U-125D-940-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	45
1	97	93	89	85	89	85	82	79	71	68	66	58	56	55	46	45	44	38
2	88	81	75	70	81	74	69	65	62	58	55	51	48	46	40	39	37	32
3	81	71	64	58	74	66	59	54	55	50	47	45	42	39	36	34	32	27
4	74	63	55	49	67	58	51	46	49	44	40	40	36	33	32	29	27	24
5	68	56	48	42	62	52	45	40	44	38	34	36	32	29	29	26	24	20
6	62	50	42	37	57	47	40	34	39	34	30	33	28	25	26	23	21	18
7	58	45	38	32	53	42	35	30	36	30	26	30	25	22	24	21	19	16
8	53	41	34	28	49	38	31	27	32	27	23	27	23	20	22	19	17	14
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	20	17	15	13
10	46	34	27	23	43	32	26	21	27	22	19	23	19	16	19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15181	15181	15181
5°	15293	15199	15146
10°	15267	15159	15091
15°	15166	15083	15001
20°	15065	14980	14867
25°	14886	14783	14637
30°	14611	14534	14350
35°	14229	14131	13952
40°	13773	13687	13530
45°	13398	13303	13171
50°	12916	12833	12709
55°	12248	12085	11993
60°	11150	10830	10777
65°	9823	9414	9382
70°	8480	8130	8130
75°	7299	7197	7094
80°	6436	6512	6360
85°	5039	5494	5494



TEST NUMBER: P563845

CATALOG NUMBER: SQ4-PP3-150U-125D-940-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	466.8	1.7
10°-20°	1332.8	4.7
20°-30°	1996.4	7.1
30°-40°	2341.6	8.3
40°-50°	2348.9	8.3
50°-60°	2003.8	7.1
60°-70°	1306.8	4.6
70°-80°	655.6	2.3
80°-90°	186.5	0.7
90°-100°	1126.1	4.0
100°-110°	3044.8	10.8
110°-120°	3201.2	11.3
120°-130°	2600.2	9.2
130°-140°	2039.6	7.2
140°-150°	1565.4	5.5
150°-160°	1125.8	4.0
160°-170°	687.8	2.4
170°-180°	231.9	0.8
0°-30°	3796.0	13.4
0°-40°	6137.6	21.7
0°-60°	10490.4	37.1
0°-90°	12639.4	44.7
90°-120°	7372.0	26.1
90°-150°	13577.3	48.0
90°-180°	15623.0	55.3
0°-180°	28262.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4936	4936	4936	4936	4936	
5°	4954	4907	4923	4906	4906	470
15°	4763	4717	4737	4720	4711	1344
25°	4387	4336	4357	4318	4313	2017
35°	3790	3752	3764	3721	3716	2367
45°	3080	3059	3059	3028	3028	2372
55°	2284	2276	2254	2241	2237	2030
65°	1350	1324	1294	1285	1289	1347
75°	614	614	606	601	597	666
85°	143	156	156	156	156	168
90°	5	15	34	36	34	17
95°	175	613	1873	969	576	183
105°	566	875	3378	4982	4778	596
115°	996	1218	2801	5423	6122	984
125°	1364	1563	2525	4261	5005	1216
135°	1635	1829	2457	3440	3894	1264
145°	1902	2044	2423	2945	3169	1190
155°	2147	2231	2402	2642	2728	990
165°	2337	2360	2413	2507	2520	658
175°	2426	2423	2415	2446	2441	230
180°	2423	2423	2423	2423	2423	

TEST NUMBER: P563845

CATALOG NUMBER: SQ4-PP3-150U-125D-940-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4936.3	4936.3	4936.3	4936.3	4936.3
2.5°	4967.5	4926.9	4936.3	4929.0	4908.7
5°	4953.7	4907.1	4923.4	4906.1	4906.1
7.5°	4919.9	4869.1	4885.3	4868.0	4867.1
10°	4888.8	4838.0	4854.1	4836.7	4832.5
12.5°	4843.8	4793.0	4812.6	4791.8	4791.0
15°	4763.3	4716.8	4737.3	4719.8	4711.4
17.5°	4672.4	4621.7	4646.5	4622.2	4618.8
20°	4603.2	4552.5	4577.3	4542.7	4542.7
22.5°	4520.2	4469.4	4497.7	4452.7	4452.7
25°	4386.9	4336.1	4356.6	4317.6	4313.4
27.5°	4228.6	4178.6	4200.0	4155.9	4155.0
30°	4114.3	4067.8	4092.7	4045.0	4040.8
32.5°	3989.7	3946.6	3964.7	3917.0	3912.7
35°	3789.9	3751.8	3763.9	3720.6	3716.3
37.5°	3579.6	3540.7	3554.5	3517.3	3515.6
40°	3430.8	3405.4	3409.2	3378.7	3370.2
42.5°	3292.3	3263.6	3267.2	3236.9	3235.2
45°	3080.4	3059.2	3058.7	3028.4	3028.4
47.5°	2855.4	2839.3	2834.6	2809.5	2808.7
50°	2699.6	2686.9	2682.3	2660.6	2656.4
52.5°	2537.0	2531.0	2516.2	2498.0	2497.2
55°	2284.3	2275.8	2254.0	2240.9	2236.7
57.5°	2010.0	1993.1	1968.5	1949.5	1952.9
60°	1812.7	1795.8	1760.8	1752.2	1752.2
62.5°	1622.4	1602.1	1567.0	1555.0	1561.8
65°	1349.8	1324.4	1293.6	1285.0	1289.2
67.5°	1102.4	1079.5	1046.1	1046.0	1042.6
70°	943.1	930.5	904.2	904.2	904.2
72.5°	801.2	795.3	776.1	776.1	772.7
75°	614.3	614.3	605.7	601.3	597.0
77.5°	460.3	462.0	457.7	453.2	445.6
80°	363.4	371.9	367.7	363.3	359.1
82.5°	273.4	281.9	281.2	273.4	272.6
85°	142.8	155.5	155.7	155.7	155.7
87.5°	39.1	54.7	62.2	62.7	65.6
90°	5.2	15.4	33.9	36.5	33.9
92.5°	74.1	269.9	532.6	231.2	167.5
95°	174.8	613.4	1872.8	969.2	576.4
97.5°	280.7	703.5	2919.2	2415.8	1774.2
100°	359.9	739.9	3244.7	3383.9	2736.1
102.5°	433.0	790.5	3359.5	4117.9	3633.4
105°	566.0	874.6	3377.8	4982.5	4778.4
107.5°	689.1	970.7	3230.1	5521.8	5589.6
110°	785.1	1040.1	3098.7	5666.6	5954.8



TEST NUMBER: P563845

CATALOG NUMBER: SQ4-PP3-150U-125D-940-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	870.7	1109.4	2977.7	5637.7	6121.7
115°	996.4	1218.3	2801.3	5422.9	6121.7
117.5°	1119.5	1327.6	2685.0	5094.8	5887.0
120°	1194.6	1398.6	2616.1	4859.4	5667.9
122.5°	1265.6	1465.5	2574.4	4607.1	5421.6
125°	1364.1	1563.1	2524.8	4260.7	5005.4
127.5°	1454.9	1650.3	2495.6	3978.0	4632.9
130°	1505.0	1706.5	2483.1	3803.3	4395.0
132.5°	1557.2	1756.6	2470.6	3645.8	4190.5
135°	1635.4	1829.2	2457.0	3440.2	3894.2
137.5°	1714.2	1897.3	2445.6	3273.5	3643.3
140°	1768.4	1939.3	2441.4	3166.1	3495.1
142.5°	1820.6	1981.3	2433.0	3069.2	3357.4
145°	1901.5	2044.3	2423.1	2944.7	3169.1
147.5°	1975.0	2101.5	2411.6	2831.9	3004.3
150°	2029.3	2141.5	2407.5	2770.6	2908.3
152.5°	2079.3	2177.3	2405.4	2713.7	2826.9
155°	2146.6	2230.8	2402.3	2641.6	2728.3
157.5°	2216.5	2275.2	2402.8	2591.4	2648.5
160°	2256.2	2304.6	2404.9	2559.7	2600.5
162.5°	2287.5	2327.8	2407.0	2534.4	2565.0
165°	2337.0	2360.0	2412.7	2506.9	2519.6
167.5°	2371.0	2386.8	2413.2	2483.3	2489.4
170°	2391.8	2399.5	2415.3	2472.7	2472.7
172.5°	2408.5	2410.0	2415.3	2460.1	2458.1
175°	2425.7	2423.2	2415.3	2446.5	2441.4
177.5°	2431.5	2425.3	2414.8	2435.5	2429.4
180°	2423.1	2423.1	2423.1	2423.1	2423.1

(END OF REPORT)