

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562720

Luminaire Tested: **SQ4-PC3-075U-050D-940-1D-UNV-STD-W-8**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P562720  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-22, G2-2106-289-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PC3-075U-050D-940-1D-UNV-STD-W-8  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.  
DOWNLIGHT 500 LUMENS PER FOOT  
UPLIGHT 750 LUMENS PER FOOT  
Light Source: 4000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 8580.7 lumens  
Efficiency: N/A  
Efficacy: 119.5 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37  
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 71.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P562720  
CATALOG NUMBER: SQ4-PC3-075U-050D-940-1D-UNV-STD-W-8

### Luminous Intensity Polar Plot





TEST NUMBER: P562720

CATALOG NUMBER: SQ4-PC3-075U-050D-940-1D-UNV-STD-W-8

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	78	78	78	61	61	61	47	47	47	40
1	96	91	87	84	87	83	80	77	68	66	64	54	53	51	41	40	39	34
2	87	80	74	69	79	73	68	63	60	56	53	48	45	43	36	35	33	28
3	79	70	63	57	72	64	58	53	53	48	44	42	39	36	32	30	28	24
4	72	62	54	48	66	57	50	45	47	42	38	37	34	31	29	26	24	20
5	66	55	47	41	60	50	43	38	42	36	32	33	30	27	26	23	21	18
6	61	49	41	36	55	45	38	33	37	32	28	30	26	23	23	21	19	15
7	56	44	37	31	51	41	34	29	34	29	25	27	23	21	21	19	16	14
8	52	40	33	27	47	37	30	25	31	26	22	25	21	18	20	17	15	12
9	49	37	29	24	44	34	27	23	28	23	19	23	19	16	18	15	13	11
10	45	33	26	22	41	31	25	20	26	21	17	21	17	15	17	14	12	10

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	5751	5751	5751
5°	5794	5757	5736
10°	5780	5753	5737
15°	5750	5750	5745
20°	5712	5729	5729
25°	5659	5699	5682
30°	5589	5657	5633
35°	5507	5591	5552
40°	5416	5492	5436
45°	5317	5355	5272
50°	5178	5178	5095
55°	5014	4949	4874
60°	4772	4676	4601
65°	4410	4321	4284
70°	3862	3893	3876
75°	3107	3436	3456
80°	2208	2914	2943
85°	1344	2445	2445



TEST NUMBER: P562720

CATALOG NUMBER: SQ4-PC3-075U-050D-940-1D-UNV-STD-W-8

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	118.0	1.4
10°-20°	338.6	3.9
20°-30°	512.8	6.0
30°-40°	614.7	7.2
40°-50°	626.8	7.3
50°-60°	547.2	6.4
60°-70°	391.7	4.6
70°-80°	201.8	2.4
80°-90°	53.0	0.6
90°-100°	374.7	4.4
100°-110°	1031.0	12.0
110°-120°	1064.2	12.4
120°-130°	852.6	9.9
130°-140°	669.7	7.8
140°-150°	513.2	6.0
150°-160°	369.0	4.3
160°-170°	225.6	2.6
170°-180°	76.1	0.9
0°-30°	969.3	11.3
0°-40°	1584.1	18.5
0°-60°	2758.0	32.1
0°-90°	3404.5	39.7
90°-120°	2470.0	28.8
90°-150°	4505.5	52.5
90°-180°	5176.0	60.3
0°-180°	8580.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1247	1247	1247	1247	1247	
5°	1251	1239	1243	1240	1239	119
15°	1204	1194	1204	1204	1203	339
25°	1112	1104	1120	1116	1116	512
35°	978	976	993	986	986	611
45°	815	813	821	810	808	627
55°	623	616	615	606	606	556
65°	404	395	396	392	392	400
75°	174	182	193	194	194	188
85°	25	39	46	47	46	35
90°	2	7	12	15	15	5
95°	56	205	663	283	181	59
105°	184	283	1136	1730	1614	194
115°	326	397	911	1814	2059	322
125°	450	512	827	1398	1638	401
135°	543	602	803	1131	1280	419
145°	627	670	791	964	1038	393
155°	710	733	786	866	891	326
165°	768	777	790	822	827	216
175°	794	796	791	801	800	75
180°	794	794	794	794	794	

TEST NUMBER: P562720

CATALOG NUMBER: SQ4-PC3-075U-050D-940-1D-UNV-STD-W-8

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1246.7	1246.7	1246.7	1246.7	1246.7
2.5°	1254.1	1243.3	1246.7	1243.8	1239.3
5°	1251.3	1238.9	1243.3	1239.8	1238.6
7.5°	1242.3	1229.9	1235.6	1233.3	1232.2
10°	1234.0	1221.6	1228.2	1225.9	1224.8
12.5°	1222.9	1211.4	1219.0	1216.7	1216.5
15°	1204.0	1193.8	1204.0	1204.0	1202.9
17.5°	1180.2	1171.0	1181.8	1182.5	1181.8
20°	1163.6	1153.4	1167.1	1165.9	1167.1
22.5°	1143.3	1134.9	1149.5	1146.5	1147.7
25°	1111.7	1103.8	1119.7	1116.3	1116.3
27.5°	1074.3	1068.6	1086.0	1082.3	1082.3
30°	1049.3	1043.7	1062.0	1057.4	1057.4
32.5°	1021.6	1017.8	1035.2	1029.7	1029.7
35°	977.8	975.5	992.8	985.8	985.8
37.5°	932.5	930.5	946.1	937.7	935.0
40°	899.3	898.1	912.0	902.7	902.7
42.5°	866.0	864.9	876.9	865.8	865.8
45°	815.0	812.7	820.8	810.3	808.1
47.5°	759.3	757.1	762.1	750.8	749.6
50°	721.5	719.2	721.5	711.1	709.9
52.5°	682.7	678.6	679.0	668.6	668.4
55°	623.4	615.5	615.3	606.0	606.0
57.5°	560.6	550.2	551.1	543.2	542.1
60°	517.2	505.9	506.8	499.8	498.7
62.5°	474.7	461.6	464.3	456.4	456.2
65°	404.0	395.0	395.9	392.5	392.5
67.5°	336.2	327.8	333.8	331.1	330.8
70°	286.3	280.6	288.6	288.6	287.4
72.5°	240.1	239.9	249.8	249.8	250.5
75°	174.3	182.2	192.8	193.9	193.9
77.5°	116.4	130.4	142.0	142.4	142.2
80°	83.1	98.9	109.7	111.9	110.8
82.5°	56.3	73.0	82.0	84.2	83.1
85°	25.4	38.9	46.2	47.3	46.2
87.5°	7.7	16.8	20.8	21.5	19.7
90°	1.7	6.6	11.8	15.2	15.2
92.5°	23.3	99.7	172.8	66.3	54.4
95°	55.8	204.6	662.7	283.4	180.9
97.5°	90.9	226.8	1011.3	779.2	549.8
100°	116.6	240.6	1120.8	1131.3	923.0
102.5°	141.0	257.0	1149.2	1403.5	1212.4
105°	184.3	283.4	1136.0	1730.2	1614.4
107.5°	225.5	316.1	1071.5	1890.1	1924.5
110°	255.3	337.9	1022.8	1929.9	2048.9



TEST NUMBER: P562720

CATALOG NUMBER: SQ4-PC3-075U-050D-940-1D-UNV-STD-W-8

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	282.3	362.3	974.1	1904.3	2085.4
115°	326.3	397.3	911.2	1814.4	2059.1
117.5°	368.2	433.7	871.3	1688.4	1965.1
120°	393.9	456.7	853.7	1593.9	1879.9
122.5°	416.9	479.7	841.5	1511.1	1782.5
125°	449.7	512.5	826.7	1398.4	1638.1
127.5°	480.8	540.6	816.9	1304.4	1514.7
130°	497.0	558.2	811.4	1248.6	1440.3
132.5°	515.9	577.1	807.4	1199.5	1372.7
135°	542.7	602.2	803.0	1131.0	1279.7
137.5°	567.7	622.9	799.3	1075.6	1198.2
140°	586.6	637.9	797.9	1038.8	1149.6
142.5°	602.8	650.1	795.2	1006.0	1100.9
145°	627.2	670.2	791.2	963.6	1038.0
147.5°	653.2	690.2	789.1	926.1	985.6
150°	669.4	702.5	787.8	905.5	951.8
152.5°	684.3	714.7	786.4	887.7	926.1
155°	710.0	733.2	786.1	866.1	890.9
157.5°	728.6	747.5	786.1	848.4	865.5
160°	742.1	757.0	786.1	838.8	852.0
162.5°	753.0	765.2	787.4	830.6	841.2
165°	767.5	777.4	789.5	821.7	826.7
167.5°	777.6	785.2	791.2	814.2	815.5
170°	784.4	789.4	791.2	811.4	811.4
172.5°	789.8	792.1	791.2	807.4	806.0
175°	794.5	796.2	791.2	801.3	799.6
177.5°	795.9	795.9	790.5	798.5	795.9
180°	794.5	794.5	794.5	794.5	794.5

(END OF REPORT)