

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562912

Luminaire Tested: **SQ4-PC3-100U-050D-940-1D-UNV-STD-W-8**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562912
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-23, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-100U-050D-940-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10348.8 lumens
Efficiency: N/A
Efficacy: 122.2 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 84.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562912
CATALOG NUMBER: SQ4-PC3-100U-050D-940-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P562912

CATALOG NUMBER: SQ4-PC3-100U-050D-940-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40	33
1	94	90	86	83	85	81	78	75	65	63	61	50	48	47	36	35	34	28
2	86	78	72	67	77	71	66	62	57	53	50	44	41	39	31	30	29	23
3	78	69	62	56	70	62	56	51	50	46	42	38	36	33	28	26	24	20
4	71	61	53	47	64	55	48	43	44	39	36	34	31	28	25	23	21	17
5	65	54	46	40	59	49	42	37	39	34	31	31	27	24	22	20	18	15
6	60	48	40	35	54	44	37	32	35	30	27	28	24	21	20	18	16	13
7	55	43	36	30	50	40	33	28	32	27	23	25	21	19	18	16	14	11
8	51	39	32	27	46	36	29	25	29	24	21	23	19	17	17	14	13	10
9	48	36	29	24	43	33	26	22	27	22	18	21	17	15	16	13	11	9
10	44	33	26	21	40	30	24	19	24	20	16	19	16	13	14	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5751	5751	5751
5°	5794	5757	5736
10°	5780	5753	5737
15°	5750	5750	5745
20°	5712	5729	5729
25°	5659	5699	5682
30°	5589	5657	5633
35°	5507	5591	5552
40°	5416	5492	5436
45°	5317	5355	5272
50°	5178	5178	5095
55°	5014	4949	4874
60°	4772	4676	4601
65°	4410	4321	4284
70°	3862	3893	3876
75°	3107	3436	3456
80°	2208	2914	2943
85°	1344	2445	2445



TEST NUMBER: P562912

CATALOG NUMBER: SQ4-PC3-100U-050D-940-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	118.0	1.1
10°-20°	338.6	3.3
20°-30°	512.8	5.0
30°-40°	614.7	5.9
40°-50°	626.8	6.1
50°-60°	547.2	5.3
60°-70°	391.7	3.8
70°-80°	201.8	1.9
80°-90°	53.2	0.5
90°-100°	500.5	4.8
100°-110°	1381.7	13.4
110°-120°	1425.0	13.8
120°-130°	1145.1	11.1
130°-140°	899.9	8.7
140°-150°	690.2	6.7
150°-160°	496.0	4.8
160°-170°	303.4	2.9
170°-180°	102.3	1.0
0°-30°	969.3	9.4
0°-40°	1584.1	15.3
0°-60°	2758.0	26.7
0°-90°	3404.7	32.9
90°-120°	3307.2	32.0
90°-150°	6042.4	58.4
90°-180°	6944.0	67.1
0°-180°	10348.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1247	1247	1247	1247	1247	
5°	1251	1239	1243	1240	1239	119
15°	1204	1194	1204	1204	1203	339
25°	1112	1104	1120	1116	1116	512
35°	978	976	993	986	986	611
45°	815	813	821	810	808	627
55°	623	616	615	606	606	556
65°	404	395	396	392	392	400
75°	174	182	193	194	194	188
85°	25	39	46	47	46	35
90°	3	7	14	15	17	6
95°	74	271	908	373	243	79
105°	246	380	1520	2321	2185	262
115°	441	533	1224	2424	2756	434
125°	605	689	1110	1878	2204	539
135°	728	807	1079	1521	1715	564
145°	845	903	1065	1295	1394	529
155°	952	984	1057	1162	1199	439
165°	1031	1044	1062	1103	1112	291
175°	1069	1070	1064	1079	1076	102
180°	1069	1069	1069	1069	1069	

TEST NUMBER: P562912

CATALOG NUMBER: SQ4-PC3-100U-050D-940-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1246.7	1246.7	1246.7	1246.7	1246.7
2.5°	1254.1	1243.3	1246.7	1243.8	1239.3
5°	1251.3	1238.9	1243.3	1239.8	1238.6
7.5°	1242.3	1229.9	1235.6	1233.3	1232.2
10°	1234.0	1221.6	1228.2	1225.9	1224.8
12.5°	1222.9	1211.4	1219.0	1216.7	1216.5
15°	1204.0	1193.8	1204.0	1204.0	1202.9
17.5°	1180.2	1171.0	1181.8	1182.5	1181.8
20°	1163.6	1153.4	1167.1	1165.9	1167.1
22.5°	1143.3	1134.9	1149.5	1146.5	1147.7
25°	1111.7	1103.8	1119.7	1116.3	1116.3
27.5°	1074.3	1068.6	1086.0	1082.3	1082.3
30°	1049.3	1043.7	1062.0	1057.4	1057.4
32.5°	1021.6	1017.8	1035.2	1029.7	1029.7
35°	977.8	975.5	992.8	985.8	985.8
37.5°	932.5	930.5	946.1	937.7	935.0
40°	899.3	898.1	912.0	902.7	902.7
42.5°	866.0	864.9	876.9	865.8	865.8
45°	815.0	812.7	820.8	810.3	808.1
47.5°	759.3	757.1	762.1	750.8	749.6
50°	721.5	719.2	721.5	711.1	709.9
52.5°	682.7	678.6	679.0	668.6	668.4
55°	623.4	615.5	615.3	606.0	606.0
57.5°	560.6	550.2	551.1	543.2	542.1
60°	517.2	505.9	506.8	499.8	498.7
62.5°	474.7	461.6	464.3	456.4	456.2
65°	404.0	395.0	395.9	392.5	392.5
67.5°	336.2	327.8	333.8	331.1	330.8
70°	286.3	280.6	288.6	288.6	287.4
72.5°	240.1	239.9	249.8	249.8	250.5
75°	174.3	182.2	192.8	193.9	193.9
77.5°	116.4	130.4	142.0	142.4	142.2
80°	83.1	98.9	109.7	111.9	110.8
82.5°	56.3	73.0	82.0	84.2	83.1
85°	25.4	38.9	46.2	47.3	46.2
87.5°	8.1	16.9	21.2	21.5	20.0
90°	3.4	6.8	13.7	15.4	17.1
92.5°	30.8	127.8	228.5	83.4	65.0
95°	73.5	270.8	908.0	373.2	242.8
97.5°	121.7	303.3	1345.1	1035.6	750.0
100°	157.3	322.8	1506.5	1517.1	1232.9
102.5°	191.5	345.0	1537.9	1874.5	1605.0
105°	246.2	380.0	1520.2	2320.8	2185.3
107.5°	304.4	423.4	1435.3	2536.0	2585.5
110°	345.4	452.4	1369.7	2582.3	2742.8



TEST NUMBER: P562912

CATALOG NUMBER: SQ4-PC3-100U-050D-940-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	382.3	485.3	1308.1	2545.7	2782.5
115°	441.2	533.1	1224.3	2423.8	2756.5
117.5°	492.5	584.1	1169.3	2252.1	2630.6
120°	526.7	617.0	1147.4	2135.9	2517.1
122.5°	559.5	645.8	1129.6	2027.3	2388.5
125°	605.3	688.9	1109.8	1878.1	2204.2
127.5°	644.3	727.9	1098.1	1751.9	2033.2
130°	670.3	753.9	1092.7	1674.7	1930.6
132.5°	694.9	774.5	1087.2	1609.9	1841.6
135°	728.4	807.0	1079.0	1521.2	1715.1
137.5°	766.1	837.6	1074.9	1446.6	1612.2
140°	786.6	856.8	1072.2	1396.9	1542.4
142.5°	809.8	874.7	1069.4	1352.8	1480.8
145°	844.7	903.2	1065.3	1295.0	1393.6
147.5°	878.2	929.4	1061.5	1246.3	1322.8
150°	902.9	944.7	1060.2	1217.2	1279.1
152.5°	922.0	961.1	1058.8	1192.3	1243.5
155°	952.5	984.2	1056.8	1161.9	1198.7
157.5°	980.5	1004.9	1057.1	1139.8	1164.8
160°	996.9	1018.6	1058.5	1127.3	1145.7
162.5°	1010.6	1029.7	1059.8	1116.3	1130.6
165°	1031.1	1044.5	1061.9	1103.1	1111.5
167.5°	1046.8	1054.9	1063.6	1095.1	1097.8
170°	1055.1	1061.7	1063.6	1091.0	1091.0
172.5°	1061.9	1065.9	1063.6	1085.5	1084.1
175°	1068.7	1070.4	1063.6	1078.9	1075.6
177.5°	1071.5	1070.1	1063.3	1072.8	1070.1
180°	1068.7	1068.7	1068.7	1068.7	1068.7

(END OF REPORT)