

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563056

Luminaire Tested: **SQ4-PC3-125U-100D-940-1D-UNV-STD-W-8**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563056
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-125U-100D-940-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 15310.1 lumens
Efficiency: N/A
Efficacy: 114.9 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 133.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563056
CATALOG NUMBER: SQ4-PC3-125U-100D-940-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P563056

CATALOG NUMBER: SQ4-PC3-125U-100D-940-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	44
1	96	92	88	85	88	84	81	78	70	68	66	57	55	54	44	43	42	37
2	88	80	74	69	80	74	69	64	61	58	54	50	47	45	39	37	36	31
3	80	71	63	58	73	65	59	54	54	49	46	44	41	38	35	32	30	26
4	73	62	55	49	67	57	51	45	48	43	39	39	35	32	31	28	26	22
5	67	56	48	42	61	51	44	39	43	37	33	35	31	28	28	25	23	19
6	62	50	42	36	56	46	39	34	39	33	29	32	28	24	25	22	20	17
7	57	45	37	31	52	41	34	29	35	29	25	29	25	22	23	20	18	15
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	21	18	16	13
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	12
10	46	34	27	22	42	31	25	21	27	22	18	22	18	15	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11263	11263	11263
5°	11348	11274	11233
10°	11320	11267	11236
15°	11261	11261	11250
20°	11187	11220	11220
25°	11081	11161	11127
30°	10946	11079	11031
35°	10783	10949	10872
40°	10605	10755	10646
45°	10412	10486	10324
50°	10140	10140	9978
55°	9819	9691	9545
60°	9344	9156	9010
65°	8636	8464	8390
70°	7561	7623	7592
75°	6085	6728	6769
80°	4325	5706	5765
85°	2631	4785	4785



TEST NUMBER: P563056

CATALOG NUMBER: SQ4-PC3-125U-100D-940-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	231.1	1.5
10°-20°	663.1	4.3
20°-30°	1004.2	6.6
30°-40°	1203.9	7.9
40°-50°	1227.5	8.0
50°-60°	1071.5	7.0
60°-70°	767.1	5.0
70°-80°	395.1	2.6
80°-90°	103.1	0.7
90°-100°	626.4	4.1
100°-110°	1687.3	11.0
110°-120°	1770.7	11.6
120°-130°	1436.9	9.4
130°-140°	1126.9	7.4
140°-150°	865.2	5.7
150°-160°	622.1	4.1
160°-170°	380.0	2.5
170°-180°	128.2	0.8
0°-30°	1898.3	12.4
0°-40°	3102.2	20.3
0°-60°	5401.2	35.3
0°-90°	6666.5	43.5
90°-120°	4084.4	26.7
90°-150°	7513.4	49.1
90°-180°	8644.0	56.5
0°-180°	15310.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2442	2442	2442	2442	2442	
5°	2451	2426	2435	2428	2426	233
15°	2358	2338	2358	2358	2356	665
25°	2177	2162	2193	2186	2186	1002
35°	1915	1910	1944	1931	1931	1198
45°	1596	1592	1607	1587	1582	1229
55°	1221	1205	1205	1187	1187	1088
65°	791	774	775	769	769	783
75°	341	357	378	380	380	369
85°	50	76	90	93	90	68
90°	3	10	20	22	22	9
95°	96	341	1027	525	363	100
105°	312	486	1866	2792	2620	328
115°	551	674	1554	3002	3396	542
125°	752	864	1395	2358	2775	672
135°	906	1011	1356	1902	2154	699
145°	1047	1129	1339	1626	1747	657
155°	1189	1232	1327	1459	1506	547
165°	1290	1304	1332	1385	1392	364
175°	1341	1339	1334	1352	1349	127
180°	1339	1339	1339	1339	1339	



TEST NUMBER: P563056

CATALOG NUMBER: SQ4-PC3-125U-100D-940-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2441.5	2441.5	2441.5	2441.5	2441.5
2.5°	2456.0	2434.8	2441.5	2435.9	2427.0
5°	2450.6	2426.2	2434.7	2427.9	2425.7
7.5°	2432.9	2408.6	2419.8	2415.2	2413.0
10°	2416.6	2392.3	2405.3	2400.8	2398.6
12.5°	2394.9	2372.4	2387.3	2382.7	2382.3
15°	2357.9	2338.0	2357.9	2357.8	2355.6
17.5°	2311.3	2293.2	2314.5	2315.8	2314.5
20°	2278.7	2258.9	2285.5	2283.3	2285.5
22.5°	2239.0	2222.6	2251.2	2245.3	2247.6
25°	2177.0	2161.5	2192.8	2186.1	2186.1
27.5°	2103.8	2092.7	2126.8	2119.6	2119.6
30°	2054.9	2043.9	2079.8	2070.8	2070.8
32.5°	2000.7	1993.2	2027.4	2016.5	2016.5
35°	1914.8	1910.4	1944.2	1930.6	1930.6
37.5°	1826.2	1822.2	1852.8	1836.4	1831.1
40°	1761.1	1758.8	1785.9	1767.8	1767.8
42.5°	1695.9	1693.7	1717.2	1695.5	1695.5
45°	1596.0	1591.6	1607.3	1586.9	1582.5
47.5°	1487.1	1482.6	1492.5	1470.3	1468.1
50°	1412.9	1408.5	1412.9	1392.5	1390.3
52.5°	1337.0	1329.0	1329.7	1309.4	1308.9
55°	1220.8	1205.3	1204.9	1186.8	1186.8
57.5°	1097.8	1077.4	1079.2	1063.8	1061.6
60°	1012.8	990.7	992.4	978.8	976.6
62.5°	929.6	903.9	909.2	893.9	893.4
65°	791.2	773.5	775.4	768.6	768.6
67.5°	658.3	641.9	653.8	648.3	647.9
70°	560.6	549.6	565.2	565.1	562.9
72.5°	470.2	469.8	489.2	489.2	490.6
75°	341.4	356.8	377.5	379.8	379.8
77.5°	227.9	255.3	278.1	279.0	278.5
80°	162.8	193.7	214.8	219.2	217.0
82.5°	110.3	143.0	160.5	165.0	162.8
85°	49.7	76.3	90.4	92.6	90.4
87.5°	15.2	32.4	40.3	40.5	37.0
90°	3.4	10.1	20.5	22.2	22.2
92.5°	41.6	147.0	290.6	139.9	97.2
95°	95.5	340.7	1026.8	525.1	363.3
97.5°	152.5	390.0	1610.5	1345.4	1014.5
100°	196.2	409.6	1796.1	1879.2	1559.0
102.5°	238.5	437.2	1857.5	2278.9	2016.1
105°	312.1	485.6	1866.0	2791.7	2619.9
107.5°	381.7	536.5	1786.5	3055.2	3099.5
110°	428.1	574.9	1714.2	3137.0	3298.7

TEST NUMBER: P563056

CATALOG NUMBER: SQ4-PC3-125U-100D-940-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	477.2	613.3	1644.6	3118.9	3384.7
115°	550.9	674.3	1553.9	3002.4	3396.0
117.5°	618.1	733.9	1483.6	2816.4	3254.7
120°	661.8	773.5	1448.1	2683.0	3133.3
122.5°	700.0	810.4	1422.2	2546.5	2995.5
125°	752.2	863.9	1395.2	2358.2	2775.1
127.5°	802.3	912.4	1378.2	2192.0	2564.3
130°	832.4	942.4	1371.3	2096.9	2423.7
132.5°	862.4	971.1	1364.5	2013.0	2313.2
135°	905.7	1010.8	1356.0	1902.4	2154.2
137.5°	947.0	1047.7	1351.6	1808.6	2015.4
140°	975.6	1072.4	1347.5	1750.8	1937.6
142.5°	1005.7	1095.7	1344.7	1697.0	1854.4
145°	1047.3	1129.0	1338.9	1626.5	1746.6
147.5°	1092.3	1163.3	1333.1	1567.3	1661.6
150°	1122.3	1184.0	1330.4	1530.0	1608.4
152.5°	1149.6	1203.3	1329.0	1499.7	1563.4
155°	1188.8	1232.2	1327.0	1459.4	1506.1
157.5°	1223.3	1257.0	1327.3	1431.1	1462.4
160°	1245.1	1273.5	1328.7	1414.5	1437.9
162.5°	1264.2	1287.2	1330.1	1400.7	1417.4
165°	1289.5	1304.5	1332.1	1385.1	1391.8
167.5°	1309.9	1318.6	1333.8	1373.1	1375.8
170°	1323.6	1326.9	1333.8	1366.2	1366.2
172.5°	1331.8	1332.4	1335.2	1359.4	1359.4
175°	1340.6	1339.0	1333.8	1352.5	1349.2
177.5°	1344.4	1341.7	1334.8	1345.7	1343.0
180°	1338.9	1338.9	1338.9	1338.9	1338.9

(END OF REPORT)