

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563200

Luminaire Tested: **SQ4-PP3-025U-050D-940-1D-UNV-STD-W-8**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P563200  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-32, G2-2103-172-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PP3-025U-050D-940-1D-UNV-STD-W-8  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.  
DOWNLIGHT 500 LUMENS PER FOOT  
UPLIGHT 250 LUMENS PER FOOT  
Light Source: 4000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5058.6 lumens  
Efficiency: N/A  
Efficacy: 110.7 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33  
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 45.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P563200  
CATALOG NUMBER: SQ4-PP3-025U-050D-940-1D-UNV-STD-W-8

### Luminous Intensity Polar Plot





TEST NUMBER: P563200

CATALOG NUMBER: SQ4-PP3-025U-050D-940-1D-UNV-STD-W-8

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	71	71	71	67				
1	102	97	94	90	96	92	89	86	82	79	77	72	70	69	64	62	61	57				
2	93	85	79	74	87	81	75	71	72	68	64	64	61	58	56	54	52	48				
3	85	75	68	62	80	71	65	59	64	58	54	57	52	49	50	47	44	41				
4	78	67	59	53	73	63	56	50	57	51	46	51	46	42	45	41	38	35				
5	72	60	51	45	67	57	49	44	51	45	40	45	41	37	40	37	33	31				
6	66	54	45	39	62	51	43	38	46	40	35	41	36	32	37	33	29	27				
7	61	49	40	35	57	46	39	33	42	36	31	37	32	29	34	29	26	24				
8	57	44	36	31	53	42	35	30	38	32	28	34	29	26	31	27	24	21				
9	53	40	33	28	50	39	31	27	35	29	25	32	27	23	28	24	21	19				
10	50	37	30	25	47	35	29	24	32	26	22	29	24	21	26	22	19	17				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6075	6075	6075
5°	6119	6082	6060
10°	6109	6066	6038
15°	6069	6035	6002
20°	6028	5994	5949
25°	5957	5916	5857
30°	5846	5816	5742
35°	5694	5655	5583
40°	5511	5476	5414
45°	5361	5323	5271
50°	5169	5135	5085
55°	4901	4836	4799
60°	4462	4334	4312
65°	3931	3767	3754
70°	3394	3253	3253
75°	2921	2880	2839
80°	2574	2606	2545
85°	2017	2197	2197



TEST NUMBER: P563200

CATALOG NUMBER: SQ4-PP3-025U-050D-940-1D-UNV-STD-W-8

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	124.5	2.5
10°-20°	355.5	7.0
20°-30°	532.6	10.5
30°-40°	624.7	12.3
40°-50°	626.6	12.4
50°-60°	534.6	10.6
60°-70°	348.6	6.9
70°-80°	174.9	3.5
80°-90°	49.8	1.0
90°-100°	126.8	2.5
100°-110°	333.5	6.6
110°-120°	345.8	6.8
120°-130°	277.3	5.5
130°-140°	217.6	4.3
140°-150°	167.0	3.3
150°-160°	120.3	2.4
160°-170°	73.6	1.5
170°-180°	24.9	0.5
0°-30°	1012.6	20.0
0°-40°	1637.3	32.4
0°-60°	2798.4	55.3
0°-90°	3371.7	66.7
90°-120°	806.1	15.9
90°-150°	1468.1	29.0
90°-180°	1687.0	33.3
0°-180°	5058.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1317	1317	1317	1317	1317	
5°	1321	1309	1313	1309	1309	125
15°	1271	1258	1264	1259	1257	358
25°	1170	1157	1162	1152	1151	538
35°	1011	1001	1004	992	991	632
45°	822	816	816	808	808	633
55°	609	607	601	598	597	542
65°	360	353	345	343	344	359
75°	164	164	162	160	159	178
85°	38	42	42	42	42	45
90°	2	5	13	7	7	3
95°	17	66	218	113	77	19
105°	60	91	369	560	522	64
115°	107	130	295	589	672	105
125°	148	166	269	454	536	132
135°	177	195	260	366	415	137
145°	205	218	257	312	337	129
155°	232	238	257	282	290	107
165°	250	254	257	267	270	71
175°	260	260	259	262	262	25
180°	260	260	260	260	260	

TEST NUMBER: P563200

CATALOG NUMBER: SQ4-PP3-025U-050D-940-1D-UNV-STD-W-8

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1316.8	1316.8	1316.8	1316.8	1316.8
2.5°	1325.1	1314.3	1316.8	1314.9	1309.4
5°	1321.4	1309.0	1313.4	1308.7	1308.7
7.5°	1312.4	1298.9	1303.2	1298.6	1298.4
10°	1304.1	1290.6	1294.9	1290.3	1289.1
12.5°	1292.1	1278.6	1283.8	1278.3	1278.0
15°	1270.7	1258.2	1263.7	1259.1	1256.8
17.5°	1246.4	1232.9	1239.5	1233.0	1232.1
20°	1228.0	1214.4	1221.0	1211.8	1211.8
22.5°	1205.8	1192.3	1199.8	1187.8	1187.8
25°	1170.3	1156.7	1162.2	1151.8	1150.6
27.5°	1128.0	1114.7	1120.4	1108.6	1108.4
30°	1097.5	1085.1	1091.8	1079.1	1077.9
32.5°	1064.3	1052.8	1057.6	1044.9	1043.8
35°	1011.0	1000.8	1004.1	992.5	991.4
37.5°	954.9	944.5	948.2	938.3	937.8
40°	915.2	908.4	909.4	901.3	899.0
42.5°	878.3	870.6	871.6	863.5	863.0
45°	821.7	816.1	815.9	807.9	807.9
47.5°	761.7	757.4	756.2	749.5	749.2
50°	720.2	716.8	715.5	709.7	708.6
52.5°	676.8	675.2	671.2	666.4	666.1
55°	609.4	607.1	601.3	597.8	596.7
57.5°	536.2	531.7	525.1	520.1	521.0
60°	483.6	479.1	469.7	467.4	467.4
62.5°	432.8	427.4	418.0	414.8	416.6
65°	360.1	353.3	345.1	342.8	343.9
67.5°	294.1	288.0	279.1	279.0	278.1
70°	251.6	248.2	241.2	241.2	241.2
72.5°	213.7	212.2	207.0	207.0	206.1
75°	163.9	163.9	161.6	160.4	159.3
77.5°	122.8	123.2	122.1	120.9	118.9
80°	96.9	99.2	98.1	96.9	95.8
82.5°	72.9	75.2	75.0	72.9	72.7
85°	38.1	41.5	41.5	41.5	41.5
87.5°	10.5	14.8	17.4	16.1	17.0
90°	1.7	4.9	13.3	6.7	6.7
92.5°	7.0	33.8	74.7	33.1	21.4
95°	16.7	65.6	218.5	112.6	76.7
97.5°	29.0	72.1	327.0	260.0	191.5
100°	38.4	77.5	360.3	365.2	283.6
102.5°	46.4	82.9	369.7	454.9	385.0
105°	60.1	91.1	368.7	559.7	522.2
107.5°	74.1	102.8	347.7	614.1	623.3
110°	83.4	109.5	330.3	628.2	667.3

TEST NUMBER: P563200

CATALOG NUMBER: SQ4-PP3-025U-050D-940-1D-UNV-STD-W-8

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	92.8	117.6	314.3	619.3	679.3
115°	106.8	129.6	295.3	589.1	672.3
117.5°	120.4	141.3	282.3	547.3	639.6
120°	128.5	148.0	276.9	519.2	608.9
122.5°	136.5	156.0	272.9	491.1	579.6
125°	148.5	166.4	268.6	454.0	535.5
127.5°	158.2	176.4	264.9	424.0	492.8
130°	163.5	183.1	263.6	405.2	468.8
132.5°	168.8	188.4	262.3	389.0	446.1
135°	176.8	194.8	260.3	366.5	415.4
137.5°	185.2	202.8	259.9	349.6	389.7
140°	191.9	208.2	258.6	336.2	373.7
142.5°	197.2	212.2	258.6	326.7	359.0
145°	205.2	218.2	256.9	312.5	337.0
147.5°	213.2	225.9	256.9	300.7	321.0
150°	218.5	230.0	256.9	294.0	310.3
152.5°	223.9	232.7	256.9	288.6	301.0
155°	231.9	238.4	256.9	282.1	290.3
157.5°	237.9	244.1	256.9	276.4	282.3
160°	241.9	246.8	256.9	273.7	276.9
162.5°	245.9	249.5	256.9	271.0	274.3
165°	250.2	253.5	256.9	267.0	270.3
167.5°	254.2	255.9	258.6	265.3	266.6
170°	256.9	258.5	258.6	265.3	265.3
172.5°	258.2	258.6	258.6	263.9	262.6
175°	260.3	260.3	258.6	261.9	261.9
177.5°	260.3	260.3	258.9	261.6	260.3
180°	260.3	260.3	260.3	260.3	260.3

(END OF REPORT)