

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563392

Luminaire Tested: **SQ4-PP3-075U-050D-940-1D-UNV-STD-W-8**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563392
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-22, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-075U-050D-940-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8548.5 lumens
Efficiency: N/A
Efficacy: 119.1 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 71.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563392
CATALOG NUMBER: SQ4-PP3-075U-050D-940-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P563392

CATALOG NUMBER: SQ4-PP3-075U-050D-940-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46	39
1	96	91	88	84	87	83	80	77	68	66	64	54	53	51	41	40	40	34
2	87	80	74	69	79	73	68	64	60	56	53	48	45	43	36	35	33	28
3	80	70	63	58	72	64	58	53	53	48	45	42	39	37	32	30	29	24
4	73	62	55	49	66	57	50	45	47	42	38	38	34	31	29	27	25	21
5	67	55	47	42	60	51	44	39	42	37	33	34	30	27	26	24	22	18
6	61	50	42	36	56	46	39	34	38	33	29	30	27	24	24	21	19	16
7	57	45	37	32	51	41	34	29	34	29	25	28	24	21	22	19	17	14
8	53	41	33	28	48	37	31	26	31	26	22	25	21	19	20	17	15	13
9	49	37	30	25	44	34	28	23	28	23	20	23	19	17	18	16	14	11
10	46	34	27	22	42	31	25	21	26	21	18	21	18	15	17	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6075	6075	6075
5°	6119	6082	6060
10°	6109	6066	6038
15°	6069	6035	6002
20°	6028	5994	5949
25°	5957	5916	5857
30°	5846	5816	5742
35°	5694	5655	5583
40°	5511	5476	5414
45°	5361	5323	5271
50°	5169	5135	5085
55°	4901	4836	4799
60°	4462	4334	4312
65°	3931	3767	3754
70°	3394	3253	3253
75°	2921	2880	2839
80°	2574	2606	2545
85°	2017	2197	2197



TEST NUMBER: P563392

CATALOG NUMBER: SQ4-PP3-075U-050D-940-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	124.5	1.5
10°-20°	355.5	4.2
20°-30°	532.6	6.2
30°-40°	624.7	7.3
40°-50°	626.6	7.3
50°-60°	534.6	6.3
60°-70°	348.6	4.1
70°-80°	174.9	2.0
80°-90°	50.4	0.6
90°-100°	374.7	4.4
100°-110°	1031.0	12.1
110°-120°	1064.2	12.4
120°-130°	852.6	10.0
130°-140°	669.7	7.8
140°-150°	513.2	6.0
150°-160°	369.0	4.3
160°-170°	225.6	2.6
170°-180°	76.1	0.9
0°-30°	1012.6	11.8
0°-40°	1637.3	19.2
0°-60°	2798.4	32.7
0°-90°	3372.4	39.4
90°-120°	2470.0	28.9
90°-150°	4505.5	52.7
90°-180°	5176.0	60.5
0°-180°	8548.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1317	1317	1317	1317	1317	
5°	1321	1309	1313	1309	1309	125
15°	1271	1258	1264	1259	1257	358
25°	1170	1157	1162	1152	1151	538
35°	1011	1001	1004	992	991	632
45°	822	816	816	808	808	633
55°	609	607	601	598	597	542
65°	360	353	345	343	344	359
75°	164	164	162	160	159	178
85°	38	42	42	42	42	45
90°	2	7	12	15	15	5
95°	56	205	663	283	181	59
105°	184	283	1136	1730	1614	194
115°	326	397	911	1814	2059	322
125°	450	512	827	1398	1638	401
135°	543	602	803	1131	1280	419
145°	627	670	791	964	1038	393
155°	710	733	786	866	891	326
165°	768	777	790	822	827	216
175°	794	796	791	801	800	75
180°	794	794	794	794	794	



TEST NUMBER: P563392

CATALOG NUMBER: SQ4-PP3-075U-050D-940-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1316.8	1316.8	1316.8	1316.8	1316.8
2.5°	1325.1	1314.3	1316.8	1314.9	1309.4
5°	1321.4	1309.0	1313.4	1308.7	1308.7
7.5°	1312.4	1298.9	1303.2	1298.6	1298.4
10°	1304.1	1290.6	1294.9	1290.3	1289.1
12.5°	1292.1	1278.6	1283.8	1278.3	1278.0
15°	1270.7	1258.2	1263.7	1259.1	1256.8
17.5°	1246.4	1232.9	1239.5	1233.0	1232.1
20°	1228.0	1214.4	1221.0	1211.8	1211.8
22.5°	1205.8	1192.3	1199.8	1187.8	1187.8
25°	1170.3	1156.7	1162.2	1151.8	1150.6
27.5°	1128.0	1114.7	1120.4	1108.6	1108.4
30°	1097.5	1085.1	1091.8	1079.1	1077.9
32.5°	1064.3	1052.8	1057.6	1044.9	1043.8
35°	1011.0	1000.8	1004.1	992.5	991.4
37.5°	954.9	944.5	948.2	938.3	937.8
40°	915.2	908.4	909.4	901.3	899.0
42.5°	878.3	870.6	871.6	863.5	863.0
45°	821.7	816.1	815.9	807.9	807.9
47.5°	761.7	757.4	756.2	749.5	749.2
50°	720.2	716.8	715.5	709.7	708.6
52.5°	676.8	675.2	671.2	666.4	666.1
55°	609.4	607.1	601.3	597.8	596.7
57.5°	536.2	531.7	525.1	520.1	521.0
60°	483.6	479.1	469.7	467.4	467.4
62.5°	432.8	427.4	418.0	414.8	416.6
65°	360.1	353.3	345.1	342.8	343.9
67.5°	294.1	288.0	279.1	279.0	278.1
70°	251.6	248.2	241.2	241.2	241.2
72.5°	213.7	212.2	207.0	207.0	206.1
75°	163.9	163.9	161.6	160.4	159.3
77.5°	122.8	123.2	122.1	120.9	118.9
80°	96.9	99.2	98.1	96.9	95.8
82.5°	72.9	75.2	75.0	72.9	72.7
85°	38.1	41.5	41.5	41.5	41.5
87.5°	10.5	15.1	17.1	17.8	18.7
90°	1.7	6.6	11.8	15.2	15.2
92.5°	23.3	99.7	172.8	66.3	54.4
95°	55.8	204.6	662.7	283.4	180.9
97.5°	90.9	226.8	1011.3	779.2	549.8
100°	116.6	240.6	1120.8	1131.3	923.0
102.5°	141.0	257.0	1149.2	1403.5	1212.4
105°	184.3	283.4	1136.0	1730.2	1614.4
107.5°	225.5	316.1	1071.5	1890.1	1924.5
110°	255.3	337.9	1022.8	1929.9	2048.9



TEST NUMBER: P563392

CATALOG NUMBER: SQ4-PP3-075U-050D-940-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	282.3	362.3	974.1	1904.3	2085.4
115°	326.3	397.3	911.2	1814.4	2059.1
117.5°	368.2	433.7	871.3	1688.4	1965.1
120°	393.9	456.7	853.7	1593.9	1879.9
122.5°	416.9	479.7	841.5	1511.1	1782.5
125°	449.7	512.5	826.7	1398.4	1638.1
127.5°	480.8	540.6	816.9	1304.4	1514.7
130°	497.0	558.2	811.4	1248.6	1440.3
132.5°	515.9	577.1	807.4	1199.5	1372.7
135°	542.7	602.2	803.0	1131.0	1279.7
137.5°	567.7	622.9	799.3	1075.6	1198.2
140°	586.6	637.9	797.9	1038.8	1149.6
142.5°	602.8	650.1	795.2	1006.0	1100.9
145°	627.2	670.2	791.2	963.6	1038.0
147.5°	653.2	690.2	789.1	926.1	985.6
150°	669.4	702.5	787.8	905.5	951.8
152.5°	684.3	714.7	786.4	887.7	926.1
155°	710.0	733.2	786.1	866.1	890.9
157.5°	728.6	747.5	786.1	848.4	865.5
160°	742.1	757.0	786.1	838.8	852.0
162.5°	753.0	765.2	787.4	830.6	841.2
165°	767.5	777.4	789.5	821.7	826.7
167.5°	777.6	785.2	791.2	814.2	815.5
170°	784.4	789.4	791.2	811.4	811.4
172.5°	789.8	792.1	791.2	807.4	806.0
175°	794.5	796.2	791.2	801.3	799.6
177.5°	795.9	795.9	790.5	798.5	795.9
180°	794.5	794.5	794.5	794.5	794.5

(END OF REPORT)