

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563440

Luminaire Tested: **SQ4-PP3-075U-100D-940-1D-UNV-STD-W-8**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563440
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-22, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-075U-100D-940-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11778.5 lumens
Efficiency: N/A
Efficacy: 108.8 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 108.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563440
CATALOG NUMBER: SQ4-PP3-075U-100D-940-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P563440

CATALOG NUMBER: SQ4-PP3-075U-100D-940-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	56
1	99	95	91	88	92	89	85	82	76	74	72	65	63	62	55	54	53	48
2	91	83	77	72	84	78	72	68	67	63	60	58	55	52	49	46	45	40
3	83	73	66	60	77	69	62	57	59	54	50	51	47	44	43	40	38	34
4	76	65	57	51	70	61	54	48	53	47	43	46	41	38	39	36	33	30
5	70	58	50	44	65	54	47	42	47	42	37	41	36	33	35	31	29	26
6	64	52	44	38	60	49	42	36	43	37	33	37	32	29	32	28	25	23
7	59	47	39	33	55	44	37	32	39	33	29	34	29	26	29	25	23	20
8	55	43	35	30	51	40	33	28	35	30	26	31	26	23	27	23	20	18
9	51	39	32	26	48	37	30	25	32	27	23	28	24	21	24	21	18	16
10	48	36	29	24	45	34	27	23	30	24	21	26	22	19	23	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11896	11896	11896
5°	11983	11910	11869
10°	11963	11879	11826
15°	11884	11819	11755
20°	11806	11739	11650
25°	11665	11584	11469
30°	11449	11389	11245
35°	11150	11073	10933
40°	10793	10725	10602
45°	10498	10425	10321
50°	10121	10057	9959
55°	9597	9470	9398
60°	8737	8487	8446
65°	7698	7377	7352
70°	6645	6372	6372
75°	5720	5639	5559
80°	5045	5103	4984
85°	3949	4308	4308



TEST NUMBER: P563440

CATALOG NUMBER: SQ4-PP3-075U-100D-940-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	243.8	2.1
10°-20°	696.3	5.9
20°-30°	1042.9	8.9
30°-40°	1223.3	10.4
40°-50°	1227.1	10.4
50°-60°	1046.8	8.9
60°-70°	682.7	5.8
70°-80°	342.5	2.9
80°-90°	96.8	0.8
90°-100°	374.7	3.2
100°-110°	1031.0	8.8
110°-120°	1064.2	9.0
120°-130°	852.6	7.2
130°-140°	669.7	5.7
140°-150°	513.2	4.4
150°-160°	369.0	3.1
160°-170°	225.6	1.9
170°-180°	76.1	0.6
0°-30°	1983.0	16.8
0°-40°	3206.4	27.2
0°-60°	5480.3	46.5
0°-90°	6602.4	56.1
90°-120°	2470.0	21.0
90°-150°	4505.5	38.3
90°-180°	5176.0	43.9
0°-180°	11778.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2579	2579	2579	2579	2579	
5°	2588	2564	2572	2563	2563	246
15°	2488	2464	2475	2466	2461	702
25°	2292	2265	2276	2256	2253	1054
35°	1980	1960	1966	1944	1941	1237
45°	1609	1598	1598	1582	1582	1239
55°	1193	1189	1178	1171	1168	1061
65°	705	692	676	671	674	704
75°	321	321	316	314	312	348
85°	75	81	81	81	81	88
90°	2	7	12	15	15	6
95°	56	205	663	283	181	59
105°	184	283	1136	1730	1614	194
115°	326	397	911	1814	2059	322
125°	450	512	827	1398	1638	401
135°	543	602	803	1131	1280	419
145°	627	670	791	964	1038	393
155°	710	733	786	866	891	326
165°	768	777	790	822	827	216
175°	794	796	791	801	800	75
180°	794	794	794	794	794	

TEST NUMBER: P563440

CATALOG NUMBER: SQ4-PP3-075U-100D-940-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2578.8	2578.8	2578.8	2578.8	2578.8
2.5°	2595.1	2573.9	2578.8	2574.9	2564.3
5°	2587.8	2563.5	2572.0	2563.0	2563.0
7.5°	2570.2	2543.7	2552.1	2543.1	2542.6
10°	2553.9	2527.4	2535.9	2526.8	2524.6
12.5°	2530.4	2503.9	2514.2	2503.3	2502.9
15°	2488.4	2464.1	2474.8	2465.7	2461.3
17.5°	2440.9	2414.4	2427.4	2414.7	2412.9
20°	2404.8	2378.3	2391.2	2373.1	2373.1
22.5°	2361.4	2334.9	2349.6	2326.1	2326.1
25°	2291.8	2265.2	2275.9	2255.6	2253.3
27.5°	2209.0	2183.0	2194.1	2171.1	2170.6
30°	2149.4	2125.1	2138.1	2113.2	2111.0
32.5°	2084.3	2061.7	2071.2	2046.3	2044.1
35°	1979.9	1960.0	1966.3	1943.7	1941.4
37.5°	1870.0	1849.7	1856.9	1837.5	1836.6
40°	1792.3	1779.0	1781.0	1765.1	1760.6
42.5°	1720.0	1704.9	1706.8	1691.0	1690.1
45°	1609.2	1598.2	1597.9	1582.1	1582.1
47.5°	1491.7	1483.3	1480.8	1467.7	1467.3
50°	1410.3	1403.7	1401.3	1389.9	1387.7
52.5°	1325.3	1322.2	1314.5	1305.0	1304.5
55°	1193.3	1188.9	1177.5	1170.7	1168.5
57.5°	1050.1	1041.2	1028.4	1018.5	1020.2
60°	947.0	938.2	919.9	915.4	915.4
62.5°	847.5	836.9	818.6	812.4	815.9
65°	705.2	691.9	675.8	671.3	673.5
67.5°	575.9	563.9	546.5	546.5	544.7
70°	492.7	486.1	472.4	472.4	472.4
72.5°	418.6	415.5	405.5	405.4	403.7
75°	320.9	320.9	316.4	314.1	311.9
77.5°	240.5	241.4	239.1	236.8	232.8
80°	189.9	194.3	192.1	189.8	187.6
82.5°	142.8	147.3	146.9	142.8	142.4
85°	74.6	81.2	81.4	81.4	81.4
87.5°	20.2	28.3	31.3	32.0	33.8
90°	1.7	6.6	11.8	15.2	15.2
92.5°	23.3	99.7	172.8	66.3	54.4
95°	55.8	204.6	662.7	283.4	180.9
97.5°	90.9	226.8	1011.3	779.2	549.8
100°	116.6	240.6	1120.8	1131.3	923.0
102.5°	141.0	257.0	1149.2	1403.5	1212.4
105°	184.3	283.4	1136.0	1730.2	1614.4
107.5°	225.5	316.1	1071.5	1890.1	1924.5
110°	255.3	337.9	1022.8	1929.9	2048.9



TEST NUMBER: P563440

CATALOG NUMBER: SQ4-PP3-075U-100D-940-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	282.3	362.3	974.1	1904.3	2085.4
115°	326.3	397.3	911.2	1814.4	2059.1
117.5°	368.2	433.7	871.3	1688.4	1965.1
120°	393.9	456.7	853.7	1593.9	1879.9
122.5°	416.9	479.7	841.5	1511.1	1782.5
125°	449.7	512.5	826.7	1398.4	1638.1
127.5°	480.8	540.6	816.9	1304.4	1514.7
130°	497.0	558.2	811.4	1248.6	1440.3
132.5°	515.9	577.1	807.4	1199.5	1372.7
135°	542.7	602.2	803.0	1131.0	1279.7
137.5°	567.7	622.9	799.3	1075.6	1198.2
140°	586.6	637.9	797.9	1038.8	1149.6
142.5°	602.8	650.1	795.2	1006.0	1100.9
145°	627.2	670.2	791.2	963.6	1038.0
147.5°	653.2	690.2	789.1	926.1	985.6
150°	669.4	702.5	787.8	905.5	951.8
152.5°	684.3	714.7	786.4	887.7	926.1
155°	710.0	733.2	786.1	866.1	890.9
157.5°	728.6	747.5	786.1	848.4	865.5
160°	742.1	757.0	786.1	838.8	852.0
162.5°	753.0	765.2	787.4	830.6	841.2
165°	767.5	777.4	789.5	821.7	826.7
167.5°	777.6	785.2	791.2	814.2	815.5
170°	784.4	789.4	791.2	811.4	811.4
172.5°	789.8	792.1	791.2	807.4	806.0
175°	794.5	796.2	791.2	801.3	799.6
177.5°	795.9	795.9	790.5	798.5	795.9
180°	794.5	794.5	794.5	794.5	794.5

(END OF REPORT)