

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563560

Luminaire Tested: **SQ4-PP3-0U-125D-940-1D-UNV-STD-W-8**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P563560  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2103-172-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PP3-0U-125D-940-1D-UNV-STD-W-8  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.  
DOWNLIGHT 1250 LUMENS PER FOOT  
DIRECT ONLY  
Light Source: 4000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 8422.9 lumens  
Efficiency: N/A  
Efficacy: 92.5 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33  
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')  
CIE Type: Direct

Input Watts (W): 91.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P563560  
CATALOG NUMBER: SQ4-PP3-0U-125D-940-1D-UNV-STD-W-8

### Luminous Intensity Polar Plot





TEST NUMBER: P563560

CATALOG NUMBER: SQ4-PP3-OU-125D-940-1D-UNV-STD-W-8

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	105	101	97	107	103	99	96	98	95	93	95	92	90	91	89	87	85
2	100	92	86	80	97	90	84	79	87	82	77	84	79	76	81	77	74	72
3	92	81	74	67	89	80	73	67	77	71	66	74	69	64	72	67	63	61
4	84	72	64	57	82	71	63	57	69	62	56	66	60	56	64	59	55	53
5	77	65	56	50	75	64	56	49	62	54	49	60	53	48	58	52	48	46
6	72	59	50	44	70	58	49	43	56	49	43	54	48	43	53	47	42	40
7	66	53	45	39	65	52	44	39	51	44	38	49	43	38	48	42	38	36
8	62	49	40	35	60	48	40	34	47	39	34	45	39	34	44	38	34	32
9	58	45	37	31	56	44	36	31	43	36	31	42	35	31	41	35	31	29
10	54	41	34	28	53	41	33	28	40	33	28	39	33	28	38	32	28	26

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	15181	15181	15181
5°	15292	15199	15146
10°	15267	15159	15091
15°	15166	15083	15000
20°	15065	14980	14867
25°	14886	14783	14637
30°	14611	14534	14350
35°	14229	14131	13952
40°	13773	13687	13530
45°	13398	13303	13172
50°	12917	12833	12709
55°	12248	12086	11992
60°	11150	10831	10777
65°	9823	9414	9382
70°	8481	8130	8130
75°	7301	7197	7094
80°	6437	6514	6360
85°	5039	5494	5494



TEST NUMBER: P563560

CATALOG NUMBER: SQ4-PP3-0U-125D-940-1D-UNV-STD-W-8

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	311.2	3.7
10°-20°	888.5	10.5
20°-30°	1330.9	15.8
30°-40°	1561.1	18.5
40°-50°	1566.0	18.6
50°-60°	1335.9	15.9
60°-70°	871.2	10.3
70°-80°	437.1	5.2
80°-90°	121.0	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2530.6	30.0
0°-40°	4091.7	48.6
0°-60°	6993.6	83.0
0°-90°	8422.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8422.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	3291	3291	3291	3291	3291	
5°	3302	3271	3282	3271	3271	314
15°	3176	3144	3158	3147	3141	896
25°	2925	2891	2904	2878	2876	1345
35°	2527	2501	2509	2480	2478	1578
45°	2054	2040	2039	2019	2019	1581
55°	1523	1517	1503	1494	1491	1353
65°	900	883	862	857	860	898
75°	410	410	404	401	398	444
85°	95	104	104	104	104	115
90°	0	0	0	0	0	



TEST NUMBER: P563560

CATALOG NUMBER: SQ4-PP3-0U-125D-940-1D-UNV-STD-W-8

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	3290.9	3290.9	3290.9	3290.9	3290.9
2.5°	3311.7	3284.6	3290.9	3286.0	3272.4
5°	3302.4	3271.4	3282.2	3270.7	3270.7
7.5°	3279.9	3246.1	3256.9	3245.3	3244.8
10°	3259.2	3225.3	3236.1	3224.5	3221.7
12.5°	3229.2	3195.3	3208.4	3194.6	3194.0
15°	3175.5	3144.5	3158.2	3146.6	3140.9
17.5°	3115.0	3081.1	3097.7	3081.5	3079.2
20°	3068.8	3035.0	3051.5	3028.4	3028.4
22.5°	3013.4	2979.6	2998.4	2968.4	2968.4
25°	2924.6	2890.8	2904.4	2878.4	2875.6
27.5°	2819.0	2785.8	2800.0	2770.6	2770.0
30°	2742.9	2711.9	2728.5	2696.7	2693.9
32.5°	2659.8	2631.1	2643.1	2611.3	2608.5
35°	2526.6	2501.2	2509.3	2480.4	2477.5
37.5°	2386.4	2360.5	2369.7	2344.8	2343.7
40°	2287.2	2270.3	2272.8	2252.5	2246.8
42.5°	2194.9	2175.7	2178.2	2158.0	2156.8
45°	2053.6	2039.5	2039.1	2019.0	2019.0
47.5°	1903.6	1892.9	1889.7	1873.0	1872.4
50°	1799.8	1791.3	1788.2	1773.7	1770.9
52.5°	1691.3	1687.4	1677.5	1665.3	1664.8
55°	1522.9	1517.2	1502.7	1494.0	1491.1
57.5°	1340.0	1328.7	1312.3	1299.7	1301.9
60°	1208.5	1197.2	1173.9	1168.1	1168.1
62.5°	1081.6	1068.0	1044.7	1036.7	1041.2
65°	899.9	883.0	862.4	856.7	859.5
67.5°	734.9	719.7	697.4	697.4	695.1
70°	628.8	620.3	602.8	602.8	602.8
72.5°	534.2	530.2	517.4	517.4	515.1
75°	409.6	409.6	403.8	400.8	398.0
77.5°	306.9	308.0	305.2	302.2	297.1
80°	242.3	247.9	245.2	242.2	239.4
82.5°	182.3	187.9	187.5	182.3	181.7
85°	95.2	103.6	103.8	103.8	103.8
87.5°	25.4	34.4	36.9	37.0	39.2
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)