

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563608

Luminaire Tested: **SQ4-PP3-100U-075D-940-1D-UNV-STD-W-8**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563608
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-23, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-100U-075D-940-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11913.7 lumens
Efficiency: N/A
Efficacy: 114.7 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 103.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563608
CATALOG NUMBER: SQ4-PP3-100U-075D-940-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P563608

CATALOG NUMBER: SQ4-PP3-100U-075D-940-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	49	49	49	42
1	96	92	88	85	88	84	81	78	69	67	65	56	54	53	43	42	41	35
2	88	80	74	69	80	74	68	64	61	57	54	49	46	44	38	36	35	30
3	80	71	64	58	73	65	59	54	54	49	45	43	40	38	34	32	30	26
4	73	63	55	49	67	57	51	46	48	43	39	39	35	32	30	28	26	22
5	67	56	48	42	61	51	44	39	43	37	33	35	31	28	27	25	23	19
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	25	22	20	17
7	57	45	37	32	52	42	35	30	35	29	26	29	25	22	23	20	18	15
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	21	18	16	13
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	12
10	46	34	27	22	42	32	25	21	27	22	18	22	18	16	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8953	8953	8953
5°	9019	8964	8932
10°	9004	8940	8900
15°	8944	8895	8847
20°	8885	8835	8768
25°	8779	8719	8632
30°	8617	8571	8463
35°	8392	8334	8229
40°	8123	8072	7980
45°	7901	7846	7768
50°	7617	7569	7495
55°	7223	7127	7073
60°	6576	6387	6356
65°	5793	5552	5533
70°	5001	4795	4795
75°	4304	4244	4183
80°	3796	3841	3751
85°	2969	3239	3239



TEST NUMBER: P563608

CATALOG NUMBER: SQ4-PP3-100U-075D-940-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	183.5	1.5
10°-20°	524.0	4.4
20°-30°	784.9	6.6
30°-40°	920.7	7.7
40°-50°	923.5	7.8
50°-60°	787.9	6.6
60°-70°	513.8	4.3
70°-80°	257.8	2.2
80°-90°	73.5	0.6
90°-100°	500.5	4.2
100°-110°	1381.7	11.6
110°-120°	1425.0	12.0
120°-130°	1145.1	9.6
130°-140°	899.9	7.6
140°-150°	690.2	5.8
150°-160°	496.0	4.2
160°-170°	303.4	2.5
170°-180°	102.3	0.9
0°-30°	1492.5	12.5
0°-40°	2413.1	20.3
0°-60°	4124.5	34.6
0°-90°	4969.7	41.7
90°-120°	3307.2	27.8
90°-150°	6042.4	50.7
90°-180°	6944.0	58.3
0°-180°	11913.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1941	1941	1941	1941	1941	
5°	1948	1929	1936	1929	1929	185
15°	1873	1854	1863	1856	1852	528
25°	1725	1705	1713	1698	1696	793
35°	1490	1475	1480	1463	1461	931
45°	1211	1203	1203	1191	1191	933
55°	898	895	886	881	879	798
65°	531	521	509	505	507	530
75°	242	242	238	236	235	262
85°	56	61	61	61	61	66
90°	3	7	14	15	17	7
95°	74	271	908	373	243	79
105°	246	380	1520	2321	2185	262
115°	441	533	1224	2424	2756	434
125°	605	689	1110	1878	2204	539
135°	728	807	1079	1521	1715	564
145°	845	903	1065	1295	1394	529
155°	952	984	1057	1162	1199	439
165°	1031	1044	1062	1103	1112	291
175°	1069	1070	1064	1079	1076	102
180°	1069	1069	1069	1069	1069	

TEST NUMBER: P563608

CATALOG NUMBER: SQ4-PP3-100U-075D-940-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1940.8	1940.8	1940.8	1940.8	1940.8
2.5°	1953.1	1937.1	1940.8	1937.9	1930.0
5°	1947.6	1929.4	1935.7	1928.9	1928.9
7.5°	1934.4	1914.4	1920.8	1914.0	1913.6
10°	1922.1	1902.2	1908.5	1901.7	1900.0
12.5°	1904.4	1884.5	1892.2	1884.0	1883.7
15°	1872.8	1854.5	1862.6	1855.7	1852.4
17.5°	1837.1	1817.1	1826.9	1817.3	1816.0
20°	1809.9	1789.9	1799.7	1786.1	1786.1
22.5°	1777.2	1757.2	1768.4	1750.7	1750.7
25°	1724.8	1704.9	1712.9	1697.6	1695.9
27.5°	1662.6	1642.9	1651.3	1634.0	1633.6
30°	1617.7	1599.4	1609.1	1590.4	1588.7
32.5°	1568.7	1551.7	1558.8	1540.0	1538.4
35°	1490.1	1475.1	1479.9	1462.8	1461.2
37.5°	1407.4	1392.1	1397.5	1382.9	1382.2
40°	1348.9	1338.9	1340.4	1328.4	1325.1
42.5°	1294.5	1283.2	1284.6	1272.7	1272.0
45°	1211.1	1202.8	1202.6	1190.7	1190.7
47.5°	1122.7	1116.3	1114.5	1104.6	1104.3
50°	1061.4	1056.4	1054.6	1046.1	1044.4
52.5°	997.5	995.1	989.3	982.2	981.8
55°	898.1	894.8	886.2	881.1	879.4
57.5°	790.3	783.6	774.0	766.5	767.8
60°	712.7	706.1	692.3	688.9	688.9
62.5°	637.9	629.9	616.1	611.4	614.1
65°	530.7	520.7	508.6	505.2	506.9
67.5°	433.4	424.4	411.3	411.3	409.9
70°	370.8	365.8	355.5	355.5	355.5
72.5°	315.0	312.7	305.2	305.1	303.8
75°	241.5	241.5	238.1	236.4	234.7
77.5°	181.0	181.7	180.0	178.2	175.2
80°	142.9	146.2	144.6	142.8	141.2
82.5°	107.5	110.8	110.6	107.5	107.2
85°	56.1	61.1	61.2	61.2	61.2
87.5°	15.7	21.6	24.5	24.9	26.6
90°	3.4	6.8	13.7	15.4	17.1
92.5°	30.8	127.8	228.5	83.4	65.0
95°	73.5	270.8	908.0	373.2	242.8
97.5°	121.7	303.3	1345.1	1035.6	750.0
100°	157.3	322.8	1506.5	1517.1	1232.9
102.5°	191.5	345.0	1537.9	1874.5	1605.0
105°	246.2	380.0	1520.2	2320.8	2185.3
107.5°	304.4	423.4	1435.3	2536.0	2585.5
110°	345.4	452.4	1369.7	2582.3	2742.8



TEST NUMBER: P563608

CATALOG NUMBER: SQ4-PP3-100U-075D-940-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	382.3	485.3	1308.1	2545.7	2782.5
115°	441.2	533.1	1224.3	2423.8	2756.5
117.5°	492.5	584.1	1169.3	2252.1	2630.6
120°	526.7	617.0	1147.4	2135.9	2517.1
122.5°	559.5	645.8	1129.6	2027.3	2388.5
125°	605.3	688.9	1109.8	1878.1	2204.2
127.5°	644.3	727.9	1098.1	1751.9	2033.2
130°	670.3	753.9	1092.7	1674.7	1930.6
132.5°	694.9	774.5	1087.2	1609.9	1841.6
135°	728.4	807.0	1079.0	1521.2	1715.1
137.5°	766.1	837.6	1074.9	1446.6	1612.2
140°	786.6	856.8	1072.2	1396.9	1542.4
142.5°	809.8	874.7	1069.4	1352.8	1480.8
145°	844.7	903.2	1065.3	1295.0	1393.6
147.5°	878.2	929.4	1061.5	1246.3	1322.8
150°	902.9	944.7	1060.2	1217.2	1279.1
152.5°	922.0	961.1	1058.8	1192.3	1243.5
155°	952.5	984.2	1056.8	1161.9	1198.7
157.5°	980.5	1004.9	1057.1	1139.8	1164.8
160°	996.9	1018.6	1058.5	1127.3	1145.7
162.5°	1010.6	1029.7	1059.8	1116.3	1130.6
165°	1031.1	1044.5	1061.9	1103.1	1111.5
167.5°	1046.8	1054.9	1063.6	1095.1	1097.8
170°	1055.1	1061.7	1063.6	1091.0	1091.0
172.5°	1061.9	1065.9	1063.6	1085.5	1084.1
175°	1068.7	1070.4	1063.6	1078.9	1075.6
177.5°	1071.5	1070.1	1063.3	1072.8	1070.1
180°	1068.7	1068.7	1068.7	1068.7	1068.7

(END OF REPORT)