

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: CORELITE

Report Number: P563800

Luminaire Tested: **SQ4-PP3-150U-075D-940-1D-UNV-STD-W-8**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563800
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-25, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-150U-075D-940-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 15386.0 lumens
Efficiency: N/A
Efficacy: 117.4 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 131.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563800
CATALOG NUMBER: SQ4-PP3-150U-075D-940-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P563800

CATALOG NUMBER: SQ4-PP3-150U-075D-940-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40	32
1	94	90	86	83	84	81	78	75	65	62	60	49	48	47	35	35	34	27
2	86	79	73	68	77	71	66	62	57	53	50	43	41	39	31	30	29	23
3	78	69	62	56	70	62	56	52	50	46	42	38	36	33	28	26	25	20
4	71	61	53	48	64	55	49	44	44	40	36	34	31	28	25	23	21	17
5	65	54	46	41	59	49	42	37	40	35	31	31	27	25	22	20	18	15
6	60	49	41	35	54	44	37	32	36	31	27	28	24	21	20	18	16	13
7	56	44	36	31	50	40	33	28	32	27	24	25	22	19	19	16	14	12
8	51	40	32	27	46	36	29	25	29	24	21	23	19	17	17	15	13	10
9	48	36	29	24	43	33	26	22	27	22	19	21	18	15	16	13	12	9
10	45	33	26	21	40	30	24	20	25	20	17	19	16	14	14	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8953	8953	8953
5°	9019	8964	8932
10°	9004	8940	8900
15°	8944	8895	8847
20°	8885	8835	8768
25°	8779	8719	8632
30°	8617	8571	8463
35°	8392	8334	8229
40°	8123	8072	7980
45°	7901	7846	7768
50°	7617	7569	7495
55°	7223	7127	7073
60°	6576	6387	6356
65°	5793	5552	5533
70°	5001	4795	4795
75°	4304	4244	4183
80°	3796	3841	3751
85°	2969	3239	3239



TEST NUMBER: P563800

CATALOG NUMBER: SQ4-PP3-150U-075D-940-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	183.5	1.2
10°-20°	524.0	3.4
20°-30°	784.9	5.1
30°-40°	920.7	6.0
40°-50°	923.5	6.0
50°-60°	787.9	5.1
60°-70°	513.8	3.3
70°-80°	257.8	1.7
80°-90°	74.7	0.5
90°-100°	750.7	4.9
100°-110°	2029.9	13.2
110°-120°	2134.1	13.9
120°-130°	1733.5	11.3
130°-140°	1359.8	8.8
140°-150°	1043.6	6.8
150°-160°	750.6	4.9
160°-170°	458.5	3.0
170°-180°	154.6	1.0
0°-30°	1492.5	9.7
0°-40°	2413.1	15.7
0°-60°	4124.5	26.8
0°-90°	4970.8	32.3
90°-120°	4914.7	31.9
90°-150°	9051.5	58.8
90°-180°	10415.0	67.7
0°-180°	15386.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1941	1941	1941	1941	1941	
5°	1948	1929	1936	1929	1929	185
15°	1873	1854	1863	1856	1852	528
25°	1725	1705	1713	1698	1696	793
35°	1490	1475	1480	1463	1461	931
45°	1211	1203	1203	1191	1191	933
55°	898	895	886	881	879	798
65°	531	521	509	505	507	530
75°	242	242	238	236	235	262
85°	56	61	61	61	61	66
90°	4	10	23	24	23	10
95°	116	409	1248	646	384	122
105°	377	583	2252	3322	3186	397
115°	664	812	1868	3615	4081	656
125°	909	1042	1683	2840	3337	811
135°	1090	1220	1638	2294	2596	843
145°	1268	1363	1615	1963	2113	793
155°	1431	1487	1602	1761	1819	660
165°	1558	1573	1608	1671	1680	439
175°	1617	1616	1610	1631	1628	154
180°	1615	1615	1615	1615	1615	

TEST NUMBER: P563800

CATALOG NUMBER: SQ4-PP3-150U-075D-940-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1940.8	1940.8	1940.8	1940.8	1940.8
2.5°	1953.1	1937.1	1940.8	1937.9	1930.0
5°	1947.6	1929.4	1935.7	1928.9	1928.9
7.5°	1934.4	1914.4	1920.8	1914.0	1913.6
10°	1922.1	1902.2	1908.5	1901.7	1900.0
12.5°	1904.4	1884.5	1892.2	1884.0	1883.7
15°	1872.8	1854.5	1862.6	1855.7	1852.4
17.5°	1837.1	1817.1	1826.9	1817.3	1816.0
20°	1809.9	1789.9	1799.7	1786.1	1786.1
22.5°	1777.2	1757.2	1768.4	1750.7	1750.7
25°	1724.8	1704.9	1712.9	1697.6	1695.9
27.5°	1662.6	1642.9	1651.3	1634.0	1633.6
30°	1617.7	1599.4	1609.1	1590.4	1588.7
32.5°	1568.7	1551.7	1558.8	1540.0	1538.4
35°	1490.1	1475.1	1479.9	1462.8	1461.2
37.5°	1407.4	1392.1	1397.5	1382.9	1382.2
40°	1348.9	1338.9	1340.4	1328.4	1325.1
42.5°	1294.5	1283.2	1284.6	1272.7	1272.0
45°	1211.1	1202.8	1202.6	1190.7	1190.7
47.5°	1122.7	1116.3	1114.5	1104.6	1104.3
50°	1061.4	1056.4	1054.6	1046.1	1044.4
52.5°	997.5	995.1	989.3	982.2	981.8
55°	898.1	894.8	886.2	881.1	879.4
57.5°	790.3	783.6	774.0	766.5	767.8
60°	712.7	706.1	692.3	688.9	688.9
62.5°	637.9	629.9	616.1	611.4	614.1
65°	530.7	520.7	508.6	505.2	506.9
67.5°	433.4	424.4	411.3	411.3	409.9
70°	370.8	365.8	355.5	355.5	355.5
72.5°	315.0	312.7	305.2	305.1	303.8
75°	241.5	241.5	238.1	236.4	234.7
77.5°	181.0	181.7	180.0	178.2	175.2
80°	142.9	146.2	144.6	142.8	141.2
82.5°	107.5	110.8	110.6	107.5	107.2
85°	56.1	61.1	61.2	61.2	61.2
87.5°	15.7	22.3	26.3	26.7	27.7
90°	3.5	10.3	22.6	24.3	22.6
92.5°	49.4	180.0	355.1	154.1	111.6
95°	116.5	408.9	1248.5	646.1	384.3
97.5°	187.1	469.0	1946.1	1610.6	1182.8
100°	240.0	493.3	2163.2	2255.9	1824.1
102.5°	288.7	527.0	2239.7	2745.3	2422.3
105°	377.3	583.1	2251.8	3321.6	3185.6
107.5°	459.4	647.1	2153.4	3681.2	3726.4
110°	523.4	693.4	2065.8	3777.7	3969.9



TEST NUMBER: P563800

CATALOG NUMBER: SQ4-PP3-150U-075D-940-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	580.4	739.6	1985.1	3758.4	4081.1
115°	664.3	812.2	1867.6	3615.3	4081.1
117.5°	746.3	885.1	1790.0	3396.5	3924.6
120°	796.4	932.4	1744.1	3239.6	3778.6
122.5°	843.7	977.0	1716.3	3071.4	3614.4
125°	909.4	1042.1	1683.2	2840.4	3336.9
127.5°	969.9	1100.2	1663.8	2652.0	3088.6
130°	1003.3	1137.6	1655.4	2535.6	2930.0
132.5°	1038.1	1171.1	1647.1	2430.5	2793.7
135°	1090.3	1219.5	1638.0	2293.5	2596.1
137.5°	1142.8	1264.9	1630.4	2182.3	2428.9
140°	1179.0	1292.9	1627.6	2110.8	2330.1
142.5°	1213.7	1320.8	1622.0	2046.2	2238.3
145°	1267.6	1362.9	1615.4	1963.1	2112.7
147.5°	1316.7	1401.0	1607.8	1887.9	2002.8
150°	1352.8	1427.7	1605.0	1847.0	1938.8
152.5°	1386.2	1451.5	1603.6	1809.1	1884.6
155°	1431.1	1487.2	1601.5	1761.1	1818.9
157.5°	1477.7	1516.8	1601.9	1727.6	1765.7
160°	1504.1	1536.4	1603.2	1706.5	1733.7
162.5°	1525.0	1551.9	1604.6	1689.6	1710.0
165°	1558.0	1573.3	1608.5	1671.3	1679.8
167.5°	1580.6	1591.2	1608.8	1655.5	1659.6
170°	1594.5	1599.6	1610.2	1648.5	1648.5
172.5°	1605.7	1606.7	1610.2	1640.1	1638.7
175°	1617.2	1615.5	1610.2	1631.0	1627.6
177.5°	1621.0	1616.9	1609.9	1623.7	1619.6
180°	1615.4	1615.4	1615.4	1615.4	1615.4

(END OF REPORT)