

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P520905

Luminaire Tested: SQ4-025U-0D-92765-1D-UNV-STD-W-4_6500K

Issue Date: 5-5-2021

Test Information

Test Method: LM-79-2019
Report Number: P520905
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51)
Test Lab: INNOVATION CENTER
Issue Date: 5-5-2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-025U-0D-92765-1D-UNV-STD-W-4_6500K
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE
INDIRECT ONLY
UPLIGHT 250 LUMENS PER FOOT
Light Source: 2700K-6500K CCT, 90 CRI LEDS, TUNED TO 6500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2074.5 lumens
Efficiency: N/A
Efficacy: 149.2 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Indirect


Input Watts (W): 13.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P520905

CATALOG NUMBER: SQ4-025U-0D-92765-1D-UNV-STD-W-4_6500K

Luminous Intensity Polar Plot



TEST NUMBER: P520905

CATALOG NUMBER: SQ4-025U-0D-92765-1D-UNV-STD-W-4_6500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	0
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	0

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 0°
 Luminance: 0 cd/sqm

TEST NUMBER: P520905

CATALOG NUMBER: SQ4-025U-0D-92765-1D-UNV-STD-W-4_6500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	152.2	7.3
100°-110°	433.0	20.9
110°-120°	414.9	20.0
120°-130°	328.4	15.8
130°-140°	263.6	12.7
140°-150°	206.3	9.9
150°-160°	151.0	7.3
160°-170°	93.5	4.5
170°-180°	31.7	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	1000.1	48.2
90°-150°	1798.3	86.7
90°-180°	2075.0	100.0
0°-180°	2074.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	1
95°	16	66	295	102	63	19
105°	67	102	441	779	741	71
115°	125	151	335	709	832	123
125°	176	196	319	530	634	158
135°	216	234	316	448	506	167
145°	255	268	318	388	422	159
155°	291	298	326	350	364	134
165°	321	322	330	337	342	90
175°	336	335	333	331	329	32
180°	334	334	334	334	334	

TEST NUMBER: P520905

CATALOG NUMBER: SQ4-025U-0D-92765-1D-UNV-STD-W-4_6500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0
92.5°	5.1	26.9	62.5	18.2	13.7
95°	16.5	65.6	294.6	102.0	62.9
97.5°	30.3	76.8	453.7	324.7	222.5
100°	40.0	83.5	488.3	494.6	381.0
102.5°	50.7	90.6	480.6	633.0	533.8
105°	67.3	102.1	441.3	779.4	740.9
107.5°	84.2	115.4	395.3	820.7	855.0
110°	95.9	125.1	368.9	804.9	881.9

TEST NUMBER: P520905

CATALOG NUMBER: SQ4-025U-0D-92765-1D-UNV-STD-W-4_6500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	107.0	134.7	351.1	767.6	877.3
115°	125.1	151.2	334.6	708.8	832.4
117.5°	141.0	165.4	324.8	644.6	775.5
120°	153.7	174.1	323.8	607.9	733.3
122.5°	163.8	184.3	321.3	575.7	692.2
125°	176.5	195.8	319.4	530.0	633.6
127.5°	190.3	208.4	318.3	502.6	588.1
130°	197.5	215.5	316.8	483.6	558.1
132.5°	205.1	222.6	316.8	468.7	537.3
135°	215.9	233.9	315.6	447.7	506.0
137.5°	226.0	243.5	315.4	429.8	480.3
140°	233.7	251.7	314.9	415.1	463.5
142.5°	242.3	257.3	316.4	403.3	446.7
145°	254.6	267.6	318.1	387.5	422.2
147.5°	265.1	277.8	320.9	371.5	401.5
150°	274.3	283.0	321.9	366.2	387.3
152.5°	281.4	290.6	322.9	359.0	378.7
155°	290.8	297.6	325.7	350.2	364.4
157.5°	302.5	306.6	326.3	346.1	356.3
160°	308.6	311.7	328.9	343.1	351.7
162.5°	312.1	315.7	329.4	340.5	347.2
165°	321.3	322.5	329.5	336.6	341.6
167.5°	327.5	326.4	332.4	335.7	337.6
170°	329.5	328.9	331.4	332.1	334.6
172.5°	334.1	332.0	333.0	331.1	333.1
175°	336.5	334.6	333.3	331.4	328.9
177.5°	337.5	334.5	333.0	330.9	331.4
180°	334.0	334.0	334.0	334.0	334.0

(END OF REPORT)