

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P520916

Luminaire Tested: SQ4-050U-0D-92765-1D-UNV-STD-W-4\_5000K

Issue Date: 5-5-2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P520916  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51)  
Test Lab: INNOVATION CENTER  
Issue Date: 5-5-2021  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ4-050U-0D-92765-1D-UNV-STD-W-4\_5000K  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE  
INDIRECT ONLY  
UPLIGHT 500 LUMENS PER FOOT  
Light Source: 2700K-6500K CCT, 90 CRI LEDS, TUNED TO 5000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2283.5 lumens  
Efficiency: N/A  
Efficacy: 144.5 lumens/watt  
Spacing Criteria (0/90/45): - / - / -  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: Indirect


Input Watts (W): 15.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P520916

CATALOG NUMBER: SQ4-050U-0D-92765-1D-UNV-STD-W-4\_5000K

### Luminous Intensity Polar Plot



TEST NUMBER: P520916

CATALOG NUMBER: SQ4-050U-0D-92765-1D-UNV-STD-W-4\_5000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	0
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	0

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 0°  
 Luminance: 0 cd/sqm

TEST NUMBER: P520916

CATALOG NUMBER: SQ4-050U-0D-92765-1D-UNV-STD-W-4\_5000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	167.5	7.3
100°-110°	476.6	20.9
110°-120°	456.7	20.0
120°-130°	361.4	15.8
130°-140°	290.1	12.7
140°-150°	227.1	9.9
150°-160°	166.2	7.3
160°-170°	102.9	4.5
170°-180°	34.9	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	1100.8	48.2
90°-150°	1979.5	86.7
90°-180°	2283.0	100.0
0°-180°	2283.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	1
95°	18	72	324	112	69	21
105°	74	112	486	858	816	78
115°	138	166	368	780	916	136
125°	194	216	352	583	698	174
135°	238	257	347	493	557	183
145°	280	295	350	426	465	175
155°	320	328	358	385	401	148
165°	354	355	363	370	376	99
175°	370	368	367	365	362	35
180°	368	368	368	368	368	

TEST NUMBER: P520916

CATALOG NUMBER: SQ4-050U-0D-92765-1D-UNV-STD-W-4\_5000K

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0
92.5°	5.6	29.6	68.8	20.0	15.1
95°	18.2	72.2	324.3	112.2	69.2
97.5°	33.4	84.5	499.4	357.4	244.9
100°	44.0	91.9	537.4	544.4	419.3
102.5°	55.8	99.8	529.1	696.8	587.6
105°	74.1	112.3	485.7	858.0	815.6
107.5°	92.7	127.0	435.1	903.4	941.1
110°	105.5	137.6	406.1	886.0	970.8

TEST NUMBER: P520916

CATALOG NUMBER: SQ4-050U-0D-92765-1D-UNV-STD-W-4\_5000K

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	117.8	148.3	386.5	844.9	965.7
115°	137.7	166.4	368.3	780.3	916.2
117.5°	155.2	182.1	357.6	709.6	853.6
120°	169.1	191.7	356.4	669.2	807.2
122.5°	180.3	202.9	353.6	633.7	761.9
125°	194.3	215.5	351.5	583.4	697.5
127.5°	209.5	229.3	350.4	553.3	647.3
130°	217.4	237.2	348.7	532.3	614.3
132.5°	225.7	245.0	348.7	516.0	591.4
135°	237.6	257.4	347.3	492.8	557.0
137.5°	248.8	268.1	347.2	473.1	528.6
140°	257.2	277.0	346.6	456.9	510.2
142.5°	266.7	283.2	348.3	443.9	491.7
145°	280.3	294.6	350.1	426.5	464.8
147.5°	291.9	305.8	353.2	408.9	442.0
150°	301.9	311.5	354.3	403.1	426.3
152.5°	309.7	319.9	355.5	395.2	416.8
155°	320.1	327.6	358.5	385.4	401.2
157.5°	332.9	337.5	359.2	381.0	392.2
160°	339.7	343.1	362.0	377.6	387.2
162.5°	343.6	347.5	362.6	374.8	382.2
165°	353.6	355.0	362.7	370.5	376.0
167.5°	360.5	359.3	365.9	369.5	371.7
170°	362.7	362.0	364.8	365.6	368.3
172.5°	367.8	365.4	366.5	364.4	366.6
175°	370.4	368.4	366.9	364.8	362.0
177.5°	371.5	368.2	366.5	364.3	364.8
180°	367.6	367.6	367.6	367.6	367.6

(END OF REPORT)