

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P520917

Luminaire Tested: SQ4-050U-0D-92765-1D-UNV-STD-W-4\_5700K

Issue Date: 5-5-2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P520917  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51)  
Test Lab: INNOVATION CENTER  
Issue Date: 5-5-2021  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ4-050U-0D-92765-1D-UNV-STD-W-4\_5700K  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE  
INDIRECT ONLY  
UPLIGHT 500 LUMENS PER FOOT  
Light Source: 2700K-6500K CCT, 90 CRI LEDS, TUNED TO 5700K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2316.0 lumens  
Efficiency: N/A  
Efficacy: 146.6 lumens/watt  
Spacing Criteria (0/90/45): - / - / -  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: Indirect


Input Watts (W): 15.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P520917

CATALOG NUMBER: SQ4-050U-0D-92765-1D-UNV-STD-W-4\_5700K

### Luminous Intensity Polar Plot



TEST NUMBER: P520917

CATALOG NUMBER: SQ4-050U-0D-92765-1D-UNV-STD-W-4\_5700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	0
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	0

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 0°  
 Luminance: 0 cd/sqm

TEST NUMBER: P520917

CATALOG NUMBER: SQ4-050U-0D-92765-1D-UNV-STD-W-4\_5700K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	169.9	7.3
100°-110°	483.4	20.9
110°-120°	463.2	20.0
120°-130°	366.6	15.8
130°-140°	294.2	12.7
140°-150°	230.4	9.9
150°-160°	168.5	7.3
160°-170°	104.4	4.5
170°-180°	35.4	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	1116.5	48.2
90°-150°	2007.7	86.7
90°-180°	2316.0	100.0
0°-180°	2316.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	1
95°	18	73	329	114	70	21
105°	75	114	493	870	827	79
115°	140	169	374	791	929	137
125°	197	218	356	592	707	176
135°	241	261	352	500	565	186
145°	284	299	355	433	471	178
155°	325	332	364	391	407	150
165°	359	360	368	376	381	101
175°	376	374	372	370	367	36
180°	373	373	373	373	373	

TEST NUMBER: P520917

CATALOG NUMBER: SQ4-050U-0D-92765-1D-UNV-STD-W-4\_5700K

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0
92.5°	5.7	30.1	69.8	20.3	15.3
95°	18.4	73.2	328.9	113.8	70.2
97.5°	33.9	85.7	506.5	362.5	248.4
100°	44.7	93.2	545.1	552.1	425.3
102.5°	56.6	101.2	536.6	706.7	596.0
105°	75.1	114.0	492.6	870.2	827.2
107.5°	94.0	128.8	441.3	916.3	954.5
110°	107.0	139.6	411.8	898.6	984.6

TEST NUMBER: P520917

CATALOG NUMBER: SQ4-050U-0D-92765-1D-UNV-STD-W-4\_5700K

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	119.5	150.4	392.0	856.9	979.5
115°	139.6	168.8	373.6	791.4	929.3
117.5°	157.4	184.7	362.6	719.7	865.8
120°	171.5	194.4	361.5	678.7	818.7
122.5°	182.9	205.8	358.7	642.8	772.8
125°	197.1	218.5	356.5	591.7	707.4
127.5°	212.5	232.6	355.4	561.2	656.5
130°	220.4	240.5	353.7	539.9	623.1
132.5°	229.0	248.5	353.7	523.3	599.8
135°	241.0	261.1	352.3	499.8	564.9
137.5°	252.3	271.9	352.2	479.9	536.2
140°	260.9	281.0	351.6	463.4	517.5
142.5°	270.5	287.3	353.3	450.2	498.7
145°	284.2	298.8	355.1	432.6	471.4
147.5°	296.0	310.2	358.2	414.7	448.3
150°	306.2	315.9	359.4	408.8	432.4
152.5°	314.2	324.4	360.5	400.9	422.8
155°	324.6	332.3	363.6	390.9	406.9
157.5°	337.7	342.3	364.3	386.4	397.8
160°	344.5	348.0	367.2	383.0	392.7
162.5°	348.5	352.5	367.7	380.1	387.6
165°	358.7	360.1	367.9	375.8	381.4
167.5°	365.6	364.4	371.1	374.7	377.0
170°	367.9	367.2	370.0	370.8	373.6
172.5°	373.0	370.6	371.7	369.6	371.9
175°	375.7	373.6	372.1	370.0	367.2
177.5°	376.8	373.5	371.7	369.5	370.0
180°	372.9	372.9	372.9	372.9	372.9

(END OF REPORT)