

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P564616

Luminaire Tested: **SQ4-PW1-025U-125D-940-1D-UNV-STD-W-8**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P564616  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-32, G2-2106-289-3)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PW1-025U-125D-940-1D-UNV-STD-W-8  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS.  
DOWNLIGHT 1250 LUMENS PER FOOT  
UPLIGHT 250 LUMENS PER FOOT  
Light Source: 4000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 10019.1 lumens  
Efficiency: N/A  
Efficacy: 98.6 lumens/watt  
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31  
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 101.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P564616  
CATALOG NUMBER: SQ4-PW1-025U-125D-940-1D-UNV-STD-W-8

### Luminous Intensity Polar Plot





TEST NUMBER: P564616

CATALOG NUMBER: SQ4-PW1-025U-125D-940-1D-UNV-STD-W-8

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	115	115	115	115	110	110	110	110	102	102	102	94	94	94	87	87	87	83
1	105	101	97	93	101	97	93	90	90	87	84	83	81	79	77	75	74	70
2	96	88	82	77	92	85	79	74	79	74	70	73	69	66	68	65	62	59
3	88	78	70	64	84	75	68	62	70	64	59	65	60	56	60	56	53	50
4	81	69	61	54	77	67	59	53	62	56	51	58	53	48	54	49	46	43
5	74	62	53	47	71	60	52	46	56	49	44	52	46	42	49	44	40	38
6	68	56	47	41	65	54	46	40	50	44	39	47	41	37	44	39	35	33
7	63	50	42	36	61	49	41	36	46	39	34	43	37	33	40	35	31	29
8	59	46	38	32	57	45	37	32	42	35	31	39	34	29	37	32	28	26
9	55	42	34	29	53	41	34	29	39	32	28	36	31	27	34	29	26	24
10	52	39	31	26	50	38	31	26	36	29	25	34	28	24	32	27	23	21

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	15105	15105	15105
5°	15203	15083	15016
10°	15081	14960	14879
15°	14922	14756	14701
20°	14743	14516	14488
25°	14538	14273	14229
30°	14230	14015	13923
35°	13826	13631	13550
40°	13395	13186	13134
45°	12874	12704	12648
50°	12340	12236	12153
55°	11763	11763	11578
60°	11046	11259	10859
65°	10109	10612	9857
70°	8910	9767	8677
75°	7611	8741	7404
80°	5900	7359	5977
85°	3816	5648	5039



TEST NUMBER: P564616

CATALOG NUMBER: SQ4-PW1-025U-125D-940-1D-UNV-STD-W-8

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	308.3	3.1
10°-20°	870.5	8.7
20°-30°	1291.3	12.9
30°-40°	1510.9	15.1
40°-50°	1504.2	15.0
50°-60°	1298.9	13.0
60°-70°	935.0	9.3
70°-80°	490.3	4.9
80°-90°	122.9	1.2
90°-100°	126.8	1.3
100°-110°	333.5	3.3
110°-120°	345.8	3.5
120°-130°	277.3	2.8
130°-140°	217.6	2.2
140°-150°	167.0	1.7
150°-160°	120.3	1.2
160°-170°	73.6	0.7
170°-180°	24.9	0.2
0°-30°	2470.1	24.7
0°-40°	3981.0	39.7
0°-60°	6784.0	67.7
0°-90°	8332.2	83.2
90°-120°	806.1	8.0
90°-150°	1468.1	14.7
90°-180°	1687.0	16.8
0°-180°	10019.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	3274	3274	3274	3274	3274	
5°	3283	3246	3257	3248	3243	311
15°	3124	3085	3090	3084	3078	881
25°	2856	2808	2804	2787	2796	1313
35°	2455	2421	2420	2398	2406	1535
45°	1973	1956	1947	1942	1939	1523
55°	1463	1460	1463	1442	1440	1305
65°	926	954	972	934	903	918
75°	427	466	490	458	415	458
85°	72	95	107	101	95	95
90°	2	5	13	7	7	4
95°	17	66	218	113	77	19
105°	60	91	369	560	522	64
115°	107	130	295	589	672	105
125°	148	166	269	454	536	132
135°	177	195	260	366	415	137
145°	205	218	257	312	337	129
155°	232	238	257	282	290	107
165°	250	254	257	267	270	71
175°	260	260	259	262	262	25
180°	260	260	260	260	260	



TEST NUMBER: P564616

CATALOG NUMBER: SQ4-PW1-025U-125D-940-1D-UNV-STD-W-8

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	3274.4	3274.4	3274.4	3274.4	3274.4
2.5°	3292.8	3265.8	3274.4	3267.1	3251.3
5°	3283.0	3246.4	3257.1	3248.3	3242.6
7.5°	3249.6	3215.7	3223.6	3214.3	3210.9
10°	3219.6	3185.7	3193.6	3181.9	3176.3
12.5°	3184.9	3148.8	3156.7	3145.1	3141.7
15°	3124.4	3084.9	3089.7	3083.8	3078.2
17.5°	3054.0	3013.9	3014.7	3005.5	3004.3
20°	3003.2	2960.9	2957.0	2945.6	2951.3
22.5°	2947.8	2903.2	2899.3	2883.4	2891.3
25°	2856.1	2808.1	2804.1	2787.0	2795.5
27.5°	2749.9	2702.5	2702.6	2678.6	2687.6
30°	2671.4	2626.3	2631.0	2602.4	2613.7
32.5°	2588.3	2547.7	2550.3	2521.7	2533.0
35°	2455.1	2421.2	2420.4	2397.6	2406.0
37.5°	2318.9	2289.0	2284.3	2271.1	2273.3
40°	2224.3	2198.9	2189.6	2181.0	2181.0
42.5°	2125.0	2101.9	2092.7	2086.3	2084.1
45°	1973.3	1956.4	1947.3	1941.5	1938.7
47.5°	1823.3	1807.5	1799.6	1795.5	1792.7
50°	1719.4	1708.1	1705.0	1696.3	1693.4
52.5°	1615.5	1608.8	1605.7	1594.7	1591.9
55°	1462.6	1459.8	1462.6	1442.4	1439.6
57.5°	1303.4	1307.9	1317.2	1290.0	1283.2
60°	1197.2	1208.5	1220.3	1188.3	1177.0
62.5°	1088.8	1106.8	1123.4	1086.7	1070.9
65°	926.1	954.3	972.2	934.0	903.0
67.5°	769.1	804.1	825.7	784.5	749.5
70°	660.6	700.1	724.1	682.8	643.3
72.5°	566.0	610.0	629.5	590.5	551.0
75°	427.0	466.5	490.4	457.7	415.4
77.5°	302.9	340.2	360.0	331.5	296.6
80°	222.1	261.6	277.0	253.2	225.0
82.5°	157.5	190.2	200.8	186.5	167.3
85°	72.1	94.7	106.7	100.8	95.2
87.5°	18.8	35.2	46.5	45.2	47.5
90°	1.7	4.9	13.3	6.7	6.7
92.5°	7.0	33.8	74.7	33.1	21.4
95°	16.7	65.6	218.5	112.6	76.7
97.5°	29.0	72.1	327.0	260.0	191.5
100°	38.4	77.5	360.3	365.2	283.6
102.5°	46.4	82.9	369.7	454.9	385.0
105°	60.1	91.1	368.7	559.7	522.2
107.5°	74.1	102.8	347.7	614.1	623.3
110°	83.4	109.5	330.3	628.2	667.3

TEST NUMBER: P564616

CATALOG NUMBER: SQ4-PW1-025U-125D-940-1D-UNV-STD-W-8

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	92.8	117.6	314.3	619.3	679.3
115°	106.8	129.6	295.3	589.1	672.3
117.5°	120.4	141.3	282.3	547.3	639.6
120°	128.5	148.0	276.9	519.2	608.9
122.5°	136.5	156.0	272.9	491.1	579.6
125°	148.5	166.4	268.6	454.0	535.5
127.5°	158.2	176.4	264.9	424.0	492.8
130°	163.5	183.1	263.6	405.2	468.8
132.5°	168.8	188.4	262.3	389.0	446.1
135°	176.8	194.8	260.3	366.5	415.4
137.5°	185.2	202.8	259.9	349.6	389.7
140°	191.9	208.2	258.6	336.2	373.7
142.5°	197.2	212.2	258.6	326.7	359.0
145°	205.2	218.2	256.9	312.5	337.0
147.5°	213.2	225.9	256.9	300.7	321.0
150°	218.5	230.0	256.9	294.0	310.3
152.5°	223.9	232.7	256.9	288.6	301.0
155°	231.9	238.4	256.9	282.1	290.3
157.5°	237.9	244.1	256.9	276.4	282.3
160°	241.9	246.8	256.9	273.7	276.9
162.5°	245.9	249.5	256.9	271.0	274.3
165°	250.2	253.5	256.9	267.0	270.3
167.5°	254.2	255.9	258.6	265.3	266.6
170°	256.9	258.5	258.6	265.3	265.3
172.5°	258.2	258.6	258.6	263.9	262.6
175°	260.3	260.3	258.6	261.9	261.9
177.5°	260.3	260.3	258.9	261.6	260.3
180°	260.3	260.3	260.3	260.3	260.3

(END OF REPORT)