

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P520926

Luminaire Tested: SQ4-075U-0D-92765-1D-UNV-STD-W-4_3500K

Issue Date: 5-5-2021

Test Information

Test Method: LM-79-2019
Report Number: P520926
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51)
Test Lab: INNOVATION CENTER
Issue Date: 5-5-2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-075U-0D-92765-1D-UNV-STD-W-4_3500K
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE
INDIRECT ONLY
UPLIGHT 750 LUMENS PER FOOT
Light Source: 2700K-6500K CCT, 90 CRI LEDS, TUNED TO 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3267.4 lumens
Efficiency: N/A
Efficacy: 137.9 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Indirect


Input Watts (W): 23.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P520926

CATALOG NUMBER: SQ4-075U-0D-92765-1D-UNV-STD-W-4_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P520926

CATALOG NUMBER: SQ4-075U-0D-92765-1D-UNV-STD-W-4_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	0
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	0

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 0°
 Luminance: 0 cd/sqm

TEST NUMBER: P520926

CATALOG NUMBER: SQ4-075U-0D-92765-1D-UNV-STD-W-4_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	239.7	7.3
100°-110°	682.0	20.9
110°-120°	653.4	20.0
120°-130°	517.2	15.8
130°-140°	415.1	12.7
140°-150°	325.0	9.9
150°-160°	237.8	7.3
160°-170°	147.3	4.5
170°-180°	50.0	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	1575.1	48.2
90°-150°	2832.3	86.7
90°-180°	3267.0	100.0
0°-180°	3267.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	1
95°	26	103	464	161	99	30
105°	106	161	695	1228	1167	112
115°	197	238	527	1116	1311	194
125°	278	308	503	835	998	249
135°	340	368	497	705	797	262
145°	401	422	501	610	665	250
155°	458	469	513	552	574	212
165°	506	508	519	530	538	142
175°	530	527	525	522	518	50
180°	526	526	526	526	526	

TEST NUMBER: P520926

CATALOG NUMBER: SQ4-075U-0D-92765-1D-UNV-STD-W-4_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0
92.5°	8.0	42.4	98.4	28.6	21.6
95°	26.0	103.2	464.0	160.6	99.0
97.5°	47.8	120.9	714.6	511.3	350.4
100°	63.0	131.4	769.0	778.9	600.0
102.5°	79.8	142.8	757.0	997.0	840.8
105°	106.0	160.8	695.0	1227.6	1167.0
107.5°	132.6	181.7	622.6	1292.6	1346.6
110°	151.0	197.0	581.0	1267.8	1389.0

TEST NUMBER: P520926

CATALOG NUMBER: SQ4-075U-0D-92765-1D-UNV-STD-W-4_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	168.6	212.2	553.0	1208.9	1381.8
115°	197.0	238.1	527.0	1116.4	1311.0
117.5°	222.0	260.5	511.6	1015.3	1221.4
120°	242.0	274.3	510.0	957.5	1155.0
122.5°	258.0	290.3	506.0	906.8	1090.2
125°	278.0	308.3	503.0	834.7	998.0
127.5°	299.8	328.2	501.4	791.7	926.2
130°	311.0	339.4	499.0	761.7	879.0
132.5°	323.0	350.6	499.0	738.3	846.2
135°	340.0	368.4	497.0	705.1	797.0
137.5°	356.0	383.6	496.8	677.0	756.4
140°	368.0	396.4	496.0	653.7	730.0
142.5°	381.6	405.3	498.4	635.2	703.6
145°	401.0	421.5	501.0	610.2	665.0
147.5°	417.6	437.5	505.4	585.1	632.4
150°	432.0	445.7	507.0	576.8	610.0
152.5°	443.2	457.7	508.6	565.5	596.4
155°	458.0	468.8	513.0	551.5	574.0
157.5°	476.4	482.9	514.0	545.2	561.2
160°	486.0	490.9	518.0	540.3	554.0
162.5°	491.6	497.3	518.8	536.2	546.8
165°	506.0	508.0	519.0	530.2	538.0
167.5°	515.8	514.0	523.6	528.7	531.8
170°	519.0	518.0	522.0	523.1	527.0
172.5°	526.2	522.9	524.4	521.5	524.6
175°	530.0	527.1	525.0	521.9	518.0
177.5°	531.6	526.9	524.4	521.2	522.0
180°	526.0	526.0	526.0	526.0	526.0

(END OF REPORT)