

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P520928

Luminaire Tested: SQ4-075U-0D-92765-1D-UNV-STD-W-4\_4500K

Issue Date: 5-5-2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P520928  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51)  
Test Lab: INNOVATION CENTER  
Issue Date: 5-5-2021  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ4-075U-0D-92765-1D-UNV-STD-W-4\_4500K  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE  
INDIRECT ONLY  
UPLIGHT 750 LUMENS PER FOOT  
Light Source: 2700K-6500K CCT, 90 CRI LEDS, TUNED TO 4500K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3380.8 lumens  
Efficiency: N/A  
Efficacy: 142.6 lumens/watt  
Spacing Criteria (0/90/45): - / - / -  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: Indirect


Input Watts (W): 23.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P520928

CATALOG NUMBER: SQ4-075U-0D-92765-1D-UNV-STD-W-4\_4500K

### Luminous Intensity Polar Plot



TEST NUMBER: P520928

CATALOG NUMBER: SQ4-075U-0D-92765-1D-UNV-STD-W-4\_4500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	0
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	0

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 0°  
 Luminance: 0 cd/sqm

TEST NUMBER: P520928

CATALOG NUMBER: SQ4-075U-0D-92765-1D-UNV-STD-W-4\_4500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	248.0	7.3
100°-110°	705.7	20.9
110°-120°	676.1	20.0
120°-130°	535.1	15.8
130°-140°	429.5	12.7
140°-150°	336.2	9.9
150°-160°	246.0	7.3
160°-170°	152.4	4.5
170°-180°	51.7	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	1629.8	48.2
90°-150°	2930.6	86.7
90°-180°	3381.0	100.0
0°-180°	3380.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	1
95°	27	107	480	166	102	31
105°	110	166	719	1270	1208	116
115°	204	246	545	1155	1356	201
125°	288	319	520	864	1033	257
135°	352	381	514	730	825	271
145°	415	436	518	631	688	259
155°	474	485	531	571	594	219
165°	524	526	537	549	557	147
175°	548	545	543	540	536	52
180°	544	544	544	544	544	

TEST NUMBER: P520928

CATALOG NUMBER: SQ4-075U-0D-92765-1D-UNV-STD-W-4\_4500K

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0
92.5°	8.3	43.9	101.8	29.6	22.3
95°	26.9	106.8	480.1	166.2	102.4
97.5°	49.5	125.1	739.4	529.1	362.6
100°	65.2	136.0	795.7	806.0	620.8
102.5°	82.6	147.7	783.3	1031.7	870.0
105°	109.7	166.3	719.1	1270.2	1207.5
107.5°	137.2	188.0	644.2	1337.5	1393.4
110°	156.2	203.8	601.2	1311.8	1437.2

TEST NUMBER: P520928

CATALOG NUMBER: SQ4-075U-0D-92765-1D-UNV-STD-W-4\_4500K

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	174.5	219.6	572.2	1250.9	1429.8
115°	203.8	246.3	545.3	1155.2	1356.5
117.5°	229.7	269.6	529.4	1050.5	1263.8
120°	250.4	283.8	527.7	990.7	1195.1
122.5°	267.0	300.3	523.6	938.3	1128.1
125°	287.7	319.0	520.5	863.7	1032.7
127.5°	310.2	339.5	518.8	819.1	958.4
130°	321.8	351.1	516.3	788.1	909.5
132.5°	334.2	362.7	516.3	763.9	875.6
135°	351.8	381.1	514.3	729.6	824.7
137.5°	368.4	396.9	514.0	700.5	782.7
140°	380.8	410.1	513.2	676.4	755.3
142.5°	394.8	419.3	515.7	657.2	728.0
145°	414.9	436.2	518.4	631.4	688.1
147.5°	432.1	452.7	522.9	605.4	654.4
150°	447.0	461.2	524.6	596.8	631.2
152.5°	458.6	473.6	526.3	585.1	617.1
155°	473.9	485.0	530.8	570.7	593.9
157.5°	492.9	499.6	531.8	564.1	580.7
160°	502.9	507.9	536.0	559.1	573.2
162.5°	508.7	514.5	536.8	554.9	565.8
165°	523.6	525.6	537.0	548.6	556.7
167.5°	533.7	531.9	541.8	547.0	550.3
170°	537.0	536.0	540.1	541.3	545.3
172.5°	544.5	541.0	542.6	539.6	542.8
175°	548.4	545.4	543.2	540.0	536.0
177.5°	550.1	545.2	542.6	539.3	540.1
180°	544.3	544.3	544.3	544.3	544.3

(END OF REPORT)