

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P519759

Luminaire Tested: **SQ4-125U-0D-940-1D-UNV-STD-W-12**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P519759
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-125U-0D-940-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 12965.5 lumens
Efficiency: N/A
Efficacy: 139.4 lumens/watt
N/A
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')
CIE Type: Indirect

Input Watts (W): 93
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P519759
CATALOG NUMBER: SQ4-125U-0D-940-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P519759

CATALOG NUMBER: SQ4-125U-0D-940-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20								20				20				20
RC	80								50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
95°	5057	54348	19231
100°	5210	47714	41416
105°	5563	33259	46696
110°	5775	23121	44493
115°	6014	16961	37068
120°	6106	13361	28908
125°	6050	11221	22320
130°	5973	9842	17394
135°	5909	8846	14054
140°	5875	8114	11668
145°	5898	7540	9836
150°	5978	7087	8568
155°	6051	6754	7666
160°	6113	6523	7059
165°	6158	6362	6647
170°	6200	6248	6400
175°	6208	6176	6248



TEST NUMBER: P519759

CATALOG NUMBER: SQ4-125U-0D-940-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	939.5	7.2
100°-110°	2530.9	19.5
110°-120°	2656.1	20.5
120°-130°	2155.4	16.6
130°-140°	1690.4	13.0
140°-150°	1297.8	10.0
150°-160°	933.1	7.2
160°-170°	570.1	4.4
170°-180°	192.2	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	6126.5	47.3
90°-150°	11270.0	86.9
90°-180°	12965.0	100.0
0°-180°	12965.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
90°	5	15	31	33	33	
95°	143	511	1540	788	545	159
105°	468	728	2799	4188	3930	492
115°	826	1012	2331	4504	5094	813
125°	1128	1296	2093	3537	4163	1007
135°	1359	1516	2034	2854	3231	1049
145°	1571	1694	2008	2440	2620	985
155°	1783	1848	1990	2189	2259	821
165°	1934	1957	1998	2078	2088	545
175°	2011	2008	2001	2029	2024	191
180°	2008	2008	2008	2008	2008	



TEST NUMBER: P519759

CATALOG NUMBER: SQ4-125U-0D-940-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
90°	5.1	15.1	30.7	33.3	33.3
92.5°	62.4	220.5	436.0	209.9	145.8
95°	143.3	511.0	1540.2	787.6	545.0
97.5°	228.7	585.0	2415.7	2018.1	1521.8
100°	294.2	614.4	2694.1	2818.8	2338.5
102.5°	357.7	655.9	2786.2	3418.4	3024.1
105°	468.2	728.4	2799.0	4187.5	3929.8
107.5°	572.6	804.7	2679.8	4582.7	4649.3
110°	642.2	862.3	2571.3	4705.4	4948.1
112.5°	715.9	920.0	2466.9	4678.3	5077.1
115°	826.4	1011.5	2330.8	4503.6	5093.9
117.5°	927.2	1100.8	2225.4	4224.7	4882.1
120°	992.7	1160.3	2172.2	4024.5	4699.9
122.5°	1050.0	1215.6	2133.3	3819.8	4493.2
125°	1128.3	1295.9	2092.8	3537.2	4162.7
127.5°	1203.5	1368.6	2067.3	3288.1	3846.4
130°	1248.5	1413.6	2057.0	3145.3	3635.6
132.5°	1293.6	1456.7	2046.8	3019.5	3469.8
135°	1358.6	1516.2	2034.0	2853.6	3231.4
137.5°	1420.5	1571.6	2027.3	2712.9	3023.1
140°	1463.5	1608.5	2021.2	2626.3	2906.4
142.5°	1508.5	1643.6	2017.1	2545.4	2781.6
145°	1570.9	1693.5	2008.4	2439.8	2619.9
147.5°	1638.5	1745.0	1999.7	2350.9	2492.5
150°	1683.5	1776.0	1995.6	2295.1	2412.6
152.5°	1724.4	1805.0	1993.6	2249.5	2345.1
155°	1783.3	1848.3	1990.5	2189.1	2259.1
157.5°	1834.9	1885.5	1991.0	2146.6	2193.6
160°	1867.7	1910.2	1993.1	2121.8	2156.8
162.5°	1896.3	1930.9	1995.1	2101.1	2126.1
165°	1934.2	1956.7	1998.2	2077.7	2087.7
167.5°	1964.9	1977.9	2000.7	2059.7	2063.7
170°	1985.4	1990.4	2000.7	2049.3	2049.3
172.5°	1997.7	1998.7	2002.8	2039.1	2039.1
175°	2011.0	2008.5	2000.7	2028.8	2023.8
177.5°	2016.6	2012.6	2002.3	2018.6	2014.5
180°	2008.4	2008.4	2008.4	2008.4	2008.4

(END OF REPORT)