

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P519783

Luminaire Tested: **SQ4-150U-0D-940-1D-UNV-STD-W-12**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P519783
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-25)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-150U-0D-940-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 15622.8 lumens
Efficiency: N/A
Efficacy: 135.3 lumens/watt
N/A
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')
CIE Type: Indirect

Input Watts (W): 115.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P519783
CATALOG NUMBER: SQ4-150U-0D-940-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P519783

CATALOG NUMBER: SQ4-150U-0D-940-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20								20				20				20				20
RC	80								50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10				0
RCR																					
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10				0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8				0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7				0
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6				0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5				0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4				0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4				0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3				0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3				0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3				0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2				0

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
95°	6168	66084	20339
100°	6374	57465	48458
105°	6725	40136	56779
110°	7060	27863	53545
115°	7251	20385	44548
120°	7348	16091	34862
125°	7314	13537	26838
130°	7201	11880	21028
135°	7113	10686	16937
140°	7100	9801	14032
145°	7139	9097	11898
150°	7206	8549	10328
155°	7284	8152	9258
160°	7384	7871	8511
165°	7441	7682	8022
170°	7469	7543	7722
175°	7488	7456	7537



TEST NUMBER: P519783

CATALOG NUMBER: SQ4-150U-0D-940-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	1126.1	7.2
100°-110°	3044.8	19.5
110°-120°	3201.2	20.5
120°-130°	2600.2	16.6
130°-140°	2039.6	13.1
140°-150°	1565.4	10.0
150°-160°	1125.8	7.2
160°-170°	687.8	4.4
170°-180°	231.9	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	7372.0	47.2
90°-150°	13577.3	86.9
90°-180°	15623.0	100.0
0°-180°	15622.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
90°	5	15	34	36	34	
95°	175	613	1873	969	576	194
105°	566	875	3378	4982	4778	596
115°	996	1218	2801	5423	6122	984
125°	1364	1563	2525	4261	5005	1216
135°	1635	1829	2457	3440	3894	1264
145°	1902	2044	2423	2945	3169	1190
155°	2147	2231	2402	2642	2728	990
165°	2337	2360	2413	2507	2520	658
175°	2426	2423	2415	2446	2441	230
180°	2423	2423	2423	2423	2423	



TEST NUMBER: P519783

CATALOG NUMBER: SQ4-150U-0D-940-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
90°	5.2	15.4	33.9	36.5	33.9
92.5°	74.1	269.9	532.6	231.2	167.5
95°	174.8	613.4	1872.8	969.2	576.4
97.5°	280.7	703.5	2919.2	2415.8	1774.2
100°	359.9	739.9	3244.7	3383.9	2736.1
102.5°	433.0	790.5	3359.5	4117.9	3633.4
105°	566.0	874.6	3377.8	4982.5	4778.4
107.5°	689.1	970.7	3230.1	5521.8	5589.6
110°	785.1	1040.1	3098.7	5666.6	5954.8
112.5°	870.7	1109.4	2977.7	5637.7	6121.7
115°	996.4	1218.3	2801.3	5422.9	6121.7
117.5°	1119.5	1327.6	2685.0	5094.8	5887.0
120°	1194.6	1398.6	2616.1	4859.4	5667.9
122.5°	1265.6	1465.5	2574.4	4607.1	5421.6
125°	1364.1	1563.1	2524.8	4260.7	5005.4
127.5°	1454.9	1650.3	2495.6	3978.0	4632.9
130°	1505.0	1706.5	2483.1	3803.3	4395.0
132.5°	1557.2	1756.6	2470.6	3645.8	4190.5
135°	1635.4	1829.2	2457.0	3440.2	3894.2
137.5°	1714.2	1897.3	2445.6	3273.5	3643.3
140°	1768.4	1939.3	2441.4	3166.1	3495.1
142.5°	1820.6	1981.3	2433.0	3069.2	3357.4
145°	1901.5	2044.3	2423.1	2944.7	3169.1
147.5°	1975.0	2101.5	2411.6	2831.9	3004.3
150°	2029.3	2141.5	2407.5	2770.6	2908.3
152.5°	2079.3	2177.3	2405.4	2713.7	2826.9
155°	2146.6	2230.8	2402.3	2641.6	2728.3
157.5°	2216.5	2275.2	2402.8	2591.4	2648.5
160°	2256.2	2304.6	2404.9	2559.7	2600.5
162.5°	2287.5	2327.8	2407.0	2534.4	2565.0
165°	2337.0	2360.0	2412.7	2506.9	2519.6
167.5°	2371.0	2386.8	2413.2	2483.3	2489.4
170°	2391.8	2399.5	2415.3	2472.7	2472.7
172.5°	2408.5	2410.0	2415.3	2460.1	2458.1
175°	2425.7	2423.2	2415.3	2446.5	2441.4
177.5°	2431.5	2425.3	2414.8	2435.5	2429.4
180°	2423.1	2423.1	2423.1	2423.1	2423.1

(END OF REPORT)