

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P520952

Luminaire Tested: SQ4-125U-0D-92765-1D-UNV-STD-W-4\_3500K

Issue Date: 5-5-2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P520952  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51)  
Test Lab: INNOVATION CENTER  
Issue Date: 5-5-2021  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ4-125U-0D-92765-1D-UNV-STD-W-4\_3500K  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE  
INDIRECT ONLY  
UPLIGHT 1250 LUMENS PER FOOT  
Light Source: 2700K-6500K CCT, 90 CRI LEDS, TUNED TO 3500K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5491.8 lumens  
Efficiency: N/A  
Efficacy: 132.3 lumens/watt  
Spacing Criteria (0/90/45): - / - / -  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: Indirect

Input Watts (W): 41.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P520952  
CATALOG NUMBER: SQ4-125U-0D-92765-1D-UNV-STD-W-4\_3500K

### Luminous Intensity Polar Plot



TEST NUMBER: P520952

CATALOG NUMBER: SQ4-125U-0D-92765-1D-UNV-STD-W-4\_3500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	0
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	0

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 0°  
 Luminance: 0 cd/sqm

TEST NUMBER: P520952

CATALOG NUMBER: SQ4-125U-0D-92765-1D-UNV-STD-W-4\_3500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	402.9	7.3
100°-110°	1146.3	20.9
110°-120°	1098.3	20.0
120°-130°	869.3	15.8
130°-140°	697.7	12.7
140°-150°	546.2	9.9
150°-160°	399.7	7.3
160°-170°	247.6	4.5
170°-180°	84.0	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	2647.5	48.2
90°-150°	4760.6	86.7
90°-180°	5492.0	100.0
0°-180°	5491.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	2
95°	44	174	780	270	166	50
105°	178	270	1168	2063	1962	188
115°	331	400	886	1876	2204	326
125°	467	518	846	1403	1678	418
135°	572	619	835	1185	1340	441
145°	674	708	842	1026	1118	421
155°	770	788	862	927	965	356
165°	850	854	872	891	904	239
175°	891	886	882	877	871	84
180°	884	884	884	884	884	

TEST NUMBER: P520952

CATALOG NUMBER: SQ4-125U-0D-92765-1D-UNV-STD-W-4\_3500K

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0
92.5°	13.4	71.3	165.4	48.1	36.3
95°	43.7	173.5	779.9	269.9	166.4
97.5°	80.3	203.3	1201.1	859.5	589.0
100°	105.9	220.9	1292.6	1309.2	1008.5
102.5°	134.1	240.0	1272.4	1675.9	1413.2
105°	178.2	270.2	1168.2	2063.4	1961.5
107.5°	222.9	305.4	1046.5	2172.7	2263.4
110°	253.8	331.0	976.6	2130.9	2334.7

TEST NUMBER: P520952

CATALOG NUMBER: SQ4-125U-0D-92765-1D-UNV-STD-W-4\_3500K

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	283.4	356.7	929.5	2032.0	2322.6
115°	331.1	400.1	885.8	1876.5	2203.6
117.5°	373.1	437.9	859.9	1706.5	2053.0
120°	406.8	461.0	857.2	1609.4	1941.3
122.5°	433.7	487.9	850.5	1524.1	1832.4
125°	467.3	518.2	845.5	1403.0	1677.5
127.5°	503.9	551.6	842.8	1330.6	1556.8
130°	522.7	570.4	838.7	1280.2	1477.4
132.5°	542.9	589.3	838.7	1240.9	1422.3
135°	571.5	619.1	835.4	1185.1	1339.6
137.5°	598.4	644.7	835.0	1137.9	1271.4
140°	618.5	666.2	833.7	1098.8	1227.0
142.5°	641.4	681.2	837.7	1067.6	1182.6
145°	674.0	708.5	842.1	1025.7	1117.7
147.5°	701.9	735.4	849.5	983.4	1063.0
150°	726.1	749.1	852.2	969.4	1025.3
152.5°	744.9	769.3	854.9	950.5	1002.4
155°	769.8	787.9	862.3	927.0	964.8
157.5°	800.7	811.6	863.9	916.3	943.3
160°	816.9	825.1	870.7	908.2	931.2
162.5°	826.3	835.8	872.0	901.3	919.1
165°	850.5	853.8	872.3	891.1	904.3
167.5°	867.0	864.0	880.1	888.6	893.9
170°	872.3	870.7	877.4	879.2	885.8
172.5°	884.4	878.9	881.4	876.5	881.8
175°	890.8	885.9	882.4	877.2	870.7
177.5°	893.5	885.6	881.4	876.1	877.4
180°	884.1	884.1	884.1	884.1	884.1

(END OF REPORT)