

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P520954

Luminaire Tested: SQ4-125U-0D-92765-1D-UNV-STD-W-4_4500K

Issue Date: 5-5-2021

Test Information

Test Method: LM-79-2019
Report Number: P520954
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51)
Test Lab: INNOVATION CENTER
Issue Date: 5-5-2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-125U-0D-92765-1D-UNV-STD-W-4_4500K
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE
INDIRECT ONLY
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 2700K-6500K CCT, 90 CRI LEDS, TUNED TO 4500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5682.5 lumens
Efficiency: N/A
Efficacy: 137.3 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Indirect


Input Watts (W): 41.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P520954

CATALOG NUMBER: SQ4-125U-0D-92765-1D-UNV-STD-W-4_4500K

Luminous Intensity Polar Plot



TEST NUMBER: P520954

CATALOG NUMBER: SQ4-125U-0D-92765-1D-UNV-STD-W-4_4500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	0
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	0

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 0°
 Luminance: 0 cd/sqm

TEST NUMBER: P520954

CATALOG NUMBER: SQ4-125U-0D-92765-1D-UNV-STD-W-4_4500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	416.8	7.3
100°-110°	1186.1	20.9
110°-120°	1136.4	20.0
120°-130°	899.4	15.8
130°-140°	721.9	12.7
140°-150°	565.2	9.9
150°-160°	413.5	7.3
160°-170°	256.2	4.5
170°-180°	86.9	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	2739.4	48.2
90°-150°	4925.9	86.7
90°-180°	5682.0	100.0
0°-180°	5682.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	2
95°	45	180	807	279	172	52
105°	184	280	1209	2135	2030	195
115°	343	414	916	1942	2280	337
125°	484	536	875	1452	1736	433
135°	591	641	864	1226	1386	456
145°	697	733	871	1061	1157	436
155°	796	815	892	959	998	368
165°	880	883	903	922	936	247
175°	922	917	913	908	901	87
180°	915	915	915	915	915	

TEST NUMBER: P520954

CATALOG NUMBER: SQ4-125U-0D-92765-1D-UNV-STD-W-4_4500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0
92.5°	13.9	73.8	171.1	49.8	37.6
95°	45.2	179.6	807.0	279.3	172.2
97.5°	83.1	210.3	1242.8	889.3	609.4
100°	109.6	228.6	1337.4	1354.7	1043.5
102.5°	138.8	248.3	1316.6	1734.0	1462.3
105°	184.4	279.6	1208.7	2135.1	2029.6
107.5°	230.6	316.0	1082.8	2248.1	2342.0
110°	262.6	342.5	1010.5	2204.9	2415.7

TEST NUMBER: P520954

CATALOG NUMBER: SQ4-125U-0D-92765-1D-UNV-STD-W-4_4500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	293.2	369.1	961.8	2102.5	2403.2
115°	342.6	414.0	916.5	1941.7	2280.1
117.5°	386.1	453.1	889.8	1765.8	2124.2
120°	420.9	477.0	887.0	1665.2	2008.8
122.5°	448.7	504.8	880.0	1577.0	1896.1
125°	483.5	536.2	874.8	1451.7	1735.7
127.5°	521.4	570.7	872.0	1376.8	1610.8
130°	540.9	590.2	867.9	1324.7	1528.7
132.5°	561.8	609.7	867.9	1284.0	1471.7
135°	591.3	640.6	864.4	1226.3	1386.1
137.5°	619.1	667.1	864.0	1177.4	1315.5
140°	640.0	689.3	862.6	1137.0	1269.6
142.5°	663.7	704.8	866.8	1104.6	1223.7
145°	697.4	733.1	871.3	1061.3	1156.6
147.5°	726.3	761.0	879.0	1017.6	1099.9
150°	751.3	775.1	881.8	1003.1	1060.9
152.5°	770.8	796.0	884.5	983.5	1037.2
155°	796.5	815.2	892.2	959.2	998.3
157.5°	828.5	839.8	893.9	948.1	976.0
160°	845.2	853.7	900.9	939.7	963.5
162.5°	855.0	864.8	902.3	932.6	951.0
165°	880.0	883.4	902.6	922.1	935.7
167.5°	897.1	894.0	910.6	919.5	924.9
170°	902.6	900.9	907.9	909.7	916.5
172.5°	915.2	909.4	912.0	906.9	912.4
175°	921.8	916.7	913.1	907.7	900.9
177.5°	924.5	916.4	912.0	906.5	907.9
180°	914.8	914.8	914.8	914.8	914.8

(END OF REPORT)