

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P520383

Luminaire Tested: **SQ4-F-150U-050D-940-1D-UNV-STD-W-12**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P520383
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-25, G3-1910-536-17)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-F-150U-050D-940-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 20841.5 lumens
Efficiency: N/A
Efficacy: 118.5 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 175.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P520383
CATALOG NUMBER: SQ4-F-150U-050D-940-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P520383

CATALOG NUMBER: SQ4-F-150U-050D-940-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	69	69	69	51	51	51	33	33	33	25
1	92	88	84	81	82	79	75	73	61	59	57	44	43	42	29	29	28	21
2	84	77	71	66	74	69	64	59	53	50	47	39	37	35	26	25	23	18
3	76	67	60	55	68	60	54	49	47	43	39	34	32	29	23	21	20	15
4	70	59	52	46	62	53	47	42	41	37	33	30	27	25	20	18	17	13
5	64	53	45	39	57	47	41	36	37	32	29	27	24	22	18	16	15	11
6	59	47	39	34	52	42	36	31	33	28	25	24	21	19	16	14	13	10
7	54	42	35	29	48	38	31	27	30	25	22	22	19	16	15	13	11	8
8	50	38	31	26	44	34	28	23	27	22	19	20	17	15	14	12	10	8
9	47	35	28	23	41	31	25	21	25	20	17	18	15	13	13	11	9	7
10	43	32	25	20	39	29	23	18	23	18	15	17	14	12	12	10	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5875	5875	5875
5°	5889	5818	5866
10°	5870	5798	5838
15°	5830	5756	5805
20°	5775	5708	5750
25°	5710	5640	5693
30°	5630	5585	5621
35°	5568	5501	5530
40°	5462	5410	5421
45°	5350	5306	5306
50°	5237	5188	5163
55°	5115	5046	5019
60°	4923	4845	4813
65°	4689	4597	4541
70°	4369	4277	4185
75°	3920	3799	3707
80°	3170	3124	3036
85°	1895	2163	2255



TEST NUMBER: P520383

CATALOG NUMBER: SQ4-F-150U-050D-940-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	180.2	0.9
10°-20°	513.3	2.5
20°-30°	770.9	3.7
30°-40°	920.2	4.4
40°-50°	943.0	4.5
50°-60°	841.0	4.0
60°-70°	626.3	3.0
70°-80°	340.0	1.6
80°-90°	83.7	0.4
90°-100°	1126.1	5.4
100°-110°	3044.8	14.6
110°-120°	3201.1	15.4
120°-130°	2600.2	12.5
130°-140°	2039.6	9.8
140°-150°	1565.4	7.5
150°-160°	1125.8	5.4
160°-170°	687.8	3.3
170°-180°	231.9	1.1
0°-30°	1464.4	7.0
0°-40°	2384.7	11.4
0°-60°	4168.7	20.0
0°-90°	5218.7	25.0
90°-120°	7372.0	35.4
90°-150°	13577.3	65.1
90°-180°	15623.0	75.0
0°-180°	20841.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1910	1910	1910	1910	1910	
5°	1908	1905	1885	1903	1900	181
15°	1831	1826	1808	1823	1823	516
25°	1683	1678	1662	1672	1678	775
35°	1483	1478	1465	1466	1473	926
45°	1230	1233	1220	1217	1220	949
55°	954	954	941	934	936	850
65°	644	642	632	624	624	638
75°	330	327	320	314	312	349
85°	54	59	61	64	64	75
90°	5	15	34	36	34	13
95°	175	614	1873	969	576	183
105°	566	875	3378	4982	4778	596
115°	996	1218	2801	5423	6122	984
125°	1364	1563	2525	4261	5005	1216
135°	1635	1829	2457	3440	3894	1264
145°	1901	2044	2423	2945	3169	1190
155°	2147	2231	2402	2642	2728	990
165°	2337	2360	2413	2507	2520	658
175°	2426	2423	2415	2446	2441	230
180°	2423	2423	2423	2423	2423	



TEST NUMBER: P520383

CATALOG NUMBER: SQ4-F-150U-050D-940-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1910.3	1910.3	1910.3	1910.3	1910.3
2.5°	1916.4	1912.5	1896.0	1910.3	1908.2
5°	1907.7	1905.3	1884.7	1902.6	1900.0
7.5°	1893.9	1888.9	1868.9	1886.2	1883.7
10°	1879.6	1874.6	1856.5	1871.8	1869.4
12.5°	1861.2	1858.2	1838.2	1853.5	1853.0
15°	1831.0	1826.0	1808.0	1823.3	1823.3
17.5°	1791.1	1788.1	1770.7	1785.5	1783.5
20°	1764.5	1759.5	1744.0	1756.9	1756.9
22.5°	1731.8	1728.8	1713.4	1724.1	1726.2
25°	1682.7	1677.7	1662.2	1672.5	1677.6
27.5°	1628.5	1624.4	1611.6	1618.3	1621.9
30°	1585.5	1585.5	1572.8	1575.4	1582.9
32.5°	1546.6	1546.6	1531.8	1534.4	1538.0
35°	1483.2	1478.2	1465.3	1465.5	1473.0
37.5°	1409.6	1407.1	1398.8	1397.3	1399.3
40°	1360.5	1358.0	1347.6	1350.2	1350.2
42.5°	1311.4	1308.9	1298.5	1295.1	1299.1
45°	1230.0	1232.6	1219.9	1217.3	1219.9
47.5°	1149.7	1149.7	1139.5	1132.5	1136.4
50°	1094.5	1094.5	1084.3	1079.1	1079.1
52.5°	1037.2	1039.2	1027.0	1019.9	1021.9
55°	953.9	953.9	941.1	933.5	936.0
57.5°	861.8	861.8	849.0	841.4	845.9
60°	800.4	800.4	787.7	780.1	782.5
62.5°	739.0	739.0	726.2	718.6	719.1
65°	644.4	641.9	631.7	624.0	624.0
67.5°	553.4	546.9	539.1	528.8	528.8
70°	485.9	483.4	475.7	465.4	465.4
72.5°	424.5	420.0	412.3	404.1	404.1
75°	329.9	327.4	319.7	314.5	312.0
77.5°	236.3	234.3	233.7	226.6	228.7
80°	179.0	179.0	176.4	171.4	171.4
82.5°	127.9	129.9	125.3	124.2	122.3
85°	53.7	58.7	61.3	63.9	63.9
87.5°	11.2	19.2	21.0	23.5	23.0
90°	5.2	15.4	33.9	36.4	33.9
92.5°	74.0	269.9	532.6	231.2	167.5
95°	174.7	613.5	1872.7	969.2	576.4
97.5°	280.7	703.5	2919.3	2415.9	1774.2
100°	359.9	739.9	3244.7	3383.9	2736.1
102.5°	433.0	790.5	3359.5	4117.9	3633.4
105°	566.0	874.6	3377.8	4982.4	4778.4
107.5°	689.1	970.7	3230.1	5521.8	5589.7
110°	785.1	1040.1	3098.6	5666.6	5954.7



TEST NUMBER: P520383

CATALOG NUMBER: SQ4-F-150U-050D-940-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	870.7	1109.4	2977.6	5637.6	6121.7
115°	996.3	1218.2	2801.4	5422.9	6121.7
117.5°	1119.5	1327.6	2685.0	5094.8	5886.9
120°	1194.6	1398.6	2616.2	4859.4	5667.8
122.5°	1265.5	1465.5	2574.4	4607.0	5421.7
125°	1364.1	1563.1	2524.8	4260.7	5005.4
127.5°	1455.0	1650.3	2495.7	3978.0	4632.9
130°	1505.0	1706.5	2483.1	3803.3	4395.1
132.5°	1557.2	1756.6	2470.6	3645.8	4190.5
135°	1635.4	1829.3	2457.0	3440.3	3894.2
137.5°	1714.2	1897.3	2445.6	3273.5	3643.3
140°	1768.4	1939.3	2441.4	3166.1	3495.1
142.5°	1820.6	1981.3	2433.1	3069.3	3357.4
145°	1901.4	2044.3	2423.1	2944.6	3169.1
147.5°	1975.1	2101.5	2411.7	2831.9	3004.3
150°	2029.3	2141.4	2407.4	2770.6	2908.3
152.5°	2079.4	2177.3	2405.4	2713.6	2826.9
155°	2146.7	2230.8	2402.3	2641.6	2728.3
157.5°	2216.6	2275.2	2402.8	2591.3	2648.5
160°	2256.2	2304.6	2404.9	2559.7	2600.5
162.5°	2287.5	2327.8	2406.9	2534.4	2565.1
165°	2337.0	2360.0	2412.7	2506.9	2519.6
167.5°	2370.9	2386.8	2413.3	2483.3	2489.4
170°	2391.8	2399.5	2415.3	2472.7	2472.7
172.5°	2408.5	2410.0	2415.3	2460.1	2458.0
175°	2425.7	2423.2	2415.3	2446.5	2441.4
177.5°	2431.5	2425.3	2414.8	2435.5	2429.4
180°	2423.1	2423.1	2423.1	2423.1	2423.1

(END OF REPORT)