

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P937873

Luminaire Tested: SQ4-FB-125U-050D-940-1D-UNV-STD-W-12

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P937873
REPORT IS A COMBINATION OF REPORTS P933589 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-125U-050D-940-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 17629.5 lumens
Efficiency: N/A
Efficacy: 123.5 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 12' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 142.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P937873
CATALOG NUMBER: SQ4-FB-125U-050D-940-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P937873

CATALOG NUMBER: SQ4-FB-125U-050D-940-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	33	33	33	24				24
1	92	88	84	80	81	78	75	72	60	58	56	44	42	41	28	28	27	20				20
2	83	76	70	65	74	68	63	58	52	49	46	38	36	34	25	23	22	16				16
3	76	66	59	54	67	59	53	48	46	42	38	33	30	28	22	20	19	13				13
4	69	58	51	45	61	52	46	41	40	36	32	29	26	24	19	17	16	11				11
5	63	52	44	38	56	46	39	34	36	31	27	26	23	20	17	15	13	10				10
6	58	46	38	33	51	41	34	29	32	27	23	23	20	17	15	13	12	8				8
7	53	41	34	28	47	37	30	26	29	24	20	21	18	15	14	12	10	7				7
8	49	37	30	25	44	33	27	22	26	21	18	19	16	13	12	10	9	6				6
9	46	34	27	22	40	30	24	20	24	19	16	17	14	12	11	9	8	6				6
10	42	31	24	19	38	28	21	17	22	17	14	16	13	10	10	9	7	5				5

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1719	1719	1719
5°	1680	1987	2310
10°	1524	2897	3830
15°	1296	3786	4625
20°	1055	4389	4713
25°	881	4594	4618
30°	743	4624	4609
35°	657	4548	4728
40°	573	4450	4851
45°	519	4378	4870
50°	477	4314	4790
55°	457	4219	4577
60°	468	4035	4242
65°	488	3756	3781
70°	522	3278	3195
75°	580	2675	2493
80°	640	1857	1680
85°	577	987	860

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 90°
 Luminance: 5122 cd/sqm



TEST NUMBER: P937873

CATALOG NUMBER: SQ4-FB-125U-050D-940-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	71.9	0.4
10°-20°	318.6	1.8
20°-30°	557.2	3.2
30°-40°	717.3	4.1
40°-50°	801.2	4.5
50°-60°	767.4	4.4
60°-70°	608.2	3.4
70°-80°	357.6	2.0
80°-90°	107.2	0.6
90°-100°	1001.8	5.7
100°-110°	2633.8	14.9
110°-120°	2730.9	15.5
120°-130°	2190.5	12.4
130°-140°	1718.8	9.7
140°-150°	1319.2	7.5
150°-160°	950.1	5.4
160°-170°	581.3	3.3
170°-180°	196.4	1.1
0°-30°	947.7	5.4
0°-40°	1665.0	9.4
0°-60°	3233.7	18.3
0°-90°	4306.7	24.4
90°-120°	6366.5	36.1
90°-150°	11595.0	65.8
90°-180°	13323.0	75.6
0°-180°	17629.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	556	556	556	556	556	
5°	541	581	654	740	766	50
15°	406	749	1262	1530	1578	113
25°	259	849	1503	1569	1571	119
35°	175	811	1415	1496	1554	109
45°	120	647	1251	1433	1497	93
55°	86	411	1061	1233	1267	78
65°	68	218	788	886	899	67
75°	50	134	432	475	477	52
85°	18	41	107	118	120	19
90°	14	39	105	52	52	13
95°	132	519	1726	890	606	147
105°	474	719	2912	4421	4124	503
115°	843	1023	2332	4652	5310	832
125°	1172	1314	2121	3585	4229	1041
135°	1397	1538	2055	2894	3281	1081
145°	1621	1724	2029	2469	2662	1015
155°	1832	1883	2029	2228	2292	842
165°	1976	2003	2029	2109	2135	558
175°	2055	2055	2043	2069	2069	195
180°	2055	2055	2055	2055	2055	



TEST NUMBER: P937873

CATALOG NUMBER: SQ4-FB-125U-050D-940-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	555.7	555.7	555.7	555.7	555.7	555.7	555.7	555.7	555.7	555.7	555.7
2.5°	555.7	555.7	559.3	561.0	564.6	566.4	570.0	573.6	584.3	586.1	589.6
5°	541.4	548.5	571.8	580.7	605.7	639.6	653.9	677.2	725.4	739.7	748.7
7.5°	519.9	536.0	593.2	607.5	670.1	759.4	796.9	847.0	923.8	961.3	991.6
10°	486.0	519.9	621.8	655.8	757.6	893.4	963.0	1032.7	1148.9	1200.8	1220.4
12.5°	448.4	503.9	652.1	698.6	845.1	1043.5	1127.5	1204.3	1336.5	1406.2	1416.9
15°	405.6	480.7	680.7	748.7	938.1	1168.5	1261.5	1356.2	1479.5	1529.5	1542.0
17.5°	368.1	462.7	707.6	779.0	1009.6	1281.1	1375.8	1454.5	1554.5	1588.5	1597.4
20°	321.6	434.2	725.4	818.4	1084.6	1363.3	1454.5	1515.2	1583.1	1604.5	1608.1
22.5°	287.7	403.8	736.2	832.7	1134.6	1413.3	1490.2	1538.5	1584.9	1592.0	1593.8
25°	259.1	369.9	734.4	848.8	1177.5	1443.7	1502.7	1538.5	1565.2	1568.8	1568.8
27.5°	232.3	332.4	727.2	852.3	1209.6	1450.9	1497.3	1522.3	1534.8	1542.0	1542.0
30°	209.0	296.6	709.3	845.1	1223.9	1443.7	1481.3	1493.8	1506.2	1517.0	1522.3
32.5°	191.2	262.7	682.5	830.8	1225.7	1425.9	1452.7	1459.8	1477.6	1502.7	1511.6
35°	175.1	228.7	652.1	811.2	1215.1	1397.3	1415.1	1422.3	1458.0	1495.6	1508.0
37.5°	159.0	203.7	612.9	777.3	1198.9	1363.3	1375.8	1388.3	1443.7	1488.4	1502.7
40°	143.0	182.2	566.4	739.7	1173.9	1322.2	1333.0	1352.6	1425.9	1477.6	1491.9
42.5°	130.4	164.4	516.4	700.5	1141.8	1275.8	1291.9	1320.5	1404.4	1459.8	1475.9
45°	119.7	146.5	462.7	646.8	1100.7	1227.5	1250.7	1290.1	1379.4	1433.0	1447.3
47.5°	109.0	134.0	407.4	591.4	1056.0	1179.3	1209.6	1254.3	1345.4	1397.3	1409.8
50°	100.1	121.5	352.0	532.4	1007.7	1127.5	1163.2	1209.6	1302.6	1350.8	1366.9
52.5°	92.9	110.8	300.1	473.5	952.4	1073.9	1115.0	1163.2	1250.7	1297.2	1307.9
55°	85.8	101.9	255.5	411.0	895.2	1016.7	1061.3	1107.8	1193.6	1232.9	1240.0
57.5°	82.2	94.7	218.0	352.0	834.5	952.4	1002.4	1045.3	1125.6	1156.1	1163.2
60°	76.8	89.3	189.4	302.0	768.3	891.6	934.5	977.3	1045.3	1070.3	1075.6
62.5°	71.5	85.8	167.9	253.7	700.5	820.2	863.0	902.3	959.5	977.3	984.5
65°	67.9	82.2	151.8	218.0	630.7	745.1	788.0	821.9	868.4	886.2	889.8
67.5°	64.3	78.6	139.3	187.6	561.0	670.1	702.2	734.4	770.1	788.0	789.8
70°	59.0	75.0	128.7	166.1	489.6	584.3	611.1	645.0	673.6	682.5	687.9
72.5°	55.4	69.7	121.5	150.1	416.3	502.1	527.1	546.7	571.8	580.7	580.7
75°	50.0	62.5	114.4	134.0	341.3	411.0	432.4	452.1	471.7	475.3	469.9
77.5°	44.7	55.4	98.3	112.6	266.2	325.2	343.0	353.8	369.9	373.4	375.2
80°	37.6	48.2	76.8	87.6	193.0	239.4	251.9	260.9	275.2	275.2	278.7
82.5°	28.6	37.6	55.4	62.5	130.4	164.4	175.1	180.4	189.4	189.4	189.4
85°	17.8	23.3	35.7	41.1	78.6	100.1	107.2	109.0	116.2	117.9	117.9
87.5°	9.0	12.5	23.3	25.0	41.1	51.9	51.9	55.4	55.4	53.6	51.9
90°	13.8	24.8	35.9	38.6	60.7	90.0	104.8	93.2	69.9	52.4	52.4
92.5°	55.1	148.9	242.8	266.2	374.3	518.3	590.3	517.3	371.5	262.0	251.7
95°	132.4	304.1	475.7	518.6	920.9	1457.3	1725.5	1539.7	1168.3	889.7	858.1
97.5°	228.9	380.3	531.8	569.7	1240.4	2134.8	2582.0	2464.6	2229.9	2053.8	1993.6
100°	303.4	440.8	578.1	612.5	1356.8	2349.3	2845.5	2854.1	2871.3	2884.1	2812.6
102.5°	366.9	495.1	623.1	655.2	1410.1	2416.7	2920.0	3069.5	3368.7	3593.1	3531.8
105°	474.5	583.0	691.5	718.7	1449.7	2424.3	2911.7	3247.0	3917.7	4420.6	4387.7
107.5°	584.8	686.0	787.1	812.4	1457.0	2316.5	2746.2	3213.9	4149.4	4851.0	4859.0
110°	659.3	750.6	842.0	864.8	1445.9	2220.8	2608.2	3131.2	4177.0	4961.3	4995.7



TEST NUMBER: P937873

CATALOG NUMBER: SQ4-FB-125U-050D-940-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	732.4	819.4	906.5	928.2	1446.4	2137.3	2482.8	3018.0	4088.3	4891.0	4943.8
115°	842.7	923.0	1003.4	1023.4	1459.8	2041.5	2332.4	2848.0	3879.1	4652.4	4725.5
117.5°	951.8	1024.7	1097.7	1115.9	1486.9	1981.6	2229.0	2694.3	3624.8	4322.7	4403.8
120°	1015.2	1083.8	1152.5	1169.7	1509.0	1961.4	2187.6	2612.8	3463.0	4100.7	4179.5
122.5°	1077.2	1146.5	1215.8	1233.1	1540.7	1950.8	2155.9	2538.7	3304.3	3878.6	3956.3
125°	1172.4	1235.6	1298.7	1314.5	1583.5	1942.1	2121.3	2446.5	3097.0	3584.8	3656.3
127.5°	1249.7	1313.4	1377.2	1393.1	1626.2	1937.0	2092.4	2371.6	2930.0	3348.9	3409.3
130°	1291.1	1359.7	1428.3	1445.5	1657.5	1940.1	2081.4	2329.9	2827.1	3200.0	3255.8
132.5°	1333.8	1402.4	1471.1	1488.3	1682.8	1942.1	2071.7	2294.2	2739.3	3073.1	3123.1
135°	1397.3	1459.8	1522.3	1537.9	1710.4	1940.3	2055.2	2241.6	2614.3	2893.8	2936.9
137.5°	1462.1	1524.0	1585.9	1601.3	1751.7	1952.2	2052.4	2210.0	2525.0	2761.3	2796.6
140°	1515.8	1572.8	1629.8	1644.1	1777.0	1954.1	2042.8	2178.8	2451.0	2655.1	2688.1
142.5°	1557.2	1609.9	1662.7	1675.8	1798.1	1961.2	2042.8	2162.3	2401.4	2580.7	2609.0
145°	1620.7	1666.7	1712.7	1724.1	1825.7	1961.2	2029.0	2126.8	2322.3	2468.9	2490.4
147.5°	1684.1	1728.8	1773.6	1784.8	1866.2	1974.7	2029.0	2105.9	2259.8	2375.1	2392.9
150°	1725.5	1766.0	1806.5	1816.6	1887.4	1981.7	2029.0	2094.0	2223.9	2321.3	2335.7
152.5°	1768.3	1798.9	1829.6	1837.3	1901.2	1986.4	2029.0	2084.5	2195.4	2278.6	2289.5
155°	1831.7	1854.4	1877.1	1882.7	1931.5	1996.5	2029.0	2073.1	2161.4	2227.5	2234.7
157.5°	1878.7	1900.7	1922.8	1928.3	1961.9	2006.6	2029.0	2063.3	2131.9	2183.4	2188.5
160°	1910.4	1927.5	1944.7	1949.0	1975.6	2011.2	2029.0	2058.4	2117.3	2161.4	2164.3
162.5°	1942.1	1954.9	1967.8	1971.0	1990.4	2016.1	2029.0	2053.9	2103.5	2140.7	2143.5
165°	1976.5	1988.1	1999.8	2002.7	2011.5	2023.1	2029.0	2046.8	2082.3	2108.9	2111.8
167.5°	2008.3	2013.8	2019.3	2020.6	2028.0	2037.9	2042.8	2054.4	2077.7	2095.1	2096.4
170°	2029.0	2034.5	2040.0	2041.3	2041.8	2042.4	2042.8	2054.4	2077.7	2095.1	2095.1
172.5°	2040.0	2041.2	2042.5	2042.8	2042.8	2042.8	2042.8	2052.0	2070.4	2084.1	2083.1
175°	2055.2	2055.2	2055.2	2055.2	2051.0	2045.5	2042.8	2048.6	2060.2	2069.0	2069.0
177.5°	2055.2	2055.2	2055.2	2055.2	2052.0	2047.6	2045.5	2050.1	2059.3	2066.2	2065.0
180°	2055.2	2055.2	2055.2	2055.2	2055.2	2055.2	2055.2	2055.2	2055.2	2055.2	2055.2



TEST NUMBER: P937873

CATALOG NUMBER: SQ4-FB-125U-050D-940-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	555.7	555.7
2.5°	593.2	589.6
5°	763.0	766.5
7.5°	1027.4	1025.6
10°	1277.6	1293.6
12.5°	1459.8	1463.3
15°	1570.6	1577.7
17.5°	1613.5	1615.3
20°	1615.3	1611.7
22.5°	1595.6	1592.0
25°	1572.4	1570.6
27.5°	1550.9	1552.8
30°	1542.0	1547.3
32.5°	1542.0	1550.9
35°	1545.6	1554.5
37.5°	1543.8	1554.5
40°	1536.6	1549.1
42.5°	1517.0	1525.9
45°	1486.6	1497.3
47.5°	1447.3	1454.5
50°	1397.3	1404.4
52.5°	1334.8	1336.5
55°	1259.7	1266.8
57.5°	1179.3	1181.0
60°	1089.9	1095.3
62.5°	995.3	995.3
65°	895.2	898.7
67.5°	791.6	800.4
70°	686.2	687.9
72.5°	582.5	582.5
75°	475.3	477.0
77.5°	373.4	373.4
80°	277.0	278.7
82.5°	191.2	194.7
85°	119.7	119.7
87.5°	55.4	50.0
90°	52.4	52.4
92.5°	209.9	168.3
95°	731.8	605.5
97.5°	1753.4	1513.1
100°	2526.3	2240.0
102.5°	3286.6	3041.4
105°	4255.9	4124.1
107.5°	4890.8	4922.7
110°	5133.0	5270.3



TEST NUMBER: P937873

CATALOG NUMBER: SQ4-FB-125U-050D-940-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	5154.6	5365.5
115°	5017.9	5310.3
117.5°	4728.1	5052.4
120°	4494.5	4809.6
122.5°	4267.1	4577.9
125°	3942.6	4228.9
127.5°	3650.8	3892.4
130°	3478.9	3702.1
132.5°	3322.9	3522.7
135°	3109.1	3281.3
137.5°	2937.6	3078.6
140°	2819.9	2951.7
142.5°	2722.4	2835.8
145°	2576.2	2662.0
147.5°	2464.0	2535.2
150°	2393.4	2451.1
152.5°	2333.0	2376.6
155°	2263.6	2292.4
157.5°	2208.7	2229.0
160°	2176.0	2187.6
162.5°	2154.5	2165.5
165°	2123.5	2135.2
167.5°	2101.3	2106.2
170°	2095.1	2095.1
172.5°	2078.7	2074.5
175°	2069.0	2069.0
177.5°	2060.1	2055.2
180°	2055.2	2055.2



TEST NUMBER: P937873
 CATALOG NUMBER: SQ4-FB-125U-050D-940-1D-UNV-STD-W-12

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.57	1.02	1.70	3.30	13.07	13.76	14.22	14.89	16.49
	3H	0.57	1.18	1.72	2.33	3.94	14.90	15.52	16.05	16.66	18.27
	4H	0.86	1.44	2.02	2.59	4.20	15.54	16.13	16.70	17.27	18.89
	6H	1.10	1.64	2.27	2.79	4.41	15.97	16.51	17.14	17.65	19.28
	8H	1.16	1.68	2.33	2.84	4.45	16.09	16.60	17.26	17.76	19.38
	12H	1.17	1.66	2.35	2.82	4.46	16.15	16.64	17.33	17.79	19.43
4H	2H	7.08	7.67	8.25	8.81	10.42	13.32	13.91	14.49	15.05	16.67
	3H	8.63	9.12	9.80	10.29	11.92	15.36	15.85	16.53	17.02	18.64
	4H	8.72	9.17	9.89	10.33	11.97	16.12	16.57	17.30	17.73	19.37
	6H	8.72	9.10	9.90	10.28	11.92	16.65	17.04	17.83	18.22	19.85
	8H	8.69	9.05	9.87	10.22	11.87	16.81	17.17	17.99	18.35	20.00
	12H	8.64	8.96	9.83	10.15	11.80	16.90	17.23	18.10	18.41	20.07
8H	4H	10.15	10.51	11.33	11.68	13.33	16.16	16.52	17.34	17.70	19.35
	6H	10.38	10.68	11.58	11.90	13.54	16.79	17.09	17.99	18.30	19.95
	8H	10.40	10.66	11.60	11.85	13.52	17.01	17.27	18.21	18.46	20.13
	12H	10.36	10.59	11.57	11.78	13.48	17.15	17.38	18.36	18.57	20.27
12H	4H	10.29	10.61	11.48	11.80	13.45	16.11	16.43	17.30	17.62	19.27
	6H	10.64	10.90	11.85	12.09	13.76	16.77	17.03	17.97	18.22	19.89
	8H	10.70	10.93	11.91	12.12	13.82	16.99	17.22	18.20	18.41	20.11