

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P520956

Luminaire Tested: SQ4-125U-0D-92765-1D-UNV-STD-W-4_5700K

Issue Date: 5-5-2021

Test Information

Test Method: LM-79-2019
Report Number: P520956
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51)
Test Lab: INNOVATION CENTER
Issue Date: 5-5-2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-125U-0D-92765-1D-UNV-STD-W-4_5700K
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE
INDIRECT ONLY
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 2700K-6500K CCT, 90 CRI LEDS, TUNED TO 5700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5827.2 lumens
Efficiency: N/A
Efficacy: 140.8 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 41.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P520956
CATALOG NUMBER: SQ4-125U-0D-92765-1D-UNV-STD-W-4_5700K

Luminous Intensity Polar Plot



TEST NUMBER: P520956

CATALOG NUMBER: SQ4-125U-0D-92765-1D-UNV-STD-W-4_5700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	0
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	0

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 0°
 Luminance: 0 cd/sqm

TEST NUMBER: P520956

CATALOG NUMBER: SQ4-125U-0D-92765-1D-UNV-STD-W-4_5700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	427.5	7.3
100°-110°	1216.3	20.9
110°-120°	1165.4	20.0
120°-130°	922.3	15.8
130°-140°	740.3	12.7
140°-150°	579.6	9.9
150°-160°	424.1	7.3
160°-170°	262.7	4.5
170°-180°	89.1	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	2809.1	48.2
90°-150°	5051.4	86.7
90°-180°	5827.0	100.0
0°-180°	5827.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	2
95°	46	184	828	286	177	53
105°	189	287	1240	2189	2081	200
115°	351	425	940	1991	2338	346
125°	496	550	897	1489	1780	444
135°	606	657	886	1258	1421	468
145°	715	752	894	1088	1186	447
155°	817	836	915	984	1024	378
165°	902	906	926	946	960	254
175°	945	940	936	931	924	90
180°	938	938	938	938	938	

TEST NUMBER: P520956

CATALOG NUMBER: SQ4-125U-0D-92765-1D-UNV-STD-W-4_5700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0
92.5°	14.3	75.7	175.5	51.1	38.5
95°	46.4	184.1	827.5	286.4	176.6
97.5°	85.2	215.7	1274.5	912.0	624.9
100°	112.4	234.4	1371.5	1389.2	1070.1
102.5°	142.3	254.6	1350.1	1778.2	1499.5
105°	189.0	286.7	1239.5	2189.4	2081.3
107.5°	236.5	324.0	1110.4	2305.4	2401.6
110°	269.3	351.3	1036.2	2261.0	2477.2

TEST NUMBER: P520956

CATALOG NUMBER: SQ4-125U-0D-92765-1D-UNV-STD-W-4_5700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	300.7	378.5	986.3	2156.1	2464.4
115°	351.3	424.6	939.9	1991.1	2338.1
117.5°	395.9	464.6	912.4	1810.7	2178.3
120°	431.6	489.1	909.6	1707.7	2059.9
122.5°	460.1	517.7	902.4	1617.2	1944.3
125°	495.8	549.9	897.1	1488.7	1779.9
127.5°	534.7	585.3	894.2	1411.9	1651.8
130°	554.7	605.2	890.0	1358.4	1567.7
132.5°	576.1	625.2	890.0	1316.7	1509.2
135°	606.4	657.0	886.4	1257.5	1421.4
137.5°	634.9	684.1	886.0	1207.4	1349.0
140°	656.3	706.9	884.6	1165.9	1301.9
142.5°	680.6	722.8	888.9	1132.8	1254.8
145°	715.2	751.8	893.5	1088.4	1186.0
147.5°	744.8	780.4	901.4	1043.5	1127.9
150°	770.5	794.9	904.2	1028.6	1087.9
152.5°	790.4	816.2	907.1	1008.6	1063.7
155°	816.8	836.0	914.9	983.6	1023.7
157.5°	849.6	861.2	916.7	972.3	1000.9
160°	866.8	875.5	923.8	963.6	988.0
162.5°	876.8	886.9	925.3	956.4	975.2
165°	902.4	905.9	925.6	945.6	959.5
167.5°	919.9	916.8	933.8	942.9	948.4
170°	925.6	923.9	931.0	932.9	939.9
172.5°	938.5	932.5	935.3	930.0	935.6
175°	945.2	940.0	936.3	930.8	923.8
177.5°	948.1	939.7	935.3	929.6	931.0
180°	938.1	938.1	938.1	938.1	938.1

(END OF REPORT)