

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P520957

Luminaire Tested: SQ4-125U-0D-92765-1D-UNV-STD-W-4_6500K

Issue Date: 5-5-2021

Test Information

Test Method: LM-79-2019
Report Number: P520957
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51)
Test Lab: INNOVATION CENTER
Issue Date: 5-5-2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-125U-0D-92765-1D-UNV-STD-W-4_6500K
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE
INDIRECT ONLY
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 2700K-6500K CCT, 90 CRI LEDS, TUNED TO 6500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5882.5 lumens
Efficiency: N/A
Efficacy: 142.8 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 41.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P520957
CATALOG NUMBER: SQ4-125U-0D-92765-1D-UNV-STD-W-4_6500K

Luminous Intensity Polar Plot



TEST NUMBER: P520957

CATALOG NUMBER: SQ4-125U-0D-92765-1D-UNV-STD-W-4_6500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	0
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	0

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 0°
 Luminance: 0 cd/sqm

TEST NUMBER: P520957

CATALOG NUMBER: SQ4-125U-0D-92765-1D-UNV-STD-W-4_6500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	431.5	7.3
100°-110°	1227.8	20.9
110°-120°	1176.4	20.0
120°-130°	931.1	15.8
130°-140°	747.3	12.7
140°-150°	585.1	9.9
150°-160°	428.1	7.3
160°-170°	265.2	4.5
170°-180°	90.0	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	2835.8	48.2
90°-150°	5099.2	86.7
90°-180°	5882.0	100.0
0°-180°	5882.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	2
95°	47	186	835	289	178	54
105°	191	289	1251	2210	2101	202
115°	355	429	949	2010	2360	349
125°	500	555	906	1503	1797	448
135°	612	663	895	1269	1435	472
145°	722	759	902	1099	1197	451
155°	825	844	924	993	1033	381
165°	911	914	934	954	969	256
175°	954	949	945	940	933	90
180°	947	947	947	947	947	

TEST NUMBER: P520957

CATALOG NUMBER: SQ4-125U-0D-92765-1D-UNV-STD-W-4_6500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0
92.5°	14.4	76.4	177.2	51.6	38.9
95°	46.8	185.9	835.4	289.1	178.2
97.5°	86.1	217.7	1286.6	920.6	630.9
100°	113.4	236.6	1384.5	1402.4	1080.2
102.5°	143.7	257.0	1362.9	1795.1	1513.8
105°	190.8	289.4	1251.3	2210.2	2101.0
107.5°	238.7	327.1	1120.9	2327.2	2424.4
110°	271.9	354.6	1046.0	2282.4	2500.7

TEST NUMBER: P520957

CATALOG NUMBER: SQ4-125U-0D-92765-1D-UNV-STD-W-4_6500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	303.5	382.1	995.6	2176.5	2487.8
115°	354.7	428.6	948.8	2010.0	2360.3
117.5°	399.7	469.0	921.1	1827.9	2199.0
120°	435.7	493.8	918.2	1723.8	2079.4
122.5°	464.5	522.6	911.0	1632.5	1962.8
125°	500.5	555.1	905.6	1502.8	1796.8
127.5°	539.8	590.8	902.7	1425.3	1667.5
130°	559.9	611.0	898.4	1371.3	1582.5
132.5°	581.5	631.2	898.4	1329.1	1523.5
135°	612.1	663.2	894.8	1269.4	1434.9
137.5°	640.9	690.6	894.4	1218.9	1361.8
140°	662.5	713.6	893.0	1177.0	1314.3
142.5°	687.0	729.6	897.3	1143.5	1266.7
145°	722.0	758.9	902.0	1098.7	1197.3
147.5°	751.8	787.8	909.9	1053.4	1138.6
150°	777.8	802.4	912.8	1038.4	1098.2
152.5°	797.9	824.0	915.7	1018.1	1073.7
155°	824.6	843.9	923.6	992.9	1033.4
157.5°	857.7	869.3	925.4	981.5	1010.4
160°	875.0	883.8	932.6	972.8	997.4
162.5°	885.1	895.3	934.0	965.4	984.4
165°	911.0	914.5	934.4	954.5	968.6
167.5°	928.6	925.5	942.7	951.8	957.4
170°	934.4	932.6	939.8	941.8	948.8
172.5°	947.4	941.4	944.1	938.8	944.5
175°	954.2	948.9	945.2	939.6	932.6
177.5°	957.1	948.6	944.1	938.4	939.8
180°	947.0	947.0	947.0	947.0	947.0

(END OF REPORT)