

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562693

Luminaire Tested: **SQ4-PC3-050U-125D-940-1D-UNV-STD-W-12**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P562693  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-21, G2-2106-289-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PC3-050U-125D-940-1D-UNV-STD-W-12  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.  
DOWNLIGHT 1250 LUMENS PER FOOT  
UPLIGHT 500 LUMENS PER FOOT  
Light Source: 4000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 17924.0 lumens  
Efficiency: N/A  
Efficacy: 107.3 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37  
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 167  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P562693  
CATALOG NUMBER: SQ4-PC3-050U-125D-940-1D-UNV-STD-W-12

### Luminous Intensity Polar Plot





TEST NUMBER: P562693

CATALOG NUMBER: SQ4-PC3-050U-125D-940-1D-UNV-STD-W-12

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	76	76	76	71
1	103	98	94	91	97	93	90	86	84	81	79	75	73	71	67	65	64	60
2	93	86	79	74	88	81	76	71	73	69	65	66	62	59	59	56	54	50
3	85	75	68	62	80	72	65	59	65	59	55	58	54	50	52	49	46	43
4	78	67	59	52	74	64	56	50	58	51	47	52	47	43	47	43	40	37
5	72	60	51	45	68	57	49	43	52	45	40	47	41	37	42	38	34	32
6	66	54	45	39	62	51	43	38	46	40	35	42	37	33	38	34	30	28
7	61	48	40	34	58	46	39	33	42	36	31	38	33	29	35	30	27	25
8	57	44	36	30	54	42	35	30	39	32	28	35	30	26	32	27	24	22
9	53	40	33	27	50	39	31	26	35	29	25	32	27	23	29	25	22	20
10	50	37	30	25	47	36	29	24	33	27	22	30	25	21	27	23	20	18

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	14373	14373	14373
5°	14482	14388	14335
10°	14446	14379	14338
15°	14370	14370	14356
20°	14276	14318	14318
25°	14141	14243	14200
30°	13969	14138	14076
35°	13761	13972	13875
40°	13533	13724	13586
45°	13287	13382	13175
50°	12940	12940	12733
55°	12529	12367	12181
60°	11925	11685	11498
65°	11022	10801	10707
70°	9650	9727	9689
75°	7764	8587	8639
80°	5519	7281	7357
85°	3359	6108	6108



TEST NUMBER: P562693

CATALOG NUMBER: SQ4-PC3-050U-125D-940-1D-UNV-STD-W-12

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	442.3	2.5
10°-20°	1269.3	7.1
20°-30°	1922.2	10.7
30°-40°	2304.4	12.9
40°-50°	2349.7	13.1
50°-60°	2051.2	11.4
60°-70°	1468.4	8.2
70°-80°	756.3	4.2
80°-90°	194.3	1.1
90°-100°	379.8	2.1
100°-110°	1031.8	5.8
110°-120°	1060.8	5.9
120°-130°	848.2	4.7
130°-140°	666.4	3.7
140°-150°	511.0	2.9
150°-160°	367.5	2.1
160°-170°	224.7	1.3
170°-180°	75.7	0.4
0°-30°	3633.7	20.3
0°-40°	5938.1	33.1
0°-60°	10339.0	57.7
0°-90°	12758.1	71.2
90°-120°	2472.4	13.8
90°-150°	4498.0	25.1
90°-180°	5166.0	28.8
0°-180°	17924.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	4674	4674	4674	4674	4674	
5°	4691	4644	4661	4648	4643	445
15°	4513	4475	4513	4513	4509	1273
25°	4167	4138	4198	4185	4185	1918
35°	3665	3657	3722	3696	3696	2292
45°	3055	3047	3077	3038	3029	2352
55°	2337	2307	2306	2272	2272	2083
65°	1515	1481	1484	1471	1471	1498
75°	653	683	723	727	727	706
85°	95	146	173	177	173	129
90°	2	10	18	23	23	8
95°	56	208	661	288	193	59
105°	183	285	1135	1728	1626	195
115°	326	395	908	1807	2058	321
125°	448	510	822	1384	1633	399
135°	539	599	799	1128	1272	417
145°	623	668	789	958	1030	391
155°	705	730	784	860	885	325
165°	763	773	786	819	822	215
175°	791	794	789	799	796	75
180°	791	791	791	791	791	

TEST NUMBER: P562693

CATALOG NUMBER: SQ4-PC3-050U-125D-940-1D-UNV-STD-W-12

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	4673.6	4673.6	4673.6	4673.6	4673.6
2.5°	4701.2	4660.6	4673.6	4662.8	4645.9
5°	4690.9	4644.3	4660.6	4647.5	4643.3
7.5°	4657.1	4610.6	4632.0	4623.3	4619.0
10°	4625.9	4579.4	4604.3	4595.6	4591.3
12.5°	4584.4	4541.2	4569.7	4561.0	4560.2
15°	4513.4	4475.4	4513.4	4513.3	4509.1
17.5°	4424.3	4389.6	4430.4	4432.9	4430.4
20°	4362.0	4323.9	4375.0	4370.7	4375.0
22.5°	4285.8	4254.5	4309.2	4298.0	4302.3
25°	4167.2	4137.6	4197.5	4184.6	4184.6
27.5°	4027.0	4005.9	4071.2	4057.3	4057.3
30°	3933.6	3912.4	3981.2	3963.9	3963.9
32.5°	3829.7	3815.3	3880.8	3860.0	3860.0
35°	3665.3	3656.8	3721.5	3695.6	3695.6
37.5°	3495.6	3488.0	3546.7	3515.3	3505.2
40°	3371.0	3366.8	3418.6	3384.0	3384.0
42.5°	3246.4	3242.2	3287.1	3245.5	3245.5
45°	3055.1	3046.7	3076.8	3037.6	3029.2
47.5°	2846.5	2838.1	2856.9	2814.4	2810.2
50°	2704.6	2696.1	2704.6	2665.6	2661.3
52.5°	2559.2	2544.0	2545.4	2506.4	2505.5
55°	2336.8	2307.2	2306.5	2271.9	2271.9
57.5°	2101.4	2062.4	2065.9	2036.4	2032.1
60°	1938.7	1896.3	1899.7	1873.7	1869.4
62.5°	1779.4	1730.3	1740.5	1711.0	1710.2
65°	1514.6	1480.7	1484.3	1471.3	1471.3
67.5°	1260.1	1228.8	1251.5	1241.1	1240.2
70°	1073.2	1052.0	1081.8	1081.7	1077.5
72.5°	900.1	899.2	936.4	936.5	939.0
75°	653.4	683.0	722.7	727.0	727.0
77.5°	436.2	488.7	532.3	534.0	533.1
80°	311.6	370.8	411.1	419.7	415.4
82.5°	211.2	273.8	307.2	315.8	311.6
85°	95.2	146.0	173.1	177.3	173.1
87.5°	28.2	60.2	72.8	73.7	66.9
90°	2.5	10.0	17.8	22.9	22.9
92.5°	22.9	104.0	180.6	77.6	65.6
95°	56.0	207.7	661.4	287.9	193.3
97.5°	92.6	229.4	1014.0	788.9	554.1
100°	117.0	243.9	1121.9	1137.3	918.4
102.5°	141.4	258.4	1150.4	1406.5	1213.5
105°	183.2	285.2	1134.6	1727.6	1625.6
107.5°	226.4	316.5	1069.0	1893.4	1921.8
110°	256.9	339.0	1020.2	1926.1	2047.9



TEST NUMBER: P562693

CATALOG NUMBER: SQ4-PC3-050U-125D-940-1D-UNV-STD-W-12

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	283.4	361.5	971.3	1899.0	2082.5
115°	325.6	395.3	908.2	1806.9	2058.1
117.5°	365.3	432.0	868.0	1676.3	1959.4
120°	391.8	456.5	849.7	1588.8	1869.9
122.5°	414.2	478.8	837.5	1501.0	1772.2
125°	447.7	509.9	821.7	1384.5	1633.3
127.5°	477.8	539.5	813.1	1296.2	1509.6
130°	496.1	555.8	809.0	1240.8	1432.3
132.5°	514.4	574.1	804.9	1193.4	1363.1
135°	539.3	599.0	798.8	1127.7	1272.0
137.5°	566.3	620.5	795.8	1069.7	1191.1
140°	582.6	634.8	793.7	1032.8	1142.3
142.5°	598.9	647.1	791.7	1003.9	1095.5
145°	623.3	668.1	788.6	958.2	1030.3
147.5°	650.8	689.1	786.1	922.2	978.9
150°	669.1	701.4	786.1	901.6	946.4
152.5°	683.3	711.7	784.1	883.1	919.9
155°	704.7	729.6	783.6	860.4	885.3
157.5°	725.6	745.0	783.6	845.0	864.0
160°	737.8	755.2	783.6	834.8	849.7
162.5°	750.0	763.4	785.6	826.5	837.5
165°	763.2	773.2	786.1	819.2	821.7
167.5°	776.9	781.9	788.6	810.6	812.6
170°	781.0	786.0	788.6	806.5	806.5
172.5°	785.1	788.1	788.6	802.4	802.4
175°	791.2	793.7	788.6	798.8	796.3
177.5°	793.2	793.2	787.1	795.2	791.2
180°	791.2	791.2	791.2	791.2	791.2

(END OF REPORT)