

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P520966

Luminaire Tested: SQ4-150U-0D-92765-1D-UNV-STD-W-4_4000K

Issue Date: 5-5-2021

Test Information

Test Method: LM-79-2019
Report Number: P520966
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51)
Test Lab: INNOVATION CENTER
Issue Date: 5-5-2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-150U-0D-92765-1D-UNV-STD-W-4_4000K
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE
INDIRECT ONLY
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 2700K-6500K CCT, 90 CRI LEDS, TUNED TO 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6739.6 lumens
Efficiency: N/A
Efficacy: 131.6 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 51.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P520966
CATALOG NUMBER: SQ4-150U-0D-92765-1D-UNV-STD-W-4_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P520966

CATALOG NUMBER: SQ4-150U-0D-92765-1D-UNV-STD-W-4_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	0
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	0

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 0°
 Luminance: 0 cd/sqm

TEST NUMBER: P520966

CATALOG NUMBER: SQ4-150U-0D-92765-1D-UNV-STD-W-4_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	494.4	7.3
100°-110°	1406.7	20.9
110°-120°	1347.8	20.0
120°-130°	1066.7	15.8
130°-140°	856.2	12.7
140°-150°	670.3	9.9
150°-160°	490.5	7.3
160°-170°	303.8	4.5
170°-180°	103.1	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	3249.0	48.2
90°-150°	5842.2	86.7
90°-180°	6740.0	100.0
0°-180°	6739.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	2
95°	54	213	957	331	204	61
105°	219	332	1434	2532	2407	231
115°	406	491	1087	2303	2704	400
125°	573	636	1038	1722	2059	513
135°	701	760	1025	1454	1644	541
145°	827	870	1033	1259	1372	517
155°	945	967	1058	1138	1184	437
165°	1044	1048	1070	1094	1110	294
175°	1093	1087	1083	1076	1068	104
180°	1085	1085	1085	1085	1085	

TEST NUMBER: P520966

CATALOG NUMBER: SQ4-150U-0D-92765-1D-UNV-STD-W-4_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0
92.5°	16.5	87.5	203.0	59.1	44.6
95°	53.6	213.0	957.1	331.3	204.2
97.5°	98.6	249.5	1474.0	1054.7	722.8
100°	129.9	271.1	1586.2	1606.7	1237.6
102.5°	164.6	294.5	1561.5	2056.6	1734.3
105°	218.6	331.6	1433.6	2532.2	2407.2
107.5°	273.5	374.8	1284.2	2666.3	2777.6
110°	311.5	406.3	1198.4	2615.0	2865.1

TEST NUMBER: P520966

CATALOG NUMBER: SQ4-150U-0D-92765-1D-UNV-STD-W-4_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	347.8	437.7	1140.7	2493.7	2850.2
115°	406.4	491.1	1087.0	2302.8	2704.2
117.5°	457.9	537.4	1055.3	2094.2	2519.4
120°	499.2	565.7	1052.0	1975.0	2382.4
122.5°	532.2	598.7	1043.7	1870.4	2248.8
125°	573.4	636.0	1037.5	1721.8	2058.6
127.5°	618.4	676.9	1034.2	1632.9	1910.5
130°	641.5	700.0	1029.3	1571.1	1813.1
132.5°	666.3	723.1	1029.3	1522.8	1745.5
135°	701.3	759.8	1025.2	1454.4	1644.0
137.5°	734.3	791.2	1024.7	1396.5	1560.2
140°	759.1	817.6	1023.1	1348.5	1505.8
142.5°	787.1	835.9	1028.0	1310.1	1451.3
145°	827.1	869.5	1033.4	1258.7	1371.7
147.5°	861.4	902.5	1042.5	1206.8	1304.4
150°	891.1	919.3	1045.8	1189.7	1258.2
152.5°	914.2	944.0	1049.1	1166.5	1230.2
155°	944.7	966.9	1058.2	1137.6	1184.0
157.5°	982.7	996.0	1060.2	1124.5	1157.6
160°	1002.5	1012.6	1068.5	1114.5	1142.7
162.5°	1014.0	1025.7	1070.1	1106.1	1127.9
165°	1043.7	1047.8	1070.5	1093.6	1109.7
167.5°	1063.9	1060.3	1080.0	1090.5	1096.9
170°	1070.5	1068.5	1076.7	1079.0	1087.0
172.5°	1085.4	1078.5	1081.7	1075.6	1082.1
175°	1093.2	1087.2	1082.9	1076.5	1068.5
177.5°	1096.5	1086.8	1081.7	1075.1	1076.7
180°	1085.0	1085.0	1085.0	1085.0	1085.0

(END OF REPORT)