

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562837

Luminaire Tested: **SQ4-PC3-0U-075D-940-1D-UNV-STD-W-12**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P562837  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-289-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PC3-0U-075D-940-1D-UNV-STD-W-12  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.  
DOWNLIGHT 750 LUMENS PER FOOT  
DIRECT ONLY  
Light Source: 4000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7522.4 lumens  
Efficiency: N/A  
Efficacy: 94.7 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37  
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')  
CIE Type: Direct

Input Watts (W): 79.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P562837  
CATALOG NUMBER: SQ4-PC3-0U-075D-940-1D-UNV-STD-W-12

### Luminous Intensity Polar Plot





TEST NUMBER: P562837

CATALOG NUMBER: SQ4-PC3-0U-075D-940-1D-UNV-STD-W-12

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	109	105	100	97	106	102	98	95	98	95	92	94	92	89	91	88	87	85																			
2	99	91	85	79	97	90	83	78	86	81	76	83	78	75	80	76	73	71																			
3	91	80	72	66	88	79	71	65	76	70	64	73	68	63	71	66	62	60																			
4	83	71	63	56	81	70	62	56	68	61	55	65	59	54	63	58	53	51																			
5	77	64	55	48	74	63	54	48	61	53	48	59	52	47	57	51	47	44																			
6	71	58	49	42	69	57	48	42	55	47	42	53	46	41	52	46	41	39																			
7	66	52	43	37	64	51	43	37	50	42	37	48	42	37	47	41	36	34																			
8	61	48	39	33	60	47	39	33	46	38	33	44	38	33	43	37	33	31																			
9	57	44	36	30	56	43	35	30	42	35	30	41	34	30	40	34	29	28																			
10	54	40	32	27	52	40	32	27	39	32	27	38	31	27	37	31	27	25																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	8477	8477	8477
5°	8541	8485	8454
10°	8520	8480	8456
15°	8475	8475	8467
20°	8419	8444	8444
25°	8340	8400	8374
30°	8238	8338	8302
35°	8115	8240	8183
40°	7982	8094	8012
45°	7837	7892	7770
50°	7632	7632	7509
55°	7389	7294	7184
60°	7032	6891	6781
65°	6500	6370	6314
70°	5691	5737	5714
75°	4579	5064	5095
80°	3255	4295	4339
85°	1980	3603	3603



TEST NUMBER: P562837

CATALOG NUMBER: SQ4-PC3-0U-075D-940-1D-UNV-STD-W-12

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	260.9	3.5
10°-20°	748.6	10.0
20°-30°	1133.6	15.1
30°-40°	1359.0	18.1
40°-50°	1385.8	18.4
50°-60°	1209.7	16.1
60°-70°	866.0	11.5
70°-80°	446.1	5.9
80°-90°	112.8	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2143.0	28.5
0°-40°	3502.1	46.6
0°-60°	6097.5	81.1
0°-90°	7522.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7522.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2756	2756	2756	2756	2756	
5°	2766	2739	2749	2741	2738	263
15°	2662	2639	2662	2662	2659	751
25°	2458	2440	2476	2468	2468	1131
35°	2162	2157	2195	2180	2180	1352
45°	1802	1797	1814	1792	1786	1387
55°	1378	1361	1360	1340	1340	1229
65°	893	873	875	868	868	883
75°	385	403	426	429	429	416
85°	56	86	102	105	102	79
90°	0	0	0	0	0	



TEST NUMBER: P562837

CATALOG NUMBER: SQ4-PC3-0U-075D-940-1D-UNV-STD-W-12

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2756.3	2756.3	2756.3	2756.3	2756.3
2.5°	2772.6	2748.7	2756.3	2749.9	2739.9
5°	2766.5	2739.0	2748.6	2740.9	2738.4
7.5°	2746.6	2719.1	2731.8	2726.6	2724.1
10°	2728.2	2700.8	2715.4	2710.3	2707.8
12.5°	2703.7	2678.3	2695.0	2689.9	2689.4
15°	2661.8	2639.4	2661.8	2661.8	2659.3
17.5°	2609.3	2588.8	2612.8	2614.3	2612.8
20°	2572.5	2550.1	2580.2	2577.7	2580.2
22.5°	2527.6	2509.1	2541.4	2534.8	2537.3
25°	2457.7	2440.2	2475.5	2467.9	2467.9
27.5°	2375.0	2362.5	2401.0	2392.9	2392.9
30°	2319.9	2307.4	2347.9	2337.7	2337.7
32.5°	2258.6	2250.1	2288.7	2276.5	2276.5
35°	2161.6	2156.6	2194.8	2179.5	2179.5
37.5°	2061.6	2057.1	2091.7	2073.2	2067.2
40°	1988.1	1985.6	2016.2	1995.7	1995.7
42.5°	1914.6	1912.1	1938.6	1914.1	1914.1
45°	1801.8	1796.8	1814.5	1791.5	1786.5
47.5°	1678.8	1673.8	1684.9	1659.8	1657.3
50°	1595.1	1590.1	1595.1	1572.0	1569.5
52.5°	1509.3	1500.3	1501.2	1478.2	1477.7
55°	1378.1	1360.7	1360.3	1339.9	1339.9
57.5°	1239.3	1216.3	1218.4	1201.0	1198.5
60°	1143.3	1118.4	1120.4	1105.0	1102.5
62.5°	1049.4	1020.5	1026.5	1009.1	1008.6
65°	893.2	873.3	875.4	867.7	867.7
67.5°	743.2	724.7	738.1	731.9	731.4
70°	632.9	620.4	638.0	638.0	635.5
72.5°	530.8	530.3	552.3	552.3	553.8
75°	385.4	402.8	426.2	428.8	428.8
77.5°	257.3	288.2	313.9	314.9	314.4
80°	183.8	218.7	242.5	247.5	245.0
82.5°	124.5	161.5	181.2	186.2	183.8
85°	56.1	86.1	102.1	104.6	102.1
87.5°	16.3	34.3	40.8	40.7	36.8
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)