

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563029

Luminaire Tested: **SQ4-PC3-125U-075D-940-1D-UNV-STD-W-12**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563029
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-125U-075D-940-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 20492.6 lumens
Efficiency: N/A
Efficacy: 118.9 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 172.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563029
CATALOG NUMBER: SQ4-PC3-125U-075D-940-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P563029

CATALOG NUMBER: SQ4-PC3-125U-075D-940-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	37				37
1	95	91	87	83	86	82	79	76	67	64	62	52	51	49	39	38	37				31	
2	86	79	73	68	78	72	67	62	58	55	52	46	43	41	34	33	31				26	
3	79	69	62	57	71	63	57	52	51	47	43	40	37	35	30	28	27				22	
4	72	61	54	48	65	56	49	44	46	41	37	36	33	30	27	25	23				19	
5	66	55	47	41	59	50	43	38	41	36	32	32	29	26	24	22	20				16	
6	61	49	41	35	55	45	38	33	37	31	27	29	25	22	22	19	17				14	
7	56	44	36	31	51	40	33	28	33	28	24	26	23	20	20	17	15				13	
8	52	40	32	27	47	36	30	25	30	25	21	24	20	18	18	16	14				11	
9	48	36	29	24	44	33	27	22	27	22	19	22	18	16	17	14	12				10	
10	45	33	26	21	41	30	24	20	25	20	17	20	17	14	16	13	11				9	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8477	8477	8477
5°	8541	8485	8454
10°	8520	8480	8456
15°	8475	8475	8467
20°	8419	8444	8444
25°	8340	8400	8374
30°	8238	8338	8302
35°	8115	8240	8183
40°	7982	8094	8012
45°	7837	7892	7770
50°	7632	7632	7509
55°	7389	7294	7184
60°	7032	6891	6781
65°	6500	6370	6314
70°	5691	5737	5714
75°	4579	5064	5095
80°	3255	4295	4339
85°	1980	3603	3603



TEST NUMBER: P563029

CATALOG NUMBER: SQ4-PC3-125U-075D-940-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	260.9	1.3
10°-20°	748.6	3.7
20°-30°	1133.6	5.5
30°-40°	1359.0	6.6
40°-50°	1385.8	6.8
50°-60°	1209.7	5.9
60°-70°	866.0	4.2
70°-80°	446.1	2.2
80°-90°	117.5	0.6
90°-100°	939.5	4.6
100°-110°	2530.9	12.4
110°-120°	2656.1	13.0
120°-130°	2155.4	10.5
130°-140°	1690.4	8.2
140°-150°	1297.8	6.3
150°-160°	933.1	4.6
160°-170°	570.1	2.8
170°-180°	192.2	0.9
0°-30°	2143.0	10.5
0°-40°	3502.1	17.1
0°-60°	6097.5	29.8
0°-90°	7527.1	36.7
90°-120°	6126.5	29.9
90°-150°	11270.0	55.0
90°-180°	12965.0	63.3
0°-180°	20492.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2756	2756	2756	2756	2756	
5°	2766	2739	2749	2741	2738	263
15°	2662	2639	2662	2662	2659	751
25°	2458	2440	2476	2468	2468	1131
35°	2162	2157	2195	2180	2180	1352
45°	1802	1797	1814	1792	1786	1387
55°	1378	1361	1360	1340	1340	1229
65°	893	873	875	868	868	883
75°	385	403	426	429	429	416
85°	56	86	102	105	102	76
90°	5	15	31	33	33	12
95°	143	511	1540	788	545	150
105°	468	728	2799	4188	3930	492
115°	826	1012	2331	4504	5094	813
125°	1128	1296	2093	3537	4163	1007
135°	1359	1516	2034	2854	3231	1049
145°	1571	1694	2008	2440	2620	985
155°	1783	1848	1990	2189	2259	821
165°	1934	1957	1998	2078	2088	545
175°	2011	2008	2001	2029	2024	191
180°	2008	2008	2008	2008	2008	

TEST NUMBER: P563029

CATALOG NUMBER: SQ4-PC3-125U-075D-940-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2756.3	2756.3	2756.3	2756.3	2756.3
2.5°	2772.6	2748.7	2756.3	2749.9	2739.9
5°	2766.5	2739.0	2748.6	2740.9	2738.4
7.5°	2746.6	2719.1	2731.8	2726.6	2724.1
10°	2728.2	2700.8	2715.4	2710.3	2707.8
12.5°	2703.7	2678.3	2695.0	2689.9	2689.4
15°	2661.8	2639.4	2661.8	2661.8	2659.3
17.5°	2609.3	2588.8	2612.8	2614.3	2612.8
20°	2572.5	2550.1	2580.2	2577.7	2580.2
22.5°	2527.6	2509.1	2541.4	2534.8	2537.3
25°	2457.7	2440.2	2475.5	2467.9	2467.9
27.5°	2375.0	2362.5	2401.0	2392.9	2392.9
30°	2319.9	2307.4	2347.9	2337.7	2337.7
32.5°	2258.6	2250.1	2288.7	2276.5	2276.5
35°	2161.6	2156.6	2194.8	2179.5	2179.5
37.5°	2061.6	2057.1	2091.7	2073.2	2067.2
40°	1988.1	1985.6	2016.2	1995.7	1995.7
42.5°	1914.6	1912.1	1938.6	1914.1	1914.1
45°	1801.8	1796.8	1814.5	1791.5	1786.5
47.5°	1678.8	1673.8	1684.9	1659.8	1657.3
50°	1595.1	1590.1	1595.1	1572.0	1569.5
52.5°	1509.3	1500.3	1501.2	1478.2	1477.7
55°	1378.1	1360.7	1360.3	1339.9	1339.9
57.5°	1239.3	1216.3	1218.4	1201.0	1198.5
60°	1143.3	1118.4	1120.4	1105.0	1102.5
62.5°	1049.4	1020.5	1026.5	1009.1	1008.6
65°	893.2	873.3	875.4	867.7	867.7
67.5°	743.2	724.7	738.1	731.9	731.4
70°	632.9	620.4	638.0	638.0	635.5
72.5°	530.8	530.3	552.3	552.3	553.8
75°	385.4	402.8	426.2	428.8	428.8
77.5°	257.3	288.2	313.9	314.9	314.4
80°	183.8	218.7	242.5	247.5	245.0
82.5°	124.5	161.5	181.2	186.2	183.8
85°	56.1	86.1	102.1	104.6	102.1
87.5°	17.4	37.3	47.0	47.4	43.4
90°	5.1	15.1	30.7	33.3	33.3
92.5°	62.4	220.5	436.0	209.9	145.8
95°	143.3	511.0	1540.2	787.6	545.0
97.5°	228.7	585.0	2415.7	2018.1	1521.8
100°	294.2	614.4	2694.1	2818.8	2338.5
102.5°	357.7	655.9	2786.2	3418.4	3024.1
105°	468.2	728.4	2799.0	4187.5	3929.8
107.5°	572.6	804.7	2679.8	4582.7	4649.3
110°	642.2	862.3	2571.3	4705.4	4948.1



TEST NUMBER: P563029

CATALOG NUMBER: SQ4-PC3-125U-075D-940-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	715.9	920.0	2466.9	4678.3	5077.1
115°	826.4	1011.5	2330.8	4503.6	5093.9
117.5°	927.2	1100.8	2225.4	4224.7	4882.1
120°	992.7	1160.3	2172.2	4024.5	4699.9
122.5°	1050.0	1215.6	2133.3	3819.8	4493.2
125°	1128.3	1295.9	2092.8	3537.2	4162.7
127.5°	1203.5	1368.6	2067.3	3288.1	3846.4
130°	1248.5	1413.6	2057.0	3145.3	3635.6
132.5°	1293.6	1456.7	2046.8	3019.5	3469.8
135°	1358.6	1516.2	2034.0	2853.6	3231.4
137.5°	1420.5	1571.6	2027.3	2712.9	3023.1
140°	1463.5	1608.5	2021.2	2626.3	2906.4
142.5°	1508.5	1643.6	2017.1	2545.4	2781.6
145°	1570.9	1693.5	2008.4	2439.8	2619.9
147.5°	1638.5	1745.0	1999.7	2350.9	2492.5
150°	1683.5	1776.0	1995.6	2295.1	2412.6
152.5°	1724.4	1805.0	1993.6	2249.5	2345.1
155°	1783.3	1848.3	1990.5	2189.1	2259.1
157.5°	1834.9	1885.5	1991.0	2146.6	2193.6
160°	1867.7	1910.2	1993.1	2121.8	2156.8
162.5°	1896.3	1930.9	1995.1	2101.1	2126.1
165°	1934.2	1956.7	1998.2	2077.7	2087.7
167.5°	1964.9	1977.9	2000.7	2059.7	2063.7
170°	1985.4	1990.4	2000.7	2049.3	2049.3
172.5°	1997.7	1998.7	2002.8	2039.1	2039.1
175°	2011.0	2008.5	2000.7	2028.8	2023.8
177.5°	2016.6	2012.6	2002.3	2018.6	2014.5
180°	2008.4	2008.4	2008.4	2008.4	2008.4

(END OF REPORT)