

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563413

Luminaire Tested: **SQ4-PP3-075U-075D-940-1D-UNV-STD-W-12**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563413
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-22, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-075U-075D-940-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 15218.4 lumens
Efficiency: N/A
Efficacy: 114.1 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 133.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563413
CATALOG NUMBER: SQ4-PP3-075U-075D-940-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P563413

CATALOG NUMBER: SQ4-PP3-075U-075D-940-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55	49				
1	98	94	90	86	90	86	83	80	73	71	68	61	59	57	49	48	47	42				
2	89	82	76	71	82	76	70	66	64	60	57	53	51	48	43	42	40	35				
3	81	72	65	59	75	67	60	55	57	52	48	47	44	41	39	36	34	30				
4	75	64	56	50	68	59	52	47	50	45	41	42	38	35	35	32	29	26				
5	68	57	49	43	63	53	46	40	45	40	35	38	34	30	31	28	26	22				
6	63	51	43	37	58	47	40	35	41	35	31	34	30	27	28	25	23	20				
7	58	46	38	33	54	43	36	31	37	31	27	31	27	24	26	23	20	18				
8	54	42	34	29	50	39	32	27	34	28	24	28	24	21	24	20	18	16				
9	50	38	31	26	46	36	29	24	31	25	22	26	22	19	22	19	16	14				
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15	13				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8953	8953	8953
5°	9019	8964	8932
10°	9004	8940	8900
15°	8944	8895	8847
20°	8885	8835	8768
25°	8779	8719	8632
30°	8617	8571	8463
35°	8391	8334	8228
40°	8123	8072	7980
45°	7901	7846	7768
50°	7617	7569	7495
55°	7223	7127	7073
60°	6576	6388	6356
65°	5793	5552	5533
70°	5001	4795	4795
75°	4305	4244	4184
80°	3795	3841	3751
85°	2971	3243	3243



TEST NUMBER: P563413

CATALOG NUMBER: SQ4-PP3-075U-075D-940-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	275.3	1.8
10°-20°	786.0	5.2
20°-30°	1177.4	7.7
30°-40°	1381.0	9.1
40°-50°	1385.3	9.1
50°-60°	1181.8	7.8
60°-70°	770.7	5.1
70°-80°	386.7	2.5
80°-90°	110.0	0.7
90°-100°	562.1	3.7
100°-110°	1546.5	10.2
110°-120°	1596.3	10.5
120°-130°	1279.0	8.4
130°-140°	1004.5	6.6
140°-150°	769.8	5.1
150°-160°	553.5	3.6
160°-170°	338.4	2.2
170°-180°	114.1	0.7
0°-30°	2238.7	14.7
0°-40°	3619.7	23.8
0°-60°	6186.8	40.7
0°-90°	7454.3	49.0
90°-120°	3704.9	24.3
90°-150°	6758.2	44.4
90°-180°	7764.0	51.0
0°-180°	15218.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2911	2911	2911	2911	2911	
5°	2922	2894	2904	2893	2893	277
15°	2809	2782	2794	2784	2779	793
25°	2587	2557	2569	2546	2544	1190
35°	2235	2213	2220	2194	2192	1396
45°	1817	1804	1804	1786	1786	1399
55°	1347	1342	1329	1322	1319	1197
65°	796	781	763	758	760	794
75°	362	362	357	355	352	393
85°	84	92	92	92	92	99
90°	2	10	18	23	23	9
95°	84	307	994	425	271	88
105°	276	425	1704	2595	2422	291
115°	489	596	1367	2722	3089	483
125°	674	769	1240	2098	2457	602
135°	814	903	1204	1696	1920	628
145°	941	1005	1187	1445	1557	590
155°	1065	1100	1179	1299	1336	489
165°	1151	1166	1184	1233	1240	324
175°	1192	1194	1187	1202	1199	113
180°	1192	1192	1192	1192	1192	



TEST NUMBER: P563413

CATALOG NUMBER: SQ4-PP3-075U-075D-940-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2911.3	2911.3	2911.3	2911.3	2911.3
2.5°	2929.6	2905.7	2911.3	2906.9	2894.9
5°	2921.5	2894.0	2903.6	2893.4	2893.4
7.5°	2901.6	2871.6	2881.2	2870.9	2870.4
10°	2883.2	2853.3	2862.8	2852.5	2850.0
12.5°	2856.7	2826.7	2838.3	2826.0	2825.5
15°	2809.2	2781.8	2793.9	2783.6	2778.6
17.5°	2755.6	2725.7	2740.3	2726.0	2724.0
20°	2714.8	2684.9	2699.5	2679.1	2679.1
22.5°	2665.8	2635.9	2652.5	2626.0	2626.0
25°	2587.2	2557.3	2569.4	2546.3	2543.8
27.5°	2493.8	2464.4	2477.0	2451.0	2450.5
30°	2426.5	2399.0	2413.7	2385.6	2383.1
32.5°	2353.0	2327.5	2338.2	2310.1	2307.6
35°	2235.1	2212.7	2219.8	2194.2	2191.7
37.5°	2111.1	2088.2	2096.3	2074.3	2073.4
40°	2023.3	2008.4	2010.6	1992.6	1987.6
42.5°	1941.7	1924.7	1926.9	1909.0	1908.0
45°	1816.7	1804.2	1803.9	1786.1	1786.1
47.5°	1684.0	1674.5	1671.7	1656.9	1656.4
50°	1592.1	1584.7	1581.9	1569.1	1566.6
52.5°	1496.2	1492.7	1484.0	1473.2	1472.7
55°	1347.2	1342.2	1329.3	1321.6	1319.1
57.5°	1185.4	1175.4	1160.9	1149.8	1151.7
60°	1069.1	1059.1	1038.5	1033.4	1033.4
62.5°	956.8	944.8	924.2	917.1	921.1
65°	796.1	781.1	762.9	757.9	760.3
67.5°	650.1	636.7	617.0	616.9	614.9
70°	556.2	548.7	533.3	533.3	533.3
72.5°	472.5	469.0	457.7	457.7	455.7
75°	362.3	362.3	357.2	354.6	352.1
77.5°	271.5	272.5	269.9	267.3	262.8
80°	214.3	219.3	216.9	214.3	211.8
82.5°	161.3	166.2	165.8	161.2	160.7
85°	84.2	91.7	91.9	91.9	91.9
87.5°	23.0	32.4	36.2	37.3	39.3
90°	2.5	10.0	17.8	22.8	22.8
92.5°	35.0	149.5	259.2	99.5	81.7
95°	83.7	306.8	994.0	425.1	271.3
97.5°	136.4	340.2	1516.9	1168.8	824.6
100°	175.0	360.9	1681.2	1696.9	1384.5
102.5°	211.5	385.5	1723.8	2105.3	1818.7
105°	276.4	425.2	1704.0	2595.2	2421.7
107.5°	338.3	474.1	1607.2	2835.2	2886.7
110°	382.9	506.9	1534.1	2894.8	3073.4

TEST NUMBER: P563413

CATALOG NUMBER: SQ4-PP3-075U-075D-940-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	423.5	543.5	1461.1	2856.4	3128.1
115°	489.4	596.0	1366.8	2721.6	3088.6
117.5°	552.3	650.5	1306.9	2532.5	2947.6
120°	590.8	685.1	1280.6	2390.8	2819.8
122.5°	625.3	719.5	1262.3	2266.6	2673.7
125°	674.5	768.7	1240.0	2097.7	2457.2
127.5°	721.2	810.9	1225.3	1956.7	2272.1
130°	745.5	837.3	1217.2	1872.9	2160.5
132.5°	773.9	865.7	1211.1	1799.2	2059.1
135°	814.0	903.2	1204.5	1696.4	1919.6
137.5°	851.5	934.3	1198.9	1613.4	1797.4
140°	879.9	956.8	1196.9	1558.2	1724.3
142.5°	904.3	975.2	1192.8	1509.0	1651.3
145°	940.8	1005.2	1186.7	1445.4	1557.0
147.5°	979.8	1035.4	1183.7	1389.1	1478.4
150°	1004.2	1053.8	1181.7	1358.2	1427.6
152.5°	1026.5	1072.1	1179.6	1331.6	1389.1
155°	1065.0	1099.7	1179.1	1299.2	1336.4
157.5°	1092.9	1121.2	1179.1	1272.5	1298.3
160°	1113.2	1135.5	1179.1	1258.2	1278.0
162.5°	1129.4	1147.8	1181.2	1245.9	1261.8
165°	1151.2	1166.1	1184.2	1232.6	1240.0
167.5°	1166.5	1177.9	1186.7	1221.3	1223.3
170°	1176.6	1184.0	1186.7	1217.2	1217.2
172.5°	1184.7	1188.2	1186.7	1211.0	1209.1
175°	1191.8	1194.3	1186.7	1201.9	1199.4
177.5°	1193.8	1193.8	1185.7	1197.8	1193.8
180°	1191.8	1191.8	1191.8	1191.8	1191.8

(END OF REPORT)