

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563749

Luminaire Tested: **SQ4-PP3-125U-125D-940-1D-UNV-STD-W-12**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563749
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-125U-125D-940-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 25604.5 lumens
Efficiency: N/A
Efficacy: 109.5 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 233.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563749
CATALOG NUMBER: SQ4-PP3-125U-125D-940-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P563749

CATALOG NUMBER: SQ4-PP3-125U-125D-940-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	49				
1	98	94	90	86	90	86	83	80	73	71	69	61	59	58	49	48	47	42				
2	89	82	76	71	82	76	71	66	64	60	57	54	51	48	44	42	40	35				
3	81	72	65	59	75	67	60	55	57	52	48	47	44	41	39	36	34	30				
4	75	64	56	50	69	59	52	47	50	45	41	42	38	35	35	32	30	26				
5	68	57	49	43	63	53	46	40	45	40	35	38	34	31	31	28	26	23				
6	63	51	43	37	58	48	40	35	41	35	31	34	30	27	28	25	23	20				
7	58	46	38	33	54	43	36	31	37	31	27	31	27	24	26	23	20	18				
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18	16				
9	50	38	31	26	46	36	29	24	31	25	22	26	22	19	22	19	16	14				
10	47	35	28	23	43	33	26	22	28	23	20	24	20	17	20	17	15	13				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15181	15181	15181
5°	15293	15199	15146
10°	15267	15159	15091
15°	15166	15083	15001
20°	15065	14980	14867
25°	14886	14783	14637
30°	14611	14534	14350
35°	14229	14131	13952
40°	13773	13687	13530
45°	13398	13303	13171
50°	12916	12833	12709
55°	12248	12085	11993
60°	11150	10830	10777
65°	9823	9414	9382
70°	8480	8130	8130
75°	7299	7197	7094
80°	6436	6512	6360
85°	5039	5494	5494



TEST NUMBER: P563749

CATALOG NUMBER: SQ4-PP3-125U-125D-940-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	466.8	1.8
10°-20°	1332.8	5.2
20°-30°	1996.4	7.8
30°-40°	2341.6	9.1
40°-50°	2348.9	9.2
50°-60°	2003.8	7.8
60°-70°	1306.8	5.1
70°-80°	655.6	2.6
80°-90°	186.2	0.7
90°-100°	939.5	3.7
100°-110°	2530.9	9.9
110°-120°	2656.1	10.4
120°-130°	2155.4	8.4
130°-140°	1690.4	6.6
140°-150°	1297.8	5.1
150°-160°	933.1	3.6
160°-170°	570.1	2.2
170°-180°	192.2	0.8
0°-30°	3796.0	14.8
0°-40°	6137.6	24.0
0°-60°	10490.4	41.0
0°-90°	12639.0	49.4
90°-120°	6126.5	23.9
90°-150°	11270.0	44.0
90°-180°	12965.0	50.6
0°-180°	25604.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4936	4936	4936	4936	4936	
5°	4954	4907	4923	4906	4906	470
15°	4763	4717	4737	4720	4711	1344
25°	4387	4336	4357	4318	4313	2017
35°	3790	3752	3764	3721	3716	2367
45°	3080	3059	3059	3028	3028	2372
55°	2284	2276	2254	2241	2237	2030
65°	1350	1324	1294	1285	1289	1347
75°	614	614	606	601	597	666
85°	143	156	156	156	156	168
90°	5	15	31	33	33	15
95°	143	511	1540	788	545	150
105°	468	728	2799	4188	3930	492
115°	826	1012	2331	4504	5094	813
125°	1128	1296	2093	3537	4163	1007
135°	1359	1516	2034	2854	3231	1049
145°	1571	1694	2008	2440	2620	985
155°	1783	1848	1990	2189	2259	821
165°	1934	1957	1998	2078	2088	545
175°	2011	2008	2001	2029	2024	191
180°	2008	2008	2008	2008	2008	

TEST NUMBER: P563749

CATALOG NUMBER: SQ4-PP3-125U-125D-940-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4936.3	4936.3	4936.3	4936.3	4936.3
2.5°	4967.5	4926.9	4936.3	4929.0	4908.7
5°	4953.7	4907.1	4923.4	4906.1	4906.1
7.5°	4919.9	4869.1	4885.3	4868.0	4867.1
10°	4888.8	4838.0	4854.1	4836.7	4832.5
12.5°	4843.8	4793.0	4812.6	4791.8	4791.0
15°	4763.3	4716.8	4737.3	4719.8	4711.4
17.5°	4672.4	4621.7	4646.5	4622.2	4618.8
20°	4603.2	4552.5	4577.3	4542.7	4542.7
22.5°	4520.2	4469.4	4497.7	4452.7	4452.7
25°	4386.9	4336.1	4356.6	4317.6	4313.4
27.5°	4228.6	4178.6	4200.0	4155.9	4155.0
30°	4114.3	4067.8	4092.7	4045.0	4040.8
32.5°	3989.7	3946.6	3964.7	3917.0	3912.7
35°	3789.9	3751.8	3763.9	3720.6	3716.3
37.5°	3579.6	3540.7	3554.5	3517.3	3515.6
40°	3430.8	3405.4	3409.2	3378.7	3370.2
42.5°	3292.3	3263.6	3267.2	3236.9	3235.2
45°	3080.4	3059.2	3058.7	3028.4	3028.4
47.5°	2855.4	2839.3	2834.6	2809.5	2808.7
50°	2699.6	2686.9	2682.3	2660.6	2656.4
52.5°	2537.0	2531.0	2516.2	2498.0	2497.2
55°	2284.3	2275.8	2254.0	2240.9	2236.7
57.5°	2010.0	1993.1	1968.5	1949.5	1952.9
60°	1812.7	1795.8	1760.8	1752.2	1752.2
62.5°	1622.4	1602.1	1567.0	1555.0	1561.8
65°	1349.8	1324.4	1293.6	1285.0	1289.2
67.5°	1102.4	1079.5	1046.1	1046.0	1042.6
70°	943.1	930.5	904.2	904.2	904.2
72.5°	801.2	795.3	776.1	776.1	772.7
75°	614.3	614.3	605.7	601.3	597.0
77.5°	460.3	462.0	457.7	453.2	445.6
80°	363.4	371.9	367.7	363.3	359.1
82.5°	273.4	281.9	281.2	273.4	272.6
85°	142.8	155.5	155.7	155.7	155.7
87.5°	39.1	54.6	61.5	62.1	65.5
90°	5.1	15.1	30.7	33.3	33.3
92.5°	62.4	220.5	436.0	209.9	145.8
95°	143.3	511.0	1540.2	787.6	545.0
97.5°	228.7	585.0	2415.7	2018.1	1521.8
100°	294.2	614.4	2694.1	2818.8	2338.5
102.5°	357.7	655.9	2786.2	3418.4	3024.1
105°	468.2	728.4	2799.0	4187.5	3929.8
107.5°	572.6	804.7	2679.8	4582.7	4649.3
110°	642.2	862.3	2571.3	4705.4	4948.1

TEST NUMBER: P563749

CATALOG NUMBER: SQ4-PP3-125U-125D-940-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	715.9	920.0	2466.9	4678.3	5077.1
115°	826.4	1011.5	2330.8	4503.6	5093.9
117.5°	927.2	1100.8	2225.4	4224.7	4882.1
120°	992.7	1160.3	2172.2	4024.5	4699.9
122.5°	1050.0	1215.6	2133.3	3819.8	4493.2
125°	1128.3	1295.9	2092.8	3537.2	4162.7
127.5°	1203.5	1368.6	2067.3	3288.1	3846.4
130°	1248.5	1413.6	2057.0	3145.3	3635.6
132.5°	1293.6	1456.7	2046.8	3019.5	3469.8
135°	1358.6	1516.2	2034.0	2853.6	3231.4
137.5°	1420.5	1571.6	2027.3	2712.9	3023.1
140°	1463.5	1608.5	2021.2	2626.3	2906.4
142.5°	1508.5	1643.6	2017.1	2545.4	2781.6
145°	1570.9	1693.5	2008.4	2439.8	2619.9
147.5°	1638.5	1745.0	1999.7	2350.9	2492.5
150°	1683.5	1776.0	1995.6	2295.1	2412.6
152.5°	1724.4	1805.0	1993.6	2249.5	2345.1
155°	1783.3	1848.3	1990.5	2189.1	2259.1
157.5°	1834.9	1885.5	1991.0	2146.6	2193.6
160°	1867.7	1910.2	1993.1	2121.8	2156.8
162.5°	1896.3	1930.9	1995.1	2101.1	2126.1
165°	1934.2	1956.7	1998.2	2077.7	2087.7
167.5°	1964.9	1977.9	2000.7	2059.7	2063.7
170°	1985.4	1990.4	2000.7	2049.3	2049.3
172.5°	1997.7	1998.7	2002.8	2039.1	2039.1
175°	2011.0	2008.5	2000.7	2028.8	2023.8
177.5°	2016.6	2012.6	2002.3	2018.6	2014.5
180°	2008.4	2008.4	2008.4	2008.4	2008.4

(END OF REPORT)