

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563797

Luminaire Tested: **SQ4-PP3-150U-075D-940-1D-UNV-STD-W-12**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563797
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-25, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-150U-075D-940-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 23079.1 lumens
Efficiency: N/A
Efficacy: 118.4 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 194.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563797
CATALOG NUMBER: SQ4-PP3-150U-075D-940-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P563797

CATALOG NUMBER: SQ4-PP3-150U-075D-940-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40	32
1	94	90	86	83	84	81	78	75	65	62	60	49	48	47	35	35	34	27
2	86	79	73	68	77	71	66	62	57	53	50	43	41	39	31	30	29	23
3	78	69	62	56	70	62	56	52	50	46	42	38	36	33	28	26	25	20
4	71	61	53	48	64	55	49	44	44	40	36	34	31	28	25	23	21	17
5	65	54	46	41	59	49	42	37	40	35	31	31	27	25	22	20	18	15
6	60	49	41	35	54	44	37	32	36	31	27	28	24	21	20	18	16	13
7	56	44	36	31	50	40	33	28	32	27	24	25	22	19	19	16	14	12
8	51	40	32	27	46	36	29	25	29	24	21	23	19	17	17	15	13	10
9	48	36	29	24	43	33	26	22	27	22	19	21	18	15	16	13	12	9
10	45	33	26	21	40	30	24	20	25	20	17	19	16	14	14	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8953	8953	8953
5°	9019	8964	8932
10°	9004	8940	8900
15°	8944	8895	8847
20°	8885	8835	8768
25°	8779	8719	8632
30°	8617	8571	8463
35°	8391	8334	8228
40°	8123	8072	7980
45°	7901	7846	7768
50°	7617	7569	7495
55°	7223	7127	7073
60°	6576	6388	6356
65°	5793	5552	5533
70°	5001	4795	4795
75°	4305	4244	4184
80°	3795	3841	3751
85°	2971	3243	3243



TEST NUMBER: P563797

CATALOG NUMBER: SQ4-PP3-150U-075D-940-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	275.3	1.2
10°-20°	786.0	3.4
20°-30°	1177.4	5.1
30°-40°	1381.0	6.0
40°-50°	1385.3	6.0
50°-60°	1181.8	5.1
60°-70°	770.7	3.3
70°-80°	386.7	1.7
80°-90°	112.1	0.5
90°-100°	1126.1	4.9
100°-110°	3044.8	13.2
110°-120°	3201.2	13.9
120°-130°	2600.2	11.3
130°-140°	2039.6	8.8
140°-150°	1565.4	6.8
150°-160°	1125.8	4.9
160°-170°	687.8	3.0
170°-180°	231.9	1.0
0°-30°	2238.7	9.7
0°-40°	3619.7	15.7
0°-60°	6186.8	26.8
0°-90°	7456.3	32.3
90°-120°	7372.0	31.9
90°-150°	13577.3	58.8
90°-180°	15623.0	67.7
0°-180°	23079.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2911	2911	2911	2911	2911	
5°	2922	2894	2904	2893	2893	277
15°	2809	2782	2794	2784	2779	793
25°	2587	2557	2569	2546	2544	1190
35°	2235	2213	2220	2194	2192	1396
45°	1817	1804	1804	1786	1786	1399
55°	1347	1342	1329	1322	1319	1197
65°	796	781	763	758	760	794
75°	362	362	357	355	352	393
85°	84	92	92	92	92	99
90°	5	15	34	36	34	15
95°	175	613	1873	969	576	183
105°	566	875	3378	4982	4778	596
115°	996	1218	2801	5423	6122	984
125°	1364	1563	2525	4261	5005	1216
135°	1635	1829	2457	3440	3894	1264
145°	1902	2044	2423	2945	3169	1190
155°	2147	2231	2402	2642	2728	990
165°	2337	2360	2413	2507	2520	658
175°	2426	2423	2415	2446	2441	230
180°	2423	2423	2423	2423	2423	

TEST NUMBER: P563797

CATALOG NUMBER: SQ4-PP3-150U-075D-940-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2911.3	2911.3	2911.3	2911.3	2911.3
2.5°	2929.6	2905.7	2911.3	2906.9	2894.9
5°	2921.5	2894.0	2903.6	2893.4	2893.4
7.5°	2901.6	2871.6	2881.2	2870.9	2870.4
10°	2883.2	2853.3	2862.8	2852.5	2850.0
12.5°	2856.7	2826.7	2838.3	2826.0	2825.5
15°	2809.2	2781.8	2793.9	2783.6	2778.6
17.5°	2755.6	2725.7	2740.3	2726.0	2724.0
20°	2714.8	2684.9	2699.5	2679.1	2679.1
22.5°	2665.8	2635.9	2652.5	2626.0	2626.0
25°	2587.2	2557.3	2569.4	2546.3	2543.8
27.5°	2493.8	2464.4	2477.0	2451.0	2450.5
30°	2426.5	2399.0	2413.7	2385.6	2383.1
32.5°	2353.0	2327.5	2338.2	2310.1	2307.6
35°	2235.1	2212.7	2219.8	2194.2	2191.7
37.5°	2111.1	2088.2	2096.3	2074.3	2073.4
40°	2023.3	2008.4	2010.6	1992.6	1987.6
42.5°	1941.7	1924.7	1926.9	1909.0	1908.0
45°	1816.7	1804.2	1803.9	1786.1	1786.1
47.5°	1684.0	1674.5	1671.7	1656.9	1656.4
50°	1592.1	1584.7	1581.9	1569.1	1566.6
52.5°	1496.2	1492.7	1484.0	1473.2	1472.7
55°	1347.2	1342.2	1329.3	1321.6	1319.1
57.5°	1185.4	1175.4	1160.9	1149.8	1151.7
60°	1069.1	1059.1	1038.5	1033.4	1033.4
62.5°	956.8	944.8	924.2	917.1	921.1
65°	796.1	781.1	762.9	757.9	760.3
67.5°	650.1	636.7	617.0	616.9	614.9
70°	556.2	548.7	533.3	533.3	533.3
72.5°	472.5	469.0	457.7	457.7	455.7
75°	362.3	362.3	357.2	354.6	352.1
77.5°	271.5	272.5	269.9	267.3	262.8
80°	214.3	219.3	216.9	214.3	211.8
82.5°	161.3	166.2	165.8	161.2	160.7
85°	84.2	91.7	91.9	91.9	91.9
87.5°	23.5	33.5	39.4	40.0	41.5
90°	5.2	15.4	33.9	36.5	33.9
92.5°	74.1	269.9	532.6	231.2	167.5
95°	174.8	613.4	1872.8	969.2	576.4
97.5°	280.7	703.5	2919.2	2415.8	1774.2
100°	359.9	739.9	3244.7	3383.9	2736.1
102.5°	433.0	790.5	3359.5	4117.9	3633.4
105°	566.0	874.6	3377.8	4982.5	4778.4
107.5°	689.1	970.7	3230.1	5521.8	5589.6
110°	785.1	1040.1	3098.7	5666.6	5954.8



TEST NUMBER: P563797

CATALOG NUMBER: SQ4-PP3-150U-075D-940-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	870.7	1109.4	2977.7	5637.7	6121.7
115°	996.4	1218.3	2801.3	5422.9	6121.7
117.5°	1119.5	1327.6	2685.0	5094.8	5887.0
120°	1194.6	1398.6	2616.1	4859.4	5667.9
122.5°	1265.6	1465.5	2574.4	4607.1	5421.6
125°	1364.1	1563.1	2524.8	4260.7	5005.4
127.5°	1454.9	1650.3	2495.6	3978.0	4632.9
130°	1505.0	1706.5	2483.1	3803.3	4395.0
132.5°	1557.2	1756.6	2470.6	3645.8	4190.5
135°	1635.4	1829.2	2457.0	3440.2	3894.2
137.5°	1714.2	1897.3	2445.6	3273.5	3643.3
140°	1768.4	1939.3	2441.4	3166.1	3495.1
142.5°	1820.6	1981.3	2433.0	3069.2	3357.4
145°	1901.5	2044.3	2423.1	2944.7	3169.1
147.5°	1975.0	2101.5	2411.6	2831.9	3004.3
150°	2029.3	2141.5	2407.5	2770.6	2908.3
152.5°	2079.3	2177.3	2405.4	2713.7	2826.9
155°	2146.6	2230.8	2402.3	2641.6	2728.3
157.5°	2216.5	2275.2	2402.8	2591.4	2648.5
160°	2256.2	2304.6	2404.9	2559.7	2600.5
162.5°	2287.5	2327.8	2407.0	2534.4	2565.0
165°	2337.0	2360.0	2412.7	2506.9	2519.6
167.5°	2371.0	2386.8	2413.2	2483.3	2489.4
170°	2391.8	2399.5	2415.3	2472.7	2472.7
172.5°	2408.5	2410.0	2415.3	2460.1	2458.1
175°	2425.7	2423.2	2415.3	2446.5	2441.4
177.5°	2431.5	2425.3	2414.8	2435.5	2429.4
180°	2423.1	2423.1	2423.1	2423.1	2423.1

(END OF REPORT)