

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P520902

Luminaire Tested: SQ4-025U-0D-92765-1D-UNV-STD-W-4\_4500K

Issue Date: 5-5-2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P520902  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51)  
Test Lab: INNOVATION CENTER  
Issue Date: 5-5-2021  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ4-025U-0D-92765-1D-UNV-STD-W-4\_4500K  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE  
INDIRECT ONLY  
UPLIGHT 250 LUMENS PER FOOT  
Light Source: 2700K-6500K CCT, 90 CRI LEDS, TUNED TO 4500K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2004.0 lumens  
Efficiency: N/A  
Efficacy: 143.1 lumens/watt  
Spacing Criteria (0/90/45): - / - / -  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: Indirect


Input Watts (W): 14  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P520902

CATALOG NUMBER: SQ4-025U-0D-92765-1D-UNV-STD-W-4\_4500K

### Luminous Intensity Polar Plot



TEST NUMBER: P520902

CATALOG NUMBER: SQ4-025U-0D-92765-1D-UNV-STD-W-4\_4500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	0
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	0

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 0°  
 Luminance: 0 cd/sqm

TEST NUMBER: P520902

CATALOG NUMBER: SQ4-025U-0D-92765-1D-UNV-STD-W-4\_4500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	147.0	7.3
100°-110°	418.3	20.9
110°-120°	400.8	20.0
120°-130°	317.2	15.8
130°-140°	254.6	12.7
140°-150°	199.3	9.9
150°-160°	145.8	7.3
160°-170°	90.3	4.5
170°-180°	30.7	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	966.1	48.2
90°-150°	1737.2	86.7
90°-180°	2004.0	100.0
0°-180°	2004.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	1
95°	16	63	285	98	61	18
105°	65	99	426	753	716	69
115°	121	146	323	685	804	119
125°	170	189	308	512	612	153
135°	208	226	305	432	489	161
145°	246	258	307	374	408	154
155°	281	288	315	338	352	130
165°	310	312	318	325	330	87
175°	325	323	322	320	318	31
180°	323	323	323	323	323	

TEST NUMBER: P520902

CATALOG NUMBER: SQ4-025U-0D-92765-1D-UNV-STD-W-4\_4500K

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0
92.5°	4.9	26.0	60.4	17.6	13.2
95°	15.9	63.3	284.6	98.5	60.7
97.5°	29.3	74.2	438.3	313.6	214.9
100°	38.6	80.6	471.7	477.7	368.0
102.5°	48.9	87.6	464.3	611.5	515.7
105°	65.0	98.6	426.3	752.9	715.8
107.5°	81.3	111.4	381.9	792.8	825.9
110°	92.6	120.8	356.3	777.6	851.9

TEST NUMBER: P520902

CATALOG NUMBER: SQ4-025U-0D-92765-1D-UNV-STD-W-4\_4500K

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	103.4	130.2	339.2	741.5	847.5
115°	120.8	146.0	323.2	684.7	804.1
117.5°	136.2	159.8	313.8	622.7	749.1
120°	148.4	168.2	312.8	587.3	708.4
122.5°	158.2	178.0	310.3	556.2	668.7
125°	170.5	189.1	308.5	512.0	612.1
127.5°	183.9	201.3	307.5	485.6	568.1
130°	190.7	208.1	306.1	467.2	539.1
132.5°	198.1	215.0	306.1	452.8	519.0
135°	208.5	225.9	304.8	432.5	488.8
137.5°	218.3	235.3	304.7	415.2	463.9
140°	225.7	243.1	304.2	401.0	447.7
142.5°	234.0	248.6	305.7	389.6	431.5
145°	245.9	258.5	307.3	374.3	407.9
147.5°	256.1	268.4	310.0	358.8	387.9
150°	265.0	273.4	311.0	353.7	374.1
152.5°	271.8	280.7	311.9	346.8	365.8
155°	280.9	287.5	314.6	338.3	352.1
157.5°	292.2	296.2	315.3	334.4	344.2
160°	298.1	301.1	317.7	331.4	339.8
162.5°	301.5	305.0	318.2	328.9	335.4
165°	310.3	311.5	318.3	325.2	330.0
167.5°	316.4	315.3	321.1	324.3	326.2
170°	318.3	317.7	320.2	320.8	323.2
172.5°	322.7	320.7	321.6	319.8	321.8
175°	325.1	323.3	322.0	320.1	317.7
177.5°	326.0	323.2	321.6	319.7	320.2
180°	322.6	322.6	322.6	322.6	322.6

(END OF REPORT)