

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P521163

Luminaire Tested: SQ4-BB-0U-100D-92765-1D-UNV-STD-W-4\_5000K

Issue Date: 5-5-2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P521163  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2009-966-12)  
Test Lab: INNOVATION CENTER  
Issue Date: 5-5-2021  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ4-BB-0U-100D-92765-1D-UNV-STD-W-4\_5000K  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH BLACK BAFFLE  
DOWNLIGHT 1000 LUMENS PER FOOT  
DIRECT ONLY  
Light Source: 2700K-6500K CCT, 90 CRI LEDS, TUNED TO 5000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2665.6 lumens  
Efficiency: N/A  
Efficacy: 63.0 lumens/watt  
Spacing Criteria (0/90/45): 0.85 / 0.97 / 0.97  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: Direct


Input Watts (W): 42.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P521163

CATALOG NUMBER: SQ4-BB-0U-100D-92765-1D-UNV-STD-W-4\_5000K

### Luminous Intensity Polar Plot



TEST NUMBER: P521163

CATALOG NUMBER: SQ4-BB-OU-100D-92765-1D-UNV-STD-W-4\_5000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99		99	98	96		96	94	93	91
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89	86	84	82
3	99	91	85	81	97	90	84	80	87	82	79		85	81	77		82	79	76	74
4	93	84	77	72	91	83	76	72	80	75	71		78	74	70		76	72	69	67
5	87	77	70	65	85	76	70	65	74	68	64		72	67	64		71	66	63	61
6	82	71	64	59	80	70	64	59	69	63	58		67	62	58		66	61	58	56
7	77	66	59	54	75	65	59	54	64	58	53		62	57	53		61	56	53	51
8	72	61	54	50	71	61	54	49	59	53	49		58	53	49		57	52	49	47
9	68	57	50	46	67	57	50	46	56	50	46		55	49	45		54	49	45	44
10	65	54	47	42	63	53	47	42	52	46	42		51	46	42		51	46	42	41

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	20616	20616	20616
5°	20284	20234	20384
10°	18980	19233	19769
15°	17254	17801	18793
20°	15317	16112	17524
25°	13338	14395	16101
30°	11425	12680	14753
35°	9473	10763	13126
40°	7278	8607	11184
45°	5261	6516	8999
50°	3584	4857	7138
55°	2331	3513	5548
60°	1336	2474	4010
65°	354	1511	2030
70°	175	467	583
75°	78	39	0
80°	58	0	0
85°	0	0	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 45°  
 Luminance: 8999 cd/sqm

TEST NUMBER: P521163

CATALOG NUMBER: SQ4-BB-OU-100D-92765-1D-UNV-STD-W-4\_5000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	203.9	7.7
10°-20°	521.5	19.6
20°-30°	652.9	24.5
30°-40°	603.0	22.6
40°-50°	405.2	15.2
50°-60°	209.3	7.9
60°-70°	65.5	2.5
70°-80°	4.2	0.2
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1378.3	51.7
0°-40°	1981.3	74.3
0°-60°	2595.8	97.4
0°-90°	2665.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2665.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2234	2234	2234	2234	2234	
5°	2190	2168	2185	2193	2201	203
15°	1806	1800	1864	1926	1968	503
25°	1310	1321	1414	1511	1582	601
35°	841	862	956	1068	1165	521
45°	403	428	499	597	690	317
55°	145	169	218	280	345	135
65°	16	31	69	84	93	27
75°	2	2	1	0	0	3
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0

TEST NUMBER: P521163

CATALOG NUMBER: SQ4-BB-OU-100D-92765-1D-UNV-STD-W-4\_5000K

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2234.5	2234.5	2234.5	2234.5	2234.5
2.5°	2239.7	2218.6	2224.2	2224.0	2218.1
5°	2190.2	2168.0	2184.8	2192.6	2201.0
7.5°	2097.7	2080.3	2112.6	2136.8	2154.3
10°	2025.9	2011.1	2052.9	2085.9	2110.2
12.5°	1942.9	1931.4	1982.0	2027.2	2058.3
15°	1806.4	1800.1	1863.7	1926.3	1967.5
17.5°	1660.3	1660.1	1732.7	1810.4	1860.1
20°	1560.0	1563.1	1641.0	1726.7	1784.8
22.5°	1459.6	1467.0	1550.2	1639.5	1706.1
25°	1310.2	1320.8	1414.0	1510.8	1581.6
27.5°	1166.7	1182.1	1280.2	1380.7	1467.0
30°	1072.4	1090.4	1190.2	1296.0	1384.8
32.5°	979.9	1001.2	1098.6	1210.5	1300.9
35°	841.1	862.2	955.6	1068.1	1165.4
37.5°	697.7	718.4	809.7	920.4	1025.5
40°	604.3	627.6	714.6	821.9	928.6
42.5°	519.6	542.8	624.6	730.1	830.9
45°	403.2	427.5	499.4	596.7	689.7
47.5°	306.8	333.2	396.3	484.3	569.1
50°	249.7	276.1	338.4	415.9	497.3
52.5°	203.9	229.5	285.6	358.7	433.3
55°	144.9	169.2	218.4	280.4	344.9
57.5°	100.1	121.0	165.2	216.9	267.5
60°	72.4	92.5	134.1	176.1	217.3
62.5°	48.2	66.6	107.2	139.4	167.1
65°	16.2	31.0	69.2	83.5	93.0
67.5°	8.2	9.9	36.3	38.3	41.5
70°	6.5	6.5	17.3	18.4	21.6
72.5°	4.8	4.8	6.9	8.9	9.5
75°	2.2	2.2	1.1	0.0	0.0
77.5°	1.1	1.1	0.9	0.0	0.0
80°	1.1	1.1	0.0	0.0	0.0
82.5°	0.2	0.2	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)