

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P520913

Luminaire Tested: SQ4-050U-0D-92765-1D-UNV-STD-W-4_3500K

Issue Date: 5-5-2021

Test Information

Test Method: LM-79-2019
Report Number: P520913
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51)
Test Lab: INNOVATION CENTER
Issue Date: 5-5-2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-050U-0D-92765-1D-UNV-STD-W-4_3500K
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE
INDIRECT ONLY
UPLIGHT 500 LUMENS PER FOOT
Light Source: 2700K-6500K CCT, 90 CRI LEDS, TUNED TO 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2182.7 lumens
Efficiency: N/A
Efficacy: 138.1 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 15.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P520913
CATALOG NUMBER: SQ4-050U-0D-92765-1D-UNV-STD-W-4_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P520913

CATALOG NUMBER: SQ4-050U-0D-92765-1D-UNV-STD-W-4_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	0
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	0

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 0°
 Luminance: 0 cd/sqm

TEST NUMBER: P520913

CATALOG NUMBER: SQ4-050U-0D-92765-1D-UNV-STD-W-4_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	160.1	7.3
100°-110°	455.6	20.9
110°-120°	436.5	20.0
120°-130°	345.5	15.8
130°-140°	277.3	12.7
140°-150°	217.1	9.9
150°-160°	158.8	7.3
160°-170°	98.4	4.5
170°-180°	33.4	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	1052.2	48.2
90°-150°	1892.1	86.7
90°-180°	2183.0	100.0
0°-180°	2182.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	1
95°	17	69	310	107	66	20
105°	71	107	464	820	780	75
115°	132	159	352	746	876	130
125°	186	206	336	558	667	166
135°	227	246	332	471	532	175
145°	268	282	335	408	444	167
155°	306	313	343	368	384	141
165°	338	339	347	354	359	95
175°	354	352	351	349	346	34
180°	351	351	351	351	351	

TEST NUMBER: P520913

CATALOG NUMBER: SQ4-050U-0D-92765-1D-UNV-STD-W-4_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0
92.5°	5.3	28.3	65.7	19.1	14.4
95°	17.4	69.0	310.0	107.3	66.1
97.5°	31.9	80.8	477.4	341.6	234.1
100°	42.1	87.8	513.7	520.4	400.8
102.5°	53.3	95.4	505.7	666.1	561.7
105°	70.8	107.4	464.3	820.1	779.6
107.5°	88.6	121.4	415.9	863.5	899.6
110°	100.9	131.6	388.1	846.9	927.9

TEST NUMBER: P520913

CATALOG NUMBER: SQ4-050U-0D-92765-1D-UNV-STD-W-4_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	112.6	141.8	369.4	807.6	923.1
115°	131.6	159.0	352.1	745.8	875.8
117.5°	148.3	174.0	341.8	678.3	815.9
120°	161.7	183.2	340.7	639.6	771.6
122.5°	172.4	193.9	338.0	605.8	728.3
125°	185.7	206.0	336.0	557.6	666.7
127.5°	200.3	219.2	335.0	528.9	618.7
130°	207.8	226.7	333.4	508.8	587.2
132.5°	215.8	234.2	333.4	493.2	565.3
135°	227.1	246.1	332.0	471.0	532.4
137.5°	237.8	256.2	331.9	452.3	505.3
140°	245.8	264.8	331.3	436.7	487.7
142.5°	254.9	270.7	333.0	424.3	470.0
145°	267.9	281.6	334.7	407.7	444.2
147.5°	279.0	292.3	337.6	390.9	422.5
150°	288.6	297.7	338.7	385.3	407.5
152.5°	296.1	305.7	339.8	377.8	398.4
155°	306.0	313.1	342.7	368.4	383.5
157.5°	318.3	322.6	343.4	364.2	374.9
160°	324.7	327.9	346.0	361.0	370.1
162.5°	328.4	332.2	346.6	358.2	365.3
165°	338.0	339.3	346.7	354.2	359.4
167.5°	344.6	343.4	349.8	353.2	355.3
170°	346.7	346.1	348.7	349.4	352.1
172.5°	351.5	349.3	350.3	348.4	350.5
175°	354.1	352.1	350.7	348.7	346.0
177.5°	355.1	352.0	350.3	348.2	348.7
180°	351.4	351.4	351.4	351.4	351.4

(END OF REPORT)