

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P520914

Luminaire Tested: SQ4-050U-0D-92765-1D-UNV-STD-W-4\_4000K

Issue Date: 5-5-2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P520914  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51)  
Test Lab: INNOVATION CENTER  
Issue Date: 5-5-2021  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ4-050U-0D-92765-1D-UNV-STD-W-4\_4000K  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE  
INDIRECT ONLY  
UPLIGHT 500 LUMENS PER FOOT  
Light Source: 2700K-6500K CCT, 90 CRI LEDS, TUNED TO 4000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2222.7 lumens  
Efficiency: N/A  
Efficacy: 140.7 lumens/watt  
Spacing Criteria (0/90/45): - / - / -  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: Indirect


Input Watts (W): 15.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P520914

CATALOG NUMBER: SQ4-050U-0D-92765-1D-UNV-STD-W-4\_4000K

### Luminous Intensity Polar Plot



TEST NUMBER: P520914

CATALOG NUMBER: SQ4-050U-0D-92765-1D-UNV-STD-W-4\_4000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	0
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	0

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 0°  
 Luminance: 0 cd/sqm

TEST NUMBER: P520914

CATALOG NUMBER: SQ4-050U-0D-92765-1D-UNV-STD-W-4\_4000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	163.0	7.3
100°-110°	463.9	20.9
110°-120°	444.5	20.0
120°-130°	351.8	15.8
130°-140°	282.4	12.7
140°-150°	221.1	9.9
150°-160°	161.8	7.3
160°-170°	100.2	4.5
170°-180°	34.0	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	1071.5	48.2
90°-150°	1926.7	86.7
90°-180°	2223.0	100.0
0°-180°	2222.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	1
95°	18	70	316	109	67	20
105°	72	109	473	835	794	76
115°	134	162	358	760	892	132
125°	189	210	342	568	679	169
135°	231	251	338	480	542	178
145°	273	287	341	415	452	170
155°	312	319	349	375	390	144
165°	344	346	353	361	366	97
175°	360	358	357	355	352	34
180°	358	358	358	358	358	

TEST NUMBER: P520914

CATALOG NUMBER: SQ4-050U-0D-92765-1D-UNV-STD-W-4\_4000K

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0
92.5°	5.4	28.9	66.9	19.5	14.7
95°	17.7	70.2	315.6	109.3	67.3
97.5°	32.5	82.3	486.1	347.8	238.4
100°	42.9	89.4	523.1	529.9	408.2
102.5°	54.3	97.1	515.0	678.3	572.0
105°	72.1	109.4	472.8	835.1	793.9
107.5°	90.2	123.6	423.5	879.3	916.0
110°	102.7	134.0	395.2	862.4	944.9

TEST NUMBER: P520914

CATALOG NUMBER: SQ4-050U-0D-92765-1D-UNV-STD-W-4\_4000K

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	114.7	144.4	376.2	822.4	940.0
115°	134.0	161.9	358.5	759.5	891.8
117.5°	151.0	177.2	348.0	690.7	830.9
120°	164.6	186.6	346.9	651.3	785.7
122.5°	175.5	197.5	344.2	616.8	741.6
125°	189.1	209.7	342.2	567.8	678.9
127.5°	203.9	223.2	341.1	538.5	630.1
130°	211.6	230.9	339.5	518.1	598.0
132.5°	219.7	238.5	339.5	502.2	575.6
135°	231.3	250.6	338.1	479.6	542.2
137.5°	242.2	260.9	338.0	460.5	514.6
140°	250.3	269.6	337.4	444.7	496.6
142.5°	259.6	275.7	339.0	432.1	478.6
145°	272.8	286.8	340.8	415.1	452.4
147.5°	284.1	297.6	343.8	398.0	430.2
150°	293.9	303.2	344.9	392.3	415.0
152.5°	301.5	311.3	346.0	384.7	405.7
155°	311.6	318.9	349.0	375.2	390.5
157.5°	324.1	328.5	349.7	370.9	381.8
160°	330.6	333.9	352.4	367.6	376.9
162.5°	334.4	338.3	352.9	364.8	372.0
165°	344.2	345.5	353.1	360.7	366.0
167.5°	350.9	349.7	356.2	359.6	361.8
170°	353.1	352.4	355.1	355.8	358.5
172.5°	358.0	355.7	356.7	354.7	356.9
175°	360.5	358.5	357.1	355.0	352.4
177.5°	361.6	358.4	356.7	354.6	355.1
180°	357.8	357.8	357.8	357.8	357.8

(END OF REPORT)