

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P521210

Luminaire Tested: SQ4-BB-100U-100D-92765-1D-UNV-STD-W-4\_2700K

Issue Date: 5-5-2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P521210  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2009-966-12)  
Test Lab: INNOVATION CENTER  
Issue Date: 5-5-2021  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ4-BB-100U-100D-92765-1D-UNV-STD-W-4\_2700K  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH BLACK BAFFLE  
DOWNLIGHT 1000 LUMENS PER FOOT  
UPLIGHT 1000 LUMENS PER FOOT  
Light Source: 2700K-6500K CCT, 90 CRI LEDS, TUNED TO 2700K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6621.1 lumens  
Efficiency: N/A  
Efficacy: 88.8 lumens/watt  
Spacing Criteria (0/90/45): 0.85 / 0.97 / 0.97  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 74.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P521210  
CATALOG NUMBER: SQ4-BB-100U-100D-92765-1D-UNV-STD-W-4\_2700K

### Luminous Intensity Polar Plot



TEST NUMBER: P521210

CATALOG NUMBER: SQ4-BB-100U-100D-92765-1D-UNV-STD-W-4\_2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	44	37			
1	96	92	89	86	87	84	81	79	68	67	65	54	53	52	41	40	40	40	34			
2	89	82	77	73	80	75	71	67	62	59	56	49	47	45	38	37	36	36	30			
3	82	74	67	62	74	67	62	58	56	52	49	45	42	40	35	33	32	32	27			
4	75	66	59	54	69	61	55	50	50	46	43	41	38	36	32	30	29	29	25			
5	70	59	52	47	63	55	48	44	46	41	38	37	34	32	29	27	26	26	23			
6	65	54	47	41	59	50	43	39	42	37	34	34	31	29	27	25	24	24	21			
7	60	49	42	37	55	45	39	35	38	34	30	32	28	26	25	23	22	22	19			
8	56	45	38	33	51	42	35	31	35	31	27	29	26	23	24	21	20	20	17			
9	52	41	34	30	48	38	32	28	33	28	25	27	24	21	22	20	18	18	16			
10	49	38	31	27	45	35	29	26	30	26	23	25	22	20	21	18	17	17	15			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	18854	18854	18854
5°	18551	18504	18642
10°	17357	17588	18079
15°	15779	16280	17186
20°	14007	14735	16025
25°	12198	13164	14724
30°	10448	11596	13492
35°	8664	9844	12004
40°	6655	7871	10228
45°	4812	5960	8231
50°	3278	4441	6528
55°	2131	3212	5073
60°	1222	2262	3666
65°	323	1382	1856
70°	159	426	534
75°	71	36	0
80°	53	0	0
85°	0	0	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 45°  
 Luminance: 8231 cd/sqm

TEST NUMBER: P521210

CATALOG NUMBER: SQ4-BB-100U-100D-92765-1D-UNV-STD-W-4\_2700K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	186.5	2.8
10°-20°	476.9	7.2
20°-30°	597.1	9.0
30°-40°	551.5	8.3
40°-50°	370.6	5.6
50°-60°	191.4	2.9
60°-70°	60.0	0.9
70°-80°	3.8	0.1
80°-90°	0.1	0.0
90°-100°	306.9	4.6
100°-110°	873.2	13.2
110°-120°	836.6	12.6
120°-130°	662.1	10.0
130°-140°	531.5	8.0
140°-150°	416.1	6.3
150°-160°	304.4	4.6
160°-170°	188.6	2.8
170°-180°	64.0	1.0
0°-30°	1260.5	19.0
0°-40°	1812.0	27.4
0°-60°	2373.9	35.9
0°-90°	2437.7	36.8
90°-120°	2016.7	30.5
90°-150°	3626.3	54.8
90°-180°	4183.0	63.2
0°-180°	6621.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2044	2044	2044	2044	2044	
5°	2003	1983	1998	2005	2013	186
15°	1652	1646	1704	1762	1799	460
25°	1198	1208	1293	1382	1446	549
35°	769	788	874	977	1066	476
45°	369	391	457	546	631	290
55°	132	155	200	256	315	124
65°	15	28	63	76	85	25
75°	2	2	1	0	0	3
85°	0	0	0	0	0	0
90°	0	0	0	0	0	1
95°	33	132	594	206	127	38
105°	136	206	890	1572	1494	144
115°	252	305	675	1429	1678	248
125°	356	395	644	1069	1278	319
135°	435	472	636	903	1020	336
145°	513	540	642	781	851	321
155°	586	600	657	706	735	271
165°	648	650	664	679	689	182
175°	679	675	672	668	663	64
180°	674	674	674	674	674	

TEST NUMBER: P521210

CATALOG NUMBER: SQ4-BB-100U-100D-92765-1D-UNV-STD-W-4\_2700K

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2043.5	2043.5	2043.5	2043.5	2043.5
2.5°	2048.3	2028.9	2034.0	2033.9	2028.5
5°	2003.0	1982.7	1998.0	2005.1	2012.9
7.5°	1918.4	1902.5	1932.0	1954.1	1970.2
10°	1852.7	1839.2	1877.4	1907.6	1929.8
12.5°	1776.8	1766.3	1812.6	1853.9	1882.4
15°	1652.0	1646.2	1704.4	1761.6	1799.3
17.5°	1518.4	1518.2	1584.6	1655.6	1701.1
20°	1426.6	1429.5	1500.8	1579.1	1632.2
22.5°	1334.9	1341.6	1417.7	1499.4	1560.3
25°	1198.2	1207.9	1293.1	1381.6	1446.4
27.5°	1066.9	1081.1	1170.7	1262.7	1341.6
30°	980.7	997.2	1088.5	1185.2	1266.4
32.5°	896.1	915.6	1004.7	1107.0	1189.7
35°	769.2	788.5	874.0	976.8	1065.8
37.5°	638.1	657.0	740.5	841.7	937.8
40°	552.6	573.9	653.5	751.6	849.2
42.5°	475.1	496.4	571.2	667.6	759.9
45°	368.8	391.0	456.8	545.7	630.8
47.5°	280.6	304.7	362.4	442.9	520.4
50°	228.4	252.5	309.4	380.3	454.8
52.5°	186.5	209.9	261.2	328.0	396.2
55°	132.5	154.7	199.7	256.4	315.4
57.5°	91.5	110.7	151.1	198.4	244.6
60°	66.2	84.6	122.6	161.0	198.7
62.5°	44.1	60.9	98.1	127.5	152.8
65°	14.8	28.4	63.3	76.3	85.0
67.5°	7.5	9.1	33.2	35.1	38.0
70°	5.9	5.9	15.8	16.9	19.8
72.5°	4.4	4.4	6.3	8.1	8.7
75°	2.0	2.0	1.0	0.0	0.0
77.5°	1.0	1.0	0.8	0.0	0.0
80°	1.0	1.0	0.0	0.0	0.0
82.5°	0.2	0.2	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0
92.5°	10.2	54.3	126.0	36.7	27.7
95°	33.3	132.2	594.1	205.6	126.8
97.5°	61.2	154.8	914.9	654.7	448.6
100°	80.7	168.3	984.6	997.3	768.2
102.5°	102.2	182.8	969.2	1276.6	1076.5
105°	135.7	205.8	889.8	1571.8	1494.2
107.5°	169.8	232.6	797.1	1655.0	1724.1
110°	193.3	252.2	743.9	1623.2	1778.4

TEST NUMBER: P521210

CATALOG NUMBER: SQ4-BB-100U-100D-92765-1D-UNV-STD-W-4\_2700K

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	215.9	271.7	708.0	1547.9	1769.2
115°	252.2	304.8	674.7	1429.4	1678.5
117.5°	284.2	333.6	655.0	1299.9	1563.8
120°	309.8	351.2	653.0	1225.9	1478.8
122.5°	330.3	371.6	647.9	1161.0	1395.8
125°	355.9	394.7	644.0	1068.7	1277.8
127.5°	383.8	420.2	642.0	1013.6	1185.9
130°	398.2	434.5	638.9	975.2	1125.4
132.5°	413.6	448.9	638.9	945.2	1083.4
135°	435.3	471.6	636.3	902.8	1020.4
137.5°	455.8	491.1	636.1	866.8	968.5
140°	471.2	507.5	635.1	837.0	934.7
142.5°	488.6	518.9	638.1	813.2	900.9
145°	513.4	539.7	641.5	781.3	851.4
147.5°	534.7	560.2	647.1	749.1	809.7
150°	553.1	570.6	649.1	738.5	781.0
152.5°	567.5	586.0	651.2	724.0	763.6
155°	586.4	600.2	656.8	706.1	734.9
157.5°	610.0	618.2	658.1	698.0	718.5
160°	622.3	628.5	663.2	691.8	709.3
162.5°	629.4	636.7	664.2	686.6	700.1
165°	647.9	650.4	664.5	678.8	688.8
167.5°	660.4	658.2	670.4	676.9	680.9
170°	664.5	663.3	668.3	669.7	674.7
172.5°	673.7	669.5	671.4	667.7	671.7
175°	678.6	674.8	672.2	668.2	663.2
177.5°	680.6	674.6	671.4	667.3	668.3
180°	673.5	673.5	673.5	673.5	673.5

(END OF REPORT)