

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P520924

Luminaire Tested: SQ4-075U-0D-92765-1D-UNV-STD-W-4_2700K

Issue Date: 5-5-2021

Test Information

Test Method: LM-79-2019
Report Number: P520924
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51)
Test Lab: INNOVATION CENTER
Issue Date: 5-5-2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-075U-0D-92765-1D-UNV-STD-W-4_2700K
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE
INDIRECT ONLY
UPLIGHT 750 LUMENS PER FOOT
Light Source: 2700K-6500K CCT, 90 CRI LEDS, TUNED TO 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3126.0 lumens
Efficiency: N/A
Efficacy: 132.5 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Indirect


Input Watts (W): 23.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P520924

CATALOG NUMBER: SQ4-075U-0D-92765-1D-UNV-STD-W-4_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P520924

CATALOG NUMBER: SQ4-075U-0D-92765-1D-UNV-STD-W-4_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	0
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	0

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 0°
 Luminance: 0 cd/sqm

TEST NUMBER: P520924

CATALOG NUMBER: SQ4-075U-0D-92765-1D-UNV-STD-W-4_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	229.3	7.3
100°-110°	652.5	20.9
110°-120°	625.2	20.0
120°-130°	494.8	15.8
130°-140°	397.1	12.7
140°-150°	310.9	9.9
150°-160°	227.5	7.3
160°-170°	140.9	4.5
170°-180°	47.8	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	1507.0	48.2
90°-150°	2709.8	86.7
90°-180°	3126.0	100.0
0°-180°	3126.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	1
95°	25	99	444	154	95	28
105°	101	154	665	1174	1116	107
115°	188	228	504	1068	1254	186
125°	266	295	481	799	955	238
135°	325	352	476	675	762	251
145°	384	403	479	584	636	240
155°	438	448	491	528	549	203
165°	484	486	496	507	515	136
175°	507	504	502	499	496	48
180°	503	503	503	503	503	

TEST NUMBER: P520924

CATALOG NUMBER: SQ4-075U-0D-92765-1D-UNV-STD-W-4_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0
92.5°	7.7	40.6	94.1	27.4	20.7
95°	24.9	98.8	443.9	153.7	94.7
97.5°	45.7	115.7	683.7	489.2	335.2
100°	60.3	125.8	735.7	745.2	574.0
102.5°	76.3	136.6	724.3	953.9	804.4
105°	101.4	153.8	664.9	1174.5	1116.5
107.5°	126.9	173.8	595.7	1236.7	1288.3
110°	144.5	188.4	555.9	1212.9	1328.9

TEST NUMBER: P520924

CATALOG NUMBER: SQ4-075U-0D-92765-1D-UNV-STD-W-4_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	161.3	203.0	529.1	1156.6	1322.0
115°	188.5	227.8	504.2	1068.1	1254.3
117.5°	212.4	249.3	489.5	971.4	1168.6
120°	231.5	262.4	487.9	916.1	1105.0
122.5°	246.8	277.7	484.1	867.5	1043.0
125°	266.0	295.0	481.2	798.6	954.8
127.5°	286.8	314.0	479.7	757.4	886.1
130°	297.5	324.7	477.4	728.7	841.0
132.5°	309.0	335.4	477.4	706.3	809.6
135°	325.3	352.4	475.5	674.6	762.5
137.5°	340.6	367.0	475.3	647.7	723.7
140°	352.1	379.2	474.5	625.5	698.4
142.5°	365.1	387.7	476.8	607.7	673.2
145°	383.7	403.3	479.3	583.8	636.2
147.5°	399.5	418.6	483.5	559.8	605.0
150°	413.3	426.4	485.1	551.8	583.6
152.5°	424.0	437.9	486.6	541.0	570.6
155°	438.2	448.5	490.8	527.7	549.2
157.5°	455.8	462.0	491.8	521.6	536.9
160°	465.0	469.7	495.6	516.9	530.0
162.5°	470.3	475.8	496.4	513.0	523.1
165°	484.1	486.0	496.5	507.2	514.7
167.5°	493.5	491.8	500.9	505.8	508.8
170°	496.5	495.6	499.4	500.5	504.2
172.5°	503.4	500.3	501.7	498.9	501.9
175°	507.1	504.3	502.3	499.3	495.6
177.5°	508.6	504.1	501.7	498.7	499.4
180°	503.2	503.2	503.2	503.2	503.2

(END OF REPORT)