

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P521213

Luminaire Tested: SQ4-BB-100U-100D-92765-1D-UNV-STD-W-4_4000K

Issue Date: 5-5-2021

Test Information

Test Method: LM-79-2019
Report Number: P521213
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2009-966-12)
Test Lab: INNOVATION CENTER
Issue Date: 5-5-2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-BB-100U-100D-92765-1D-UNV-STD-W-4_4000K
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH BLACK BAFFLE
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: 2700K-6500K CCT, 90 CRI LEDS, TUNED TO 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7047.1 lumens
Efficiency: N/A
Efficacy: 94.2 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.97 / 0.97
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 74.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P521213

CATALOG NUMBER: SQ4-BB-100U-100D-92765-1D-UNV-STD-W-4_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P521213

CATALOG NUMBER: SQ4-BB-100U-100D-92765-1D-UNV-STD-W-4_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	37				
1	96	92	89	86	87	84	81	79	68	67	65	54	53	52	41	40	40	34				
2	89	82	77	73	80	75	71	67	62	59	56	49	47	45	38	37	36	30				
3	82	74	67	62	74	67	62	58	56	52	49	45	42	40	35	33	32	27				
4	75	66	59	54	69	61	55	50	50	46	43	41	38	36	32	30	29	25				
5	70	59	52	47	63	55	48	44	46	41	38	37	34	32	29	27	26	23				
6	65	54	47	41	59	50	43	39	42	37	34	34	31	29	27	25	24	21				
7	60	49	42	37	55	45	39	35	38	34	30	32	28	26	25	23	22	19				
8	56	45	38	33	51	42	35	31	35	31	27	29	26	23	24	21	20	17				
9	52	41	34	30	48	38	32	28	33	28	25	27	24	21	22	20	18	16				
10	49	38	31	27	45	35	29	26	30	26	23	25	22	20	21	18	17	15				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	20067	20067	20067
5°	19744	19695	19842
10°	18474	18720	19243
15°	16795	17328	18292
20°	14908	15683	17057
25°	12983	14011	15671
30°	11120	12342	14360
35°	9220	10477	12776
40°	7084	8377	10887
45°	5121	6343	8759
50°	3489	4728	6947
55°	2268	3420	5400
60°	1301	2408	3903
65°	345	1469	1976
70°	170	453	566
75°	75	39	0
80°	58	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 8759 cd/sqm

TEST NUMBER: P521213

CATALOG NUMBER: SQ4-BB-100U-100D-92765-1D-UNV-STD-W-4_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	198.5	2.8
10°-20°	507.6	7.2
20°-30°	635.5	9.0
30°-40°	587.0	8.3
40°-50°	394.4	5.6
50°-60°	203.7	2.9
60°-70°	63.8	0.9
70°-80°	4.0	0.1
80°-90°	0.1	0.0
90°-100°	326.6	4.6
100°-110°	929.4	13.2
110°-120°	890.4	12.6
120°-130°	704.7	10.0
130°-140°	565.7	8.0
140°-150°	442.8	6.3
150°-160°	324.0	4.6
160°-170°	200.7	2.8
170°-180°	68.1	1.0
0°-30°	1341.6	19.0
0°-40°	1928.5	27.4
0°-60°	2526.7	35.9
0°-90°	2594.6	36.8
90°-120°	2146.4	30.5
90°-150°	3859.7	54.8
90°-180°	4453.0	63.2
0°-180°	7047.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2175	2175	2175	2175	2175	
5°	2132	2110	2127	2134	2142	198
15°	1758	1752	1814	1875	1915	490
25°	1275	1286	1376	1470	1539	585
35°	819	839	930	1040	1134	507
45°	392	416	486	581	671	308
55°	141	165	213	273	336	132
65°	16	30	67	81	90	27
75°	2	2	1	0	0	3
85°	0	0	0	0	0	0
90°	0	0	0	0	0	1
95°	35	141	632	219	135	40
105°	144	219	947	1673	1590	153
115°	268	324	718	1521	1786	264
125°	379	420	686	1138	1360	339
135°	463	502	677	961	1086	358
145°	546	574	683	832	906	341
155°	624	639	699	752	782	289
165°	690	692	707	722	733	194
175°	722	718	715	711	706	68
180°	717	717	717	717	717	

TEST NUMBER: P521213

CATALOG NUMBER: SQ4-BB-100U-100D-92765-1D-UNV-STD-W-4_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2175.0	2175.0	2175.0	2175.0	2175.0
2.5°	2180.0	2159.5	2164.9	2164.8	2159.0
5°	2131.9	2110.2	2126.6	2134.1	2142.4
7.5°	2041.8	2024.9	2056.3	2079.8	2096.9
10°	1971.9	1957.5	1998.2	2030.3	2054.0
12.5°	1891.1	1880.0	1929.2	1973.2	2003.5
15°	1758.3	1752.1	1814.1	1875.0	1915.1
17.5°	1616.0	1615.8	1686.5	1762.1	1810.5
20°	1518.4	1521.5	1597.3	1680.7	1737.3
22.5°	1420.7	1427.9	1508.9	1595.8	1660.7
25°	1275.3	1285.6	1376.3	1470.5	1539.4
27.5°	1135.6	1150.6	1246.1	1343.9	1427.9
30°	1043.8	1061.3	1158.5	1261.5	1347.9
32.5°	953.8	974.5	1069.3	1178.2	1266.3
35°	818.6	839.2	930.2	1039.7	1134.3
37.5°	679.1	699.3	788.1	895.9	998.2
40°	588.2	610.8	695.5	800.0	903.9
42.5°	505.7	528.3	608.0	710.6	808.8
45°	392.5	416.2	486.1	580.8	671.3
47.5°	298.6	324.3	385.8	471.4	553.9
50°	243.1	268.8	329.4	404.8	484.0
52.5°	198.5	223.4	278.0	349.1	421.7
55°	141.0	164.7	212.6	272.9	335.7
57.5°	97.4	117.8	160.8	211.1	260.3
60°	70.5	90.0	130.5	171.4	211.5
62.5°	46.9	64.8	104.4	135.7	162.7
65°	15.8	30.2	67.3	81.2	90.5
67.5°	8.0	9.6	35.4	37.3	40.4
70°	6.3	6.3	16.8	18.0	21.0
72.5°	4.6	4.6	6.7	8.6	9.3
75°	2.1	2.1	1.1	0.0	0.0
77.5°	1.1	1.1	0.8	0.0	0.0
80°	1.1	1.1	0.0	0.0	0.0
82.5°	0.2	0.2	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0
92.5°	10.9	57.8	134.1	39.0	29.4
95°	35.4	140.7	632.3	218.9	134.9
97.5°	65.1	164.8	973.8	696.8	477.5
100°	85.9	179.1	1047.9	1061.5	817.6
102.5°	108.7	194.6	1031.6	1358.7	1145.8
105°	144.4	219.1	947.1	1672.9	1590.3
107.5°	180.7	247.6	848.4	1761.5	1835.1
110°	205.8	268.4	791.7	1727.6	1892.8

TEST NUMBER: P521213

CATALOG NUMBER: SQ4-BB-100U-100D-92765-1D-UNV-STD-W-4_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	229.8	289.2	753.6	1647.4	1883.0
115°	268.5	324.4	718.2	1521.4	1786.5
117.5°	302.5	355.0	697.2	1383.6	1664.4
120°	329.8	373.8	695.0	1304.8	1574.0
122.5°	351.6	395.6	689.5	1235.7	1485.7
125°	378.8	420.1	685.5	1137.5	1360.0
127.5°	408.5	447.2	683.3	1078.8	1262.2
130°	423.8	462.5	680.0	1037.9	1197.8
132.5°	440.2	477.7	680.0	1006.0	1153.1
135°	463.3	502.0	677.3	960.8	1086.1
137.5°	485.1	522.7	677.0	922.6	1030.8
140°	501.5	540.1	675.9	890.9	994.8
142.5°	520.0	552.3	679.2	865.5	958.8
145°	546.5	574.4	682.7	831.6	906.2
147.5°	569.1	596.3	688.7	797.3	861.8
150°	588.7	607.4	690.9	786.0	831.3
152.5°	604.0	623.7	693.1	770.6	812.7
155°	624.1	638.8	699.1	751.6	782.2
157.5°	649.2	658.0	700.4	742.9	764.8
160°	662.3	668.9	705.9	736.3	755.0
162.5°	669.9	677.6	707.0	730.8	745.1
165°	689.5	692.2	707.3	722.5	733.1
167.5°	702.9	700.5	713.5	720.4	724.7
170°	707.3	705.9	711.3	712.8	718.2
172.5°	717.1	712.5	714.6	710.6	714.9
175°	722.2	718.3	715.4	711.2	705.9
177.5°	724.4	718.0	714.6	710.3	711.3
180°	716.8	716.8	716.8	716.8	716.8

(END OF REPORT)