

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P520927

Luminaire Tested: SQ4-075U-0D-92765-1D-UNV-STD-W-4_4000K

Issue Date: 5-5-2021

Test Information

Test Method: LM-79-2019
Report Number: P520927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51)
Test Lab: INNOVATION CENTER
Issue Date: 5-5-2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-075U-0D-92765-1D-UNV-STD-W-4_4000K
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE
INDIRECT ONLY
UPLIGHT 750 LUMENS PER FOOT
Light Source: 2700K-6500K CCT, 90 CRI LEDS, TUNED TO 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3327.1 lumens
Efficiency: N/A
Efficacy: 140.4 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Indirect


Input Watts (W): 23.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P520927

CATALOG NUMBER: SQ4-075U-0D-92765-1D-UNV-STD-W-4_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P520927

CATALOG NUMBER: SQ4-075U-0D-92765-1D-UNV-STD-W-4_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	0
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	0

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 0°
 Luminance: 0 cd/sqm

TEST NUMBER: P520927

CATALOG NUMBER: SQ4-075U-0D-92765-1D-UNV-STD-W-4_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	244.1	7.3
100°-110°	694.5	20.9
110°-120°	665.4	20.0
120°-130°	526.6	15.8
130°-140°	422.7	12.7
140°-150°	330.9	9.9
150°-160°	242.1	7.3
160°-170°	150.0	4.5
170°-180°	50.9	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	1603.9	48.2
90°-150°	2884.1	86.7
90°-180°	3327.0	100.0
0°-180°	3327.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	1
95°	26	105	472	164	101	30
105°	108	164	708	1250	1188	114
115°	201	242	537	1137	1335	198
125°	283	314	512	850	1016	253
135°	346	375	506	718	812	267
145°	408	429	510	621	677	255
155°	466	477	522	562	584	216
165°	515	517	528	540	548	145
175°	540	537	535	532	528	51
180°	536	536	536	536	536	

TEST NUMBER: P520927

CATALOG NUMBER: SQ4-075U-0D-92765-1D-UNV-STD-W-4_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0
92.5°	8.1	43.2	100.2	29.2	22.0
95°	26.5	105.1	472.5	163.5	100.8
97.5°	48.7	123.2	727.7	520.7	356.8
100°	64.2	133.8	783.1	793.2	611.0
102.5°	81.3	145.4	770.8	1015.3	856.2
105°	107.9	163.7	707.7	1250.1	1188.4
107.5°	135.0	185.0	634.0	1316.3	1371.2
110°	153.8	200.6	591.6	1290.9	1414.4

TEST NUMBER: P520927

CATALOG NUMBER: SQ4-075U-0D-92765-1D-UNV-STD-W-4_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	171.7	216.1	563.1	1231.0	1407.1
115°	200.6	242.4	536.6	1136.8	1335.0
117.5°	226.1	265.3	521.0	1033.9	1243.7
120°	246.4	279.3	519.3	975.0	1176.1
122.5°	262.7	295.6	515.3	923.4	1110.1
125°	283.1	314.0	512.2	850.0	1016.3
127.5°	305.3	334.2	510.6	806.1	943.1
130°	316.7	345.6	508.1	775.6	895.1
132.5°	328.9	357.0	508.1	751.8	861.7
135°	346.2	375.1	506.1	718.0	811.6
137.5°	362.5	390.6	505.9	689.4	770.2
140°	374.7	403.6	505.1	665.7	743.4
142.5°	388.6	412.7	507.5	646.8	716.5
145°	408.3	429.2	510.2	621.4	677.2
147.5°	425.2	445.6	514.6	595.8	644.0
150°	439.9	453.8	516.3	587.3	621.2
152.5°	451.3	466.0	517.9	575.8	607.3
155°	466.4	477.3	522.4	561.6	584.5
157.5°	485.1	491.7	523.4	555.1	571.5
160°	494.9	499.9	527.5	550.2	564.1
162.5°	500.6	506.4	528.3	546.1	556.8
165°	515.3	517.2	528.5	539.9	547.8
167.5°	525.2	523.4	533.2	538.3	541.5
170°	528.5	527.5	531.5	532.7	536.6
172.5°	535.8	532.4	534.0	531.0	534.2
175°	539.7	536.7	534.6	531.5	527.5
177.5°	541.3	536.5	534.0	530.8	531.5
180°	535.6	535.6	535.6	535.6	535.6

(END OF REPORT)