

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P520930

Luminaire Tested: SQ4-075U-0D-92765-1D-UNV-STD-W-4_5700K

Issue Date: 5-5-2021

Test Information

Test Method: LM-79-2019
Report Number: P520930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51)
Test Lab: INNOVATION CENTER
Issue Date: 5-5-2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-075U-0D-92765-1D-UNV-STD-W-4_5700K
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE
INDIRECT ONLY
UPLIGHT 750 LUMENS PER FOOT
Light Source: 2700K-6500K CCT, 90 CRI LEDS, TUNED TO 5700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3466.9 lumens
Efficiency: N/A
Efficacy: 146.9 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 23.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P520930
CATALOG NUMBER: SQ4-075U-0D-92765-1D-UNV-STD-W-4_5700K

Luminous Intensity Polar Plot



TEST NUMBER: P520930

CATALOG NUMBER: SQ4-075U-0D-92765-1D-UNV-STD-W-4_5700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	0
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	0

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 0°
 Luminance: 0 cd/sqm

TEST NUMBER: P520930

CATALOG NUMBER: SQ4-075U-0D-92765-1D-UNV-STD-W-4_5700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	254.3	7.3
100°-110°	723.6	20.9
110°-120°	693.3	20.0
120°-130°	548.7	15.8
130°-140°	440.5	12.7
140°-150°	344.8	9.9
150°-160°	252.3	7.3
160°-170°	156.3	4.5
170°-180°	53.0	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	1671.3	48.2
90°-150°	3005.3	86.7
90°-180°	3467.0	100.0
0°-180°	3466.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	1
95°	28	110	492	170	105	32
105°	112	171	737	1303	1238	119
115°	209	253	559	1185	1391	206
125°	295	327	534	886	1059	264
135°	361	391	527	748	846	278
145°	426	447	532	648	706	266
155°	486	497	544	585	609	225
165°	537	539	551	563	571	151
175°	562	559	557	554	550	53
180°	558	558	558	558	558	

TEST NUMBER: P520930

CATALOG NUMBER: SQ4-075U-0D-92765-1D-UNV-STD-W-4_5700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0
92.5°	8.5	45.0	104.4	30.4	22.9
95°	27.6	109.5	492.3	170.4	105.0
97.5°	50.7	128.3	758.2	542.6	371.8
100°	66.8	139.5	816.0	826.5	636.6
102.5°	84.7	151.5	803.2	1057.9	892.1
105°	112.5	170.6	737.4	1302.6	1238.3
107.5°	140.7	192.8	660.6	1371.6	1428.8
110°	160.2	209.0	616.5	1345.2	1473.8

TEST NUMBER: P520930

CATALOG NUMBER: SQ4-075U-0D-92765-1D-UNV-STD-W-4_5700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	178.9	225.2	586.8	1282.8	1466.2
115°	209.0	252.6	559.2	1184.6	1391.1
117.5°	235.6	276.4	542.8	1077.3	1296.0
120°	256.8	291.0	541.1	1016.0	1225.5
122.5°	273.8	308.0	536.9	962.1	1156.8
125°	295.0	327.1	533.7	885.7	1058.9
127.5°	318.1	348.2	532.0	840.0	982.8
130°	330.0	360.1	529.5	808.2	932.7
132.5°	342.7	372.0	529.5	783.3	897.9
135°	360.8	390.9	527.4	748.1	845.7
137.5°	377.7	407.0	527.1	718.4	802.6
140°	390.5	420.6	526.3	693.7	774.6
142.5°	404.9	430.0	528.8	673.9	746.6
145°	425.5	447.3	531.6	647.5	705.6
147.5°	443.1	464.3	536.3	620.8	671.0
150°	458.4	472.9	538.0	612.0	647.3
152.5°	470.3	485.6	539.7	600.0	632.8
155°	486.0	497.4	544.3	585.2	609.1
157.5°	505.5	512.3	545.4	578.5	595.5
160°	515.7	520.9	549.6	573.3	587.8
162.5°	521.6	527.6	550.5	569.0	580.2
165°	536.9	539.0	550.7	562.6	570.9
167.5°	547.3	545.4	555.6	561.0	564.3
170°	550.7	549.7	553.9	555.0	559.2
172.5°	558.3	554.8	556.4	553.3	556.6
175°	562.4	559.3	557.1	553.8	549.6
177.5°	564.1	559.1	556.4	553.0	553.9
180°	558.1	558.1	558.1	558.1	558.1

(END OF REPORT)