

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P521266

Luminaire Tested: SQ4-BB-125U-100D-92765-1D-UNV-STD-W-4_4500K

Issue Date: 5-5-2021

Test Information

Test Method: LM-79-2019
Report Number: P521266
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2009-966-12)
Test Lab: INNOVATION CENTER
Issue Date: 5-5-2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-BB-125U-100D-92765-1D-UNV-STD-W-4_4500K
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH BLACK BAFFLE
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 2700K-6500K CCT, 90 CRI LEDS, TUNED TO 4500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8318.9 lumens
Efficiency: N/A
Efficacy: 99.4 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.97 / 0.97
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 83.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P521266

CATALOG NUMBER: SQ4-BB-125U-100D-92765-1D-UNV-STD-W-4_4500K

Luminous Intensity Polar Plot



TEST NUMBER: P521266

CATALOG NUMBER: SQ4-BB-125U-100D-92765-1D-UNV-STD-W-4_4500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	103	103	103	103	92	92	92	92	73	73	73		56	56	56		39	39	39	32
1	95	91	88	85	85	82	79	77	66	64	62		50	49	48		36	36	35	29
2	87	81	75	71	79	73	69	65	59	56	53		46	44	42		33	32	32	26
3	80	72	66	61	72	65	60	56	53	49	46		41	39	37		31	29	28	24
4	74	65	58	52	67	59	53	48	48	44	40		38	35	33		28	27	25	21
5	68	58	51	45	62	53	47	42	43	39	36		34	31	29		26	24	23	19
6	63	52	45	40	57	48	42	37	39	35	32		32	28	26		24	22	21	18
7	59	48	40	35	53	44	37	33	36	32	28		29	26	24		22	20	19	16
8	55	44	36	32	50	40	34	30	33	29	25		27	24	21		21	19	17	15
9	51	40	33	28	46	37	31	27	31	26	23		25	22	20		19	17	16	14
10	48	37	30	26	43	34	28	24	28	24	21		23	20	18		18	16	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	20391	20391	20391
5°	20062	20013	20161
10°	18772	19023	19553
15°	17066	17607	18588
20°	15149	15936	17332
25°	13192	14237	15925
30°	11300	12541	14592
35°	9370	10646	12982
40°	7199	8513	11062
45°	5203	6446	8901
50°	3545	4804	7059
55°	2305	3474	5487
60°	1321	2447	3965
65°	349	1493	2008
70°	173	461	577
75°	75	39	0
80°	58	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 8901 cd/sqm

TEST NUMBER: P521266

CATALOG NUMBER: SQ4-BB-125U-100D-92765-1D-UNV-STD-W-4_4500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	201.7	2.4
10°-20°	515.8	6.2
20°-30°	645.7	7.8
30°-40°	596.4	7.2
40°-50°	400.8	4.8
50°-60°	207.0	2.5
60°-70°	64.8	0.8
70°-80°	4.1	0.0
80°-90°	0.1	0.0
90°-100°	416.8	5.0
100°-110°	1186.1	14.3
110°-120°	1136.4	13.7
120°-130°	899.4	10.8
130°-140°	721.9	8.7
140°-150°	565.2	6.8
150°-160°	413.5	5.0
160°-170°	256.2	3.1
170°-180°	86.9	1.0
0°-30°	1363.2	16.4
0°-40°	1959.7	23.6
0°-60°	2567.4	30.9
0°-90°	2636.4	31.7
90°-120°	2739.4	32.9
90°-150°	4925.9	59.2
90°-180°	5682.0	68.3
0°-180°	8318.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2210	2210	2210	2210	2210	
5°	2166	2144	2161	2169	2177	201
15°	1787	1780	1843	1905	1946	498
25°	1296	1306	1398	1494	1564	594
35°	832	853	945	1056	1153	515
45°	399	423	494	590	682	313
55°	143	167	216	277	341	134
65°	16	31	68	82	92	27
75°	2	2	1	0	0	3
85°	0	0	0	0	0	0
90°	0	0	0	0	0	2
95°	45	180	807	279	172	52
105°	184	280	1209	2135	2030	195
115°	343	414	916	1942	2280	337
125°	484	536	875	1452	1736	433
135°	591	641	864	1226	1386	456
145°	697	733	871	1061	1157	436
155°	796	815	892	959	998	368
165°	880	883	903	922	936	247
175°	922	917	913	908	901	87
180°	915	915	915	915	915	

TEST NUMBER: P521266

CATALOG NUMBER: SQ4-BB-125U-100D-92765-1D-UNV-STD-W-4_4500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2210.1	2210.1	2210.1	2210.1	2210.1
2.5°	2215.2	2194.3	2199.8	2199.7	2193.8
5°	2166.2	2144.3	2160.9	2168.6	2176.9
7.5°	2074.7	2057.6	2089.5	2113.4	2130.7
10°	2003.7	1989.1	2030.5	2063.1	2087.1
12.5°	1921.6	1910.3	1960.3	2005.1	2035.8
15°	1786.7	1780.4	1843.3	1905.2	1946.0
17.5°	1642.1	1641.9	1713.7	1790.6	1839.7
20°	1542.9	1546.0	1623.1	1707.8	1765.3
22.5°	1443.7	1451.0	1533.3	1621.6	1687.4
25°	1295.9	1306.4	1398.5	1494.2	1564.3
27.5°	1153.9	1169.2	1266.2	1365.6	1450.9
30°	1060.7	1078.4	1177.2	1281.9	1369.7
32.5°	969.1	990.3	1086.5	1197.2	1286.7
35°	831.9	852.8	945.2	1056.4	1152.6
37.5°	690.1	710.6	800.8	910.3	1014.3
40°	597.7	620.7	706.8	812.9	918.5
42.5°	513.9	536.9	617.8	722.1	821.8
45°	398.8	422.9	494.0	590.2	682.2
47.5°	303.4	329.6	392.0	479.0	562.8
50°	247.0	273.1	334.7	411.3	491.8
52.5°	201.7	227.0	282.5	354.7	428.5
55°	143.3	167.3	216.0	277.3	341.1
57.5°	99.0	119.7	163.4	214.6	264.5
60°	71.6	91.5	132.6	174.1	214.9
62.5°	47.7	65.9	106.1	137.9	165.3
65°	16.0	30.7	68.4	82.5	92.0
67.5°	8.1	9.8	35.9	37.9	41.1
70°	6.4	6.4	17.1	18.2	21.4
72.5°	4.7	4.7	6.8	8.8	9.4
75°	2.1	2.1	1.1	0.0	0.0
77.5°	1.1	1.1	0.9	0.0	0.0
80°	1.1	1.1	0.0	0.0	0.0
82.5°	0.2	0.2	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0
92.5°	13.9	73.8	171.1	49.8	37.6
95°	45.2	179.6	807.0	279.3	172.2
97.5°	83.1	210.3	1242.8	889.3	609.4
100°	109.6	228.6	1337.4	1354.7	1043.5
102.5°	138.8	248.3	1316.6	1734.0	1462.3
105°	184.4	279.6	1208.7	2135.1	2029.6
107.5°	230.6	316.0	1082.8	2248.1	2342.0
110°	262.6	342.5	1010.5	2204.9	2415.7

TEST NUMBER: P521266

CATALOG NUMBER: SQ4-BB-125U-100D-92765-1D-UNV-STD-W-4_4500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	293.2	369.1	961.8	2102.5	2403.2
115°	342.6	414.0	916.5	1941.7	2280.1
117.5°	386.1	453.1	889.8	1765.8	2124.2
120°	420.9	477.0	887.0	1665.2	2008.8
122.5°	448.7	504.8	880.0	1577.0	1896.1
125°	483.5	536.2	874.8	1451.7	1735.7
127.5°	521.4	570.7	872.0	1376.8	1610.8
130°	540.9	590.2	867.9	1324.7	1528.7
132.5°	561.8	609.7	867.9	1284.0	1471.7
135°	591.3	640.6	864.4	1226.3	1386.1
137.5°	619.1	667.1	864.0	1177.4	1315.5
140°	640.0	689.3	862.6	1137.0	1269.6
142.5°	663.7	704.8	866.8	1104.6	1223.7
145°	697.4	733.1	871.3	1061.3	1156.6
147.5°	726.3	761.0	879.0	1017.6	1099.9
150°	751.3	775.1	881.8	1003.1	1060.9
152.5°	770.8	796.0	884.5	983.5	1037.2
155°	796.5	815.2	892.2	959.2	998.3
157.5°	828.5	839.8	893.9	948.1	976.0
160°	845.2	853.7	900.9	939.7	963.5
162.5°	855.0	864.8	902.3	932.6	951.0
165°	880.0	883.4	902.6	922.1	935.7
167.5°	897.1	894.0	910.6	919.5	924.9
170°	902.6	900.9	907.9	909.7	916.5
172.5°	915.2	909.4	912.0	906.9	912.4
175°	921.8	916.7	913.1	907.7	900.9
177.5°	924.5	916.4	912.0	906.5	907.9
180°	914.8	914.8	914.8	914.8	914.8

(END OF REPORT)