

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P520939

Luminaire Tested: SQ4-100U-0D-92765-1D-UNV-STD-W-4\_3500K

Issue Date: 5-5-2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P520939  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51)  
Test Lab: INNOVATION CENTER  
Issue Date: 5-5-2021  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ4-100U-0D-92765-1D-UNV-STD-W-4\_3500K  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE  
INDIRECT ONLY  
UPLIGHT 1000 LUMENS PER FOOT  
Light Source: 2700K-6500K CCT, 90 CRI LEDS, TUNED TO 3500K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4372.5 lumens  
Efficiency: N/A  
Efficacy: 135.0 lumens/watt  
Spacing Criteria (0/90/45): - / - / -  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: Indirect


Input Watts (W): 32.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P520939

CATALOG NUMBER: SQ4-100U-0D-92765-1D-UNV-STD-W-4\_3500K

### Luminous Intensity Polar Plot



TEST NUMBER: P520939

CATALOG NUMBER: SQ4-100U-0D-92765-1D-UNV-STD-W-4\_3500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	0
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	0

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 0°  
 Luminance: 0 cd/sqm

TEST NUMBER: P520939

CATALOG NUMBER: SQ4-100U-0D-92765-1D-UNV-STD-W-4\_3500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	320.7	7.3
100°-110°	912.7	20.9
110°-120°	874.4	20.0
120°-130°	692.1	15.8
130°-140°	555.5	12.7
140°-150°	434.9	9.9
150°-160°	318.2	7.3
160°-170°	197.1	4.5
170°-180°	66.9	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	2107.9	48.2
90°-150°	3790.4	86.7
90°-180°	4373.0	100.0
0°-180°	4372.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	1
95°	35	138	621	215	132	40
105°	142	215	930	1643	1562	150
115°	264	319	705	1494	1754	260
125°	372	413	673	1117	1336	333
135°	455	493	665	944	1067	351
145°	537	564	670	817	890	335
155°	613	627	686	738	768	283
165°	677	680	695	710	720	190
175°	709	705	703	698	693	67
180°	704	704	704	704	704	

TEST NUMBER: P520939

CATALOG NUMBER: SQ4-100U-0D-92765-1D-UNV-STD-W-4\_3500K

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0
92.5°	10.7	56.8	131.7	38.3	28.9
95°	34.8	138.2	620.9	214.9	132.5
97.5°	64.0	161.8	956.3	684.3	468.9
100°	84.3	175.9	1029.1	1042.4	802.9
102.5°	106.8	191.1	1013.1	1334.3	1125.2
105°	141.9	215.1	930.1	1642.9	1561.7
107.5°	177.5	243.1	833.2	1729.9	1802.1
110°	202.1	263.6	777.5	1696.6	1858.8

TEST NUMBER: P520939

CATALOG NUMBER: SQ4-100U-0D-92765-1D-UNV-STD-W-4\_3500K

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	225.6	284.0	740.1	1617.8	1849.2
115°	263.6	318.6	705.3	1494.1	1754.4
117.5°	297.1	348.6	684.6	1358.7	1634.5
120°	323.9	367.0	682.5	1281.4	1545.7
122.5°	345.3	388.4	677.2	1213.5	1459.0
125°	372.0	412.6	673.1	1117.1	1335.6
127.5°	401.2	439.2	671.0	1059.4	1239.5
130°	416.2	454.1	667.8	1019.3	1176.3
132.5°	432.3	469.2	667.8	988.0	1132.4
135°	455.0	493.0	665.1	943.6	1066.6
137.5°	476.4	513.3	664.8	906.0	1012.3
140°	492.5	530.4	663.8	874.9	976.9
142.5°	510.7	542.3	667.0	850.0	941.6
145°	536.6	564.1	670.5	816.7	889.9
147.5°	558.9	585.5	676.4	783.0	846.3
150°	578.1	596.4	678.5	771.8	816.3
152.5°	593.1	612.5	680.6	756.8	798.1
155°	612.9	627.3	686.5	738.1	768.2
157.5°	637.5	646.2	687.9	729.6	751.0
160°	650.4	656.9	693.2	723.1	741.4
162.5°	657.9	665.5	694.3	717.6	731.8
165°	677.2	679.8	694.6	709.5	720.0
167.5°	690.3	687.9	700.7	707.5	711.7
170°	694.6	693.2	698.6	700.0	705.3
172.5°	704.2	699.7	701.8	697.9	702.0
175°	709.3	705.3	702.6	698.4	693.2
177.5°	711.4	705.1	701.8	697.5	698.6
180°	703.9	703.9	703.9	703.9	703.9

(END OF REPORT)