

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P520942

Luminaire Tested: SQ4-100U-0D-92765-1D-UNV-STD-W-4_5000K

Issue Date: 5-5-2021

Test Information

Test Method: LM-79-2019
Report Number: P520942
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51)
Test Lab: INNOVATION CENTER
Issue Date: 5-5-2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-100U-0D-92765-1D-UNV-STD-W-4_5000K
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE
INDIRECT ONLY
UPLIGHT 1000 LUMENS PER FOOT
Light Source: 2700K-6500K CCT, 90 CRI LEDS, TUNED TO 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4574.4 lumens
Efficiency: N/A
Efficacy: 141.6 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Indirect


Input Watts (W): 32.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P520942

CATALOG NUMBER: SQ4-100U-0D-92765-1D-UNV-STD-W-4_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P520942

CATALOG NUMBER: SQ4-100U-0D-92765-1D-UNV-STD-W-4_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	0
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	0

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 0°
 Luminance: 0 cd/sqm

TEST NUMBER: P520942

CATALOG NUMBER: SQ4-100U-0D-92765-1D-UNV-STD-W-4_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	335.6	7.3
100°-110°	954.8	20.9
110°-120°	914.8	20.0
120°-130°	724.0	15.8
130°-140°	581.1	12.7
140°-150°	455.0	9.9
150°-160°	332.9	7.3
160°-170°	206.2	4.5
170°-180°	70.0	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	2205.2	48.2
90°-150°	3965.3	86.7
90°-180°	4574.0	100.0
0°-180°	4574.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	2
95°	36	144	650	225	139	42
105°	148	225	973	1719	1634	157
115°	276	333	738	1563	1835	272
125°	389	432	704	1169	1397	348
135°	476	516	696	987	1116	367
145°	561	590	701	854	931	351
155°	641	656	718	772	804	296
165°	708	711	727	742	753	199
175°	742	738	735	731	725	70
180°	736	736	736	736	736	

TEST NUMBER: P520942

CATALOG NUMBER: SQ4-100U-0D-92765-1D-UNV-STD-W-4_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0
92.5°	11.2	59.4	137.8	40.1	30.2
95°	36.4	144.5	649.6	224.8	138.6
97.5°	66.9	169.3	1000.5	715.9	490.6
100°	88.2	184.0	1076.6	1090.5	840.0
102.5°	111.7	199.9	1059.8	1395.9	1177.1
105°	148.4	225.1	973.0	1718.7	1633.8
107.5°	185.6	254.4	871.7	1809.7	1885.3
110°	211.4	275.7	813.4	1774.9	1944.6

TEST NUMBER: P520942

CATALOG NUMBER: SQ4-100U-0D-92765-1D-UNV-STD-W-4_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	236.0	297.1	774.2	1692.5	1934.6
115°	275.8	333.3	737.8	1563.0	1835.4
117.5°	310.8	364.7	716.3	1421.4	1710.0
120°	338.8	384.0	714.0	1340.5	1617.0
122.5°	361.2	406.4	708.4	1269.5	1526.3
125°	389.2	431.6	704.2	1168.6	1397.2
127.5°	419.7	459.4	702.0	1108.3	1296.7
130°	435.4	475.1	698.6	1066.4	1230.6
132.5°	452.2	490.8	698.6	1033.6	1184.7
135°	476.0	515.7	695.8	987.1	1115.8
137.5°	498.4	537.0	695.5	947.8	1059.0
140°	515.2	554.9	694.4	915.2	1022.0
142.5°	534.3	567.4	697.8	889.2	985.1
145°	561.4	590.2	701.4	854.4	931.0
147.5°	584.7	612.6	707.6	819.1	885.4
150°	604.8	624.0	709.8	807.5	854.0
152.5°	620.5	640.8	712.1	791.7	835.0
155°	641.2	656.3	718.2	772.1	803.6
157.5°	667.0	676.0	719.6	763.2	785.7
160°	680.4	687.3	725.2	756.5	775.6
162.5°	688.3	696.2	726.3	750.8	765.5
165°	708.4	711.2	726.6	742.3	753.2
167.5°	722.1	719.7	733.1	740.2	744.5
170°	726.6	725.2	730.8	732.3	737.8
172.5°	736.7	732.0	734.2	730.1	734.5
175°	742.0	737.9	735.0	730.7	725.2
177.5°	744.3	737.7	734.2	729.7	730.8
180°	736.4	736.4	736.4	736.4	736.4

(END OF REPORT)